

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580593

Luminaire Tested: **HCC4W40D010BZ-HM43040835-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010BZ-HM43040835-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4181.7 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580593
CATALOG NUMBER: HCC4W40D010BZ-HM43040835-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580593

CATALOG NUMBER: HCC4W40D010BZ-HM43040835-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90				88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79				77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69				67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34				32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	270608	270608	270608
5°	277721	270626	265575
10°	284013	268295	257724
15°	291991	264498	250924
20°	291204	254359	240760
25°	278930	238129	229228
30°	256568	219309	217002
35°	225715	199033	200689
40°	195281	178165	185620
45°	169710	158319	167808
50°	150616	139620	149042
55°	133630	122491	127759
60°	119004	106225	106225
65°	105799	88317	82713
70°	91422	66826	59000
75°	76633	44178	36362
80°	58033	21239	19321
85°	30711	7784	7784



TEST NUMBER: P580593
 CATALOG NUMBER: HCC4W40D010BZ-HM43040835-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.8	5.0
10°-20°	589.0	14.1
20°-30°	830.7	19.9
30°-40°	858.2	20.5
40°-50°	727.5	17.4
50°-60°	529.3	12.7
60°-70°	309.3	7.4
70°-80°	114.9	2.7
80°-90°	15.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1627.5	38.9
0°-40°	2485.7	59.4
0°-60°	3742.5	89.5
0°-90°	4181.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4181.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2194	2194	2194	2194	2194	
5°	2243	2224	2186	2153	2145	215
15°	2287	2216	2071	1984	1965	643
25°	2050	1935	1750	1687	1684	937
35°	1499	1434	1322	1325	1333	936
45°	973	946	908	940	962	757
55°	621	591	570	589	594	559
65°	362	332	303	283	283	360
75°	161	134	93	74	76	173
85°	22	14	6	6	6	30
90°	0	0	0	0	0	



TEST NUMBER: P580593

CATALOG NUMBER: HCC4W40D010BZ-HM43040835-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2193.9	2193.9	2193.9	2193.9	2193.9	2193.9	2193.9	2193.9	2193.9
2.5°	2213.1	2207.6	2202.1	2193.9	2183.0	2174.9	2166.7	2161.3	2161.3
5°	2243.0	2234.8	2224.0	2204.9	2185.7	2169.5	2153.1	2144.9	2144.9
7.5°	2264.8	2253.9	2232.1	2204.9	2172.2	2147.6	2123.1	2112.2	2106.7
10°	2267.6	2256.6	2226.6	2185.7	2142.1	2104.0	2076.8	2060.4	2057.7
12.5°	2272.9	2259.4	2221.1	2164.0	2106.7	2060.4	2030.5	2014.1	2008.6
15°	2286.6	2267.6	2215.8	2142.1	2071.3	2016.8	1984.1	1970.5	1965.0
17.5°	2272.9	2245.7	2183.0	2095.8	2016.8	1956.8	1924.1	1910.5	1910.5
20°	2218.5	2191.2	2117.7	2022.3	1937.8	1880.5	1847.9	1839.7	1834.2
22.5°	2142.1	2112.2	2033.2	1932.3	1847.9	1796.1	1774.2	1763.3	1760.6
25°	2049.5	2019.5	1935.1	1831.5	1749.7	1706.0	1687.0	1687.0	1684.3
27.5°	1945.9	1907.8	1820.6	1730.6	1651.6	1618.8	1610.8	1610.8	1613.5
30°	1801.4	1774.2	1700.7	1613.5	1539.8	1518.1	1518.1	1523.6	1523.6
32.5°	1646.2	1627.0	1561.7	1485.3	1428.2	1414.5	1420.0	1430.8	1433.5
35°	1499.0	1477.1	1433.5	1365.4	1321.8	1316.4	1324.6	1332.8	1332.8
37.5°	1354.5	1332.8	1302.7	1248.2	1215.5	1218.3	1229.2	1240.1	1248.2
40°	1212.8	1196.4	1174.7	1131.1	1106.5	1117.4	1131.1	1142.0	1152.8
42.5°	1087.5	1071.1	1054.7	1022.0	1005.6	1019.3	1035.7	1046.6	1057.4
45°	972.9	962.0	945.7	918.4	907.6	921.2	940.3	951.2	962.0
47.5°	874.8	869.4	847.6	823.0	817.7	831.2	847.6	861.3	869.4
50°	784.9	776.7	757.7	733.1	727.6	749.5	760.4	768.6	776.7
52.5°	697.7	689.5	667.7	645.9	645.9	662.3	670.5	673.2	681.3
55°	621.4	613.2	591.4	575.1	569.6	583.3	588.6	588.6	594.1
57.5°	550.5	542.3	520.6	501.4	498.7	506.9	506.9	506.9	509.6
60°	482.4	474.2	452.4	436.1	430.6	433.4	430.6	427.9	430.6
62.5°	419.7	411.5	389.8	370.6	365.2	365.2	357.0	354.3	357.0
65°	362.5	348.9	332.5	313.4	302.6	294.4	283.4	283.4	283.4
67.5°	305.2	294.4	275.3	256.1	242.6	228.9	212.5	218.0	220.7
70°	253.5	245.3	223.5	204.4	185.3	168.9	155.4	160.8	163.6
72.5°	207.2	196.2	177.1	155.4	139.0	117.1	109.0	114.5	114.5
75°	160.8	149.9	133.5	111.8	92.7	73.5	73.5	76.3	76.3
77.5°	119.9	109.0	92.7	73.5	57.3	43.6	46.3	46.3	46.3
80°	81.7	73.5	60.0	43.6	29.9	24.5	24.5	24.5	27.2
82.5°	46.3	40.9	32.7	21.7	13.7	13.7	13.7	13.7	13.7
85°	21.7	16.4	13.7	8.2	5.5	5.5	5.5	5.5	5.5
87.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)