

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580581

Luminaire Tested: **HCC4S40D010MW-HM43040835-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010MW-HM43040835-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4007.3 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580581
CATALOG NUMBER: HCC4S40D010MW-HM43040835-41MDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580581

CATALOG NUMBER: HCC4S40D010MW-HM43040835-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93					93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86					86			
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79					79			
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73					73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67					67			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62					62			
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58					58			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54					54			
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51					51			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47					47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	518779
5°	507934
10°	480002
15°	448305
20°	410022
25°	366141
30°	307472
35°	216289
40°	133418
45°	79875
50°	47071
55°	23462
60°	12113
65°	7939
70°	4941
75°	3908
80°	1918
85°	3821



TEST NUMBER: P580581
 CATALOG NUMBER: HCC4S40D010MW-HM43040835-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	383.1	9.6
10°-20°	981.4	24.5
20°-30°	1223.9	30.5
30°-40°	901.5	22.5
40°-50°	370.8	9.3
50°-60°	108.4	2.7
60°-70°	27.8	0.7
70°-80°	8.6	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2588.3	64.6
0°-40°	3489.8	87.1
0°-60°	3968.9	99.0
0°-90°	4007.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4007.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4206	
5°	4102	383
15°	3511	981
25°	2690	1224
35°	1436	902
45°	458	371
55°	109	108
65°	27	28
75°	8	9
85°	3	2
90°	0	



TEST NUMBER: P580581
CATALOG NUMBER: HCC4S40D010MW-HM43040835-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4205.9
2.5°	4162.3
5°	4102.3
7.5°	3993.2
10°	3832.4
12.5°	3674.3
15°	3510.7
17.5°	3328.1
20°	3123.7
22.5°	2911.1
25°	2690.3
27.5°	2445.0
30°	2158.8
32.5°	1812.7
35°	1436.4
37.5°	1104.0
40°	828.6
42.5°	613.3
45°	457.9
47.5°	338.0
50°	245.3
52.5°	169.0
55°	109.1
57.5°	65.5
60°	49.1
62.5°	35.4
65°	27.2
67.5°	19.1
70°	13.7
72.5°	10.9
75°	8.2
77.5°	5.5
80°	2.7
82.5°	2.7
85°	2.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)