

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592808

Luminaire Tested: **HCC4W40D010MW-HM43040850-41WDC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592808  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W40D010MW-HM43040850-41WDC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4840.1 lumens  
Efficiency: N/A  
Efficacy: 118.1 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592808  
CATALOG NUMBER: HCC4W40D010MW-HM43040850-41WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P592808

CATALOG NUMBER: HCC4W40D010MW-HM43040850-41WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77	77	77	77
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51	51	51	51
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47	47	47	47
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	391006
5°	396746
10°	409187
15°	437234
20°	463301
25°	458224
30°	411273
35°	320097
40°	216857
45°	135381
50°	58565
55°	19612
60°	4934
65°	3327
70°	2056
75°	1334
80°	1989
85°	0



TEST NUMBER: P592808  
 CATALOG NUMBER: HCC4W40D010MW-HM43040850-41WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	307.8	6.4
10°-20°	972.0	20.1
20°-30°	1522.9	31.5
30°-40°	1314.4	27.2
40°-50°	604.4	12.5
50°-60°	102.6	2.1
60°-70°	11.6	0.2
70°-80°	4.1	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2802.7	57.9
0°-40°	4117.0	85.1
0°-60°	4824.1	99.7
0°-90°	4840.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4840.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3170	
5°	3204	308
15°	3424	972
25°	3367	1523
35°	2126	1314
45°	776	604
55°	91	103
65°	11	12
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P592808  
CATALOG NUMBER: HCC4W40D010MW-HM43040850-41WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3170.0
2.5°	3170.0
5°	3204.3
7.5°	3235.7
10°	3267.0
12.5°	3332.6
15°	3424.0
17.5°	3501.0
20°	3529.6
22.5°	3486.8
25°	3366.9
27.5°	3172.9
30°	2887.6
32.5°	2528.0
35°	2125.8
37.5°	1720.5
40°	1346.8
42.5°	1030.1
45°	776.1
47.5°	545.0
50°	305.2
52.5°	168.4
55°	91.2
57.5°	45.6
60°	20.0
62.5°	14.2
65°	11.4
67.5°	8.5
70°	5.7
72.5°	5.7
75°	2.8
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)