

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580631

Luminaire Tested: **HCC4W40D010MW-HM43040927-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010MW-HM43040927-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3295.8 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580631
CATALOG NUMBER: HCC4W40D010MW-HM43040927-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P580631

CATALOG NUMBER: HCC4W40D010MW-HM43040927-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	227634	227634	227634
5°	237654	226634	216135
10°	243658	221903	202602
15°	248702	215986	187982
20°	247376	205490	172150
25°	236999	190005	156607
30°	218939	173491	141943
35°	191911	154312	128488
40°	167103	136349	115722
45°	145446	118931	103406
50°	129584	102509	91245
55°	115781	90104	78901
60°	103364	78719	68037
65°	91878	69054	64647
70°	80639	59505	60263
75°	68293	50707	55902
80°	52493	43187	50859
85°	30711	33824	43023



TEST NUMBER: P580631
 CATALOG NUMBER: HCC4W40D010MW-HM43040927-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.0	5.2
10°-20°	477.2	14.5
20°-30°	651.9	19.8
30°-40°	654.6	19.9
40°-50°	541.6	16.4
50°-60°	392.5	11.9
60°-70°	248.6	7.5
70°-80°	125.7	3.8
80°-90°	30.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1302.1	39.5
0°-40°	1956.7	59.4
0°-60°	2890.8	87.7
0°-90°	3295.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3295.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1846	1846	1846	1846	1846	
5°	1919	1891	1830	1770	1746	184
15°	1948	1872	1691	1535	1472	548
25°	1741	1626	1396	1220	1151	796
35°	1274	1199	1025	899	853	799
45°	834	786	682	614	593	648
55°	538	491	419	382	367	484
65°	315	280	237	213	222	313
75°	143	124	106	111	117	153
85°	22	22	24	28	30	30
90°	0	0	0	0	0	



TEST NUMBER: P580631

CATALOG NUMBER: HCC4W40D010MW-HM43040927-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1845.5	1845.5	1845.5	1845.5	1845.5	1845.5	1845.5	1845.5	1845.5
2.5°	1880.3	1873.8	1862.9	1849.9	1834.7	1817.4	1802.1	1793.5	1789.1
5°	1919.4	1910.6	1891.1	1862.9	1830.4	1797.7	1769.6	1752.2	1745.6
7.5°	1943.3	1930.2	1902.0	1858.6	1808.6	1760.9	1719.6	1695.7	1689.2
10°	1945.4	1930.2	1893.4	1834.7	1771.7	1708.7	1658.9	1624.1	1617.6
12.5°	1947.6	1928.0	1882.5	1813.0	1734.9	1656.6	1595.9	1554.6	1543.7
15°	1947.6	1928.0	1871.6	1789.1	1691.4	1602.4	1535.1	1487.3	1472.1
17.5°	1930.2	1908.5	1841.2	1745.6	1639.2	1539.4	1461.2	1411.3	1396.1
20°	1884.6	1860.7	1784.7	1680.5	1565.5	1461.2	1383.1	1331.0	1311.5
22.5°	1819.5	1791.2	1711.0	1598.0	1483.0	1376.6	1300.6	1246.3	1229.0
25°	1741.4	1713.1	1626.2	1515.5	1396.1	1296.2	1220.2	1170.3	1150.7
27.5°	1645.7	1615.4	1530.7	1420.0	1309.2	1209.3	1139.9	1094.3	1074.8
30°	1537.2	1504.7	1424.3	1318.0	1218.1	1122.6	1055.2	1018.3	996.6
32.5°	1411.3	1383.1	1311.5	1215.8	1122.6	1031.3	974.9	942.3	924.9
35°	1274.5	1259.3	1198.6	1116.1	1024.8	948.8	898.9	868.4	853.3
37.5°	1152.9	1137.7	1085.6	1016.2	935.8	866.3	825.1	799.0	785.9
40°	1037.8	1024.8	974.9	916.3	846.8	785.9	751.3	731.7	718.7
42.5°	924.9	918.4	877.2	822.9	762.1	710.0	681.8	666.5	655.7
45°	833.8	825.1	785.9	733.9	681.8	638.3	614.4	603.7	592.8
47.5°	753.4	742.6	701.3	655.7	607.9	568.9	547.2	536.3	531.9
50°	675.3	664.4	627.5	581.9	534.2	505.9	488.5	477.7	475.5
52.5°	605.8	594.9	553.7	510.3	473.3	449.4	434.3	423.4	419.0
55°	538.4	525.4	490.7	449.4	419.0	397.3	382.1	371.3	366.9
57.5°	477.7	464.7	434.3	395.2	366.9	347.4	334.4	323.5	319.1
60°	419.0	408.2	380.0	343.0	319.1	301.8	288.8	280.1	275.8
62.5°	364.8	356.0	327.9	295.3	275.8	260.5	249.6	241.0	245.4
65°	314.8	306.1	280.1	251.9	236.6	221.5	212.8	212.8	221.5
67.5°	267.0	258.4	236.6	212.8	199.8	188.9	182.4	188.9	195.4
70°	223.6	215.0	195.4	175.9	165.0	156.4	156.4	162.9	167.1
72.5°	182.4	173.6	158.5	143.3	134.6	128.1	134.6	139.0	143.3
75°	143.3	136.8	123.8	112.9	106.4	104.3	110.8	115.1	117.3
77.5°	106.4	102.0	93.4	84.6	80.4	82.5	89.0	91.1	93.4
80°	73.9	71.6	65.1	60.8	60.8	63.0	67.3	69.5	71.6
82.5°	45.6	45.6	41.3	39.1	41.3	45.6	47.8	49.9	49.9
85°	21.7	23.9	21.7	21.7	23.9	28.2	28.2	30.4	30.4
87.5°	6.5	6.5	8.6	8.6	10.9	10.9	10.9	10.9	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)