

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580649

Luminaire Tested: **HCC4S40D010BZ-HM43040930-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010BZ-HM43040930-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3537.2 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580649
CATALOG NUMBER: HCC4S40D010BZ-HM43040930-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580649

CATALOG NUMBER: HCC4S40D010BZ-HM43040930-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87																			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76																			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66																			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																			
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	244311	244311	244311
5°	255050	243226	231971
10°	261519	238172	217444
15°	266912	231795	201748
20°	265503	220546	184751
25°	254351	203914	168080
30°	234991	186195	152326
35°	205960	165620	137884
40°	179340	146332	124208
45°	156086	127636	110977
50°	139064	110012	97922
55°	124275	96706	84685
60°	110937	84516	72996
65°	98620	74133	69375
70°	86553	63869	64735
75°	73297	54424	60000
80°	56328	46313	54624
85°	32975	36371	46137



TEST NUMBER: P580649

CATALOG NUMBER: HCC4S40D010BZ-HM43040930-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.7	5.2
10°-20°	512.1	14.5
20°-30°	699.7	19.8
30°-40°	702.6	19.9
40°-50°	581.2	16.4
50°-60°	421.2	11.9
60°-70°	266.8	7.5
70°-80°	134.9	3.8
80°-90°	33.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1397.5	39.5
0°-40°	2100.1	59.4
0°-60°	3102.5	87.7
0°-90°	3537.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3537.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1981	1981	1981	1981	1981	
5°	2060	2030	1964	1899	1874	197
15°	2090	2009	1815	1648	1580	588
25°	1869	1745	1498	1310	1235	854
35°	1368	1286	1100	965	916	857
45°	895	844	732	660	636	696
55°	578	527	450	410	394	520
65°	338	301	254	228	238	336
75°	154	133	114	119	126	164
85°	23	23	26	30	33	32
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580649

CATALOG NUMBER: HCC4S40D010BZ-HM43040930-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1980.7	1980.7	1980.7	1980.7	1980.7	1980.7	1980.7	1980.7	1980.7
2.5°	2018.0	2011.1	1999.4	1985.4	1969.0	1950.4	1934.2	1924.8	1920.2
5°	2059.9	2050.6	2029.7	1999.4	1964.4	1929.5	1899.2	1880.5	1873.5
7.5°	2085.6	2071.6	2041.3	1994.7	1941.1	1889.9	1845.6	1819.9	1813.0
10°	2088.0	2071.6	2032.0	1969.0	1901.6	1834.0	1780.4	1743.0	1736.1
12.5°	2090.2	2069.3	2020.4	1945.8	1861.9	1778.0	1712.8	1668.5	1656.8
15°	2090.2	2069.3	2008.7	1920.2	1815.2	1719.7	1647.5	1596.2	1579.9
17.5°	2071.6	2048.3	1976.1	1873.5	1759.4	1652.1	1568.3	1514.7	1498.3
20°	2022.7	1997.1	1915.5	1803.6	1680.2	1568.3	1484.4	1428.5	1407.5
22.5°	1952.8	1922.5	1836.3	1715.1	1591.6	1477.4	1395.9	1337.6	1319.0
25°	1868.9	1838.6	1745.4	1626.6	1498.3	1391.2	1309.7	1256.0	1235.0
27.5°	1766.4	1733.7	1642.8	1524.0	1405.2	1298.0	1223.3	1174.5	1153.5
30°	1649.9	1614.9	1528.7	1414.5	1307.3	1204.7	1132.5	1092.9	1069.5
32.5°	1514.7	1484.4	1407.5	1305.0	1204.7	1106.9	1046.3	1011.4	992.6
35°	1367.8	1351.6	1286.3	1197.8	1099.9	1018.3	964.7	932.1	915.7
37.5°	1237.4	1221.1	1165.2	1090.6	1004.3	929.8	885.5	857.6	843.6
40°	1113.8	1099.9	1046.3	983.3	908.8	843.6	806.2	785.3	771.4
42.5°	992.6	985.7	941.4	883.1	817.9	761.9	731.7	715.4	703.8
45°	894.8	885.5	843.6	787.6	731.7	685.2	659.5	647.8	636.2
47.5°	808.6	796.9	752.6	703.8	652.4	610.5	587.2	575.6	570.9
50°	724.7	713.1	673.5	624.5	573.3	542.9	524.3	512.6	510.3
52.5°	650.2	638.5	594.2	547.6	508.0	482.4	466.0	454.5	449.7
55°	577.9	564.0	526.6	482.4	449.7	426.4	410.2	398.5	393.8
57.5°	512.6	498.7	466.0	424.1	393.8	372.8	358.8	347.2	342.6
60°	449.7	438.1	407.8	368.1	342.6	323.9	310.0	300.7	295.9
62.5°	391.5	382.1	351.9	316.9	295.9	279.6	268.0	258.6	263.3
65°	337.9	328.6	300.7	270.3	254.0	237.7	228.3	228.3	237.7
67.5°	286.6	277.3	254.0	228.3	214.3	202.8	195.7	202.8	209.7
70°	240.0	230.7	209.7	188.8	177.1	167.8	167.8	174.8	179.5
72.5°	195.7	186.4	170.1	153.8	144.5	137.4	144.5	149.1	153.8
75°	153.8	146.9	132.8	121.2	114.2	111.9	118.8	123.5	125.9
77.5°	114.2	109.5	100.2	90.9	86.2	88.6	95.5	97.9	100.2
80°	79.3	76.9	70.0	65.2	65.2	67.6	72.2	74.5	76.9
82.5°	49.0	49.0	44.3	41.9	44.3	49.0	51.2	53.6	53.6
85°	23.3	25.7	23.3	23.3	25.7	30.3	30.3	32.6	32.6
87.5°	7.0	7.0	9.3	9.3	11.7	11.7	11.7	11.7	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)