

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580648

Luminaire Tested: **HCC4W40D010MW-HM43040930-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010MW-HM43040930-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2828.9 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580648
CATALOG NUMBER: HCC4W40D010MW-HM43040930-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580648

CATALOG NUMBER: HCC4W40D010MW-HM43040930-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78																			
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61																			
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55																			
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49																			
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44																			
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40																			
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37																			
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	202003	202003	202003
5°	214030	201326	191235
10°	222917	198118	180020
15°	231438	193358	169275
20°	233620	184081	156556
25°	226057	170257	143310
30°	211362	154277	130392
35°	188372	137146	117164
40°	164671	119281	104274
45°	143457	101191	90201
50°	125171	85833	77332
55°	109717	71137	62622
60°	95963	57454	45983
65°	83618	42816	25859
70°	73101	27733	8403
75°	59953	14440	2240
80°	44679	6606	1705
85°	26323	3397	3397



TEST NUMBER: P580648
 CATALOG NUMBER: HCC4W40D010MW-HM43040930-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.6	5.5
10°-20°	432.6	15.3
20°-30°	598.1	21.1
30°-40°	601.4	21.3
40°-50°	485.3	17.2
50°-60°	328.2	11.6
60°-70°	167.0	5.9
70°-80°	53.5	1.9
80°-90°	8.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1185.3	41.9
0°-40°	1786.7	63.2
0°-60°	2600.2	91.9
0°-90°	2828.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2828.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1638	1638	1638	1638	1638	
5°	1729	1696	1626	1568	1544	167
15°	1812	1715	1514	1370	1326	510
25°	1661	1517	1251	1097	1053	760
35°	1251	1130	911	797	778	782
45°	822	736	580	517	517	637
55°	510	440	331	289	291	458
65°	286	233	147	96	89	287
75°	126	89	30	7	5	136
85°	19	9	2	2	2	25
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580648

CATALOG NUMBER: HCC4W40D010MW-HM43040930-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7	1637.7
2.5°	1681.9	1672.6	1663.3	1647.0	1628.4	1609.8	1598.1	1588.8	1584.1
5°	1728.6	1716.9	1696.0	1661.0	1626.0	1593.4	1567.8	1551.5	1544.5
7.5°	1765.8	1749.5	1714.6	1665.7	1612.1	1560.8	1528.3	1504.9	1495.6
10°	1779.8	1761.2	1714.6	1649.3	1581.8	1518.8	1472.3	1449.0	1437.3
12.5°	1796.1	1775.1	1716.9	1635.3	1551.5	1476.9	1423.3	1393.1	1381.4
15°	1812.4	1784.4	1714.6	1614.4	1514.2	1428.0	1369.7	1339.5	1325.6
17.5°	1812.4	1779.8	1696.0	1579.5	1465.3	1374.5	1309.2	1274.2	1262.6
20°	1779.8	1742.5	1651.7	1523.6	1402.4	1304.6	1241.6	1206.8	1192.7
22.5°	1728.6	1686.7	1588.8	1456.0	1327.8	1232.3	1169.4	1136.8	1122.9
25°	1661.0	1619.1	1516.6	1379.2	1251.0	1155.5	1097.2	1067.0	1053.0
27.5°	1581.8	1535.2	1432.8	1295.2	1169.4	1078.6	1025.0	997.0	985.4
30°	1484.0	1439.7	1339.5	1204.4	1083.2	999.4	950.5	924.8	915.5
32.5°	1369.7	1332.5	1234.7	1108.9	994.8	917.9	873.6	852.6	843.3
35°	1251.0	1216.1	1129.9	1013.4	910.8	838.6	796.7	782.8	778.1
37.5°	1139.2	1108.9	1025.0	917.9	824.7	761.7	724.5	715.2	710.5
40°	1022.7	1001.7	924.8	827.0	740.8	684.9	654.7	647.6	647.6
42.5°	917.9	894.6	827.0	738.5	661.6	605.7	584.7	577.8	580.1
45°	822.4	799.0	736.2	654.7	580.1	533.5	517.1	517.1	517.1
47.5°	733.8	712.8	654.7	570.7	510.2	472.9	456.6	456.6	458.9
50°	652.3	638.3	573.1	500.9	447.3	412.3	400.6	398.4	403.0
52.5°	575.4	559.2	500.9	435.6	384.4	356.5	344.8	342.5	344.8
55°	510.2	491.6	440.3	377.4	330.8	302.9	288.9	286.5	291.2
57.5°	447.3	433.3	379.7	323.9	279.6	251.6	239.9	235.3	237.7
60°	389.0	375.1	326.1	272.5	232.9	205.0	188.7	184.1	186.4
62.5°	335.5	323.9	277.2	226.0	186.4	160.8	144.4	132.8	137.4
65°	286.5	274.9	232.9	181.7	146.7	118.8	95.5	86.2	88.6
67.5°	244.6	230.6	191.0	144.4	109.5	79.3	53.6	48.9	48.9
70°	202.7	188.7	153.8	111.9	76.9	41.9	23.3	23.3	23.3
72.5°	163.1	151.4	118.8	83.9	48.9	18.6	9.3	9.3	9.3
75°	125.8	116.5	88.6	58.3	30.3	9.3	7.0	4.7	4.7
77.5°	93.2	83.9	62.9	39.6	18.6	4.7	4.7	4.7	4.7
80°	62.9	55.9	41.9	23.3	9.3	2.4	2.4	2.4	2.4
82.5°	37.3	32.6	23.3	11.7	4.7	2.4	2.4	2.4	2.4
85°	18.6	14.0	9.3	4.7	2.4	2.4	2.4	2.4	2.4
87.5°	4.7	2.4	2.4	2.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)