

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580667

Luminaire Tested: **HCC4W40D010MB-HM43040935-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010MB-HM43040935-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3689.4 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580667
CATALOG NUMBER: HCC4W40D010MB-HM43040935-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P580667

CATALOG NUMBER: HCC4W40D010MB-HM43040935-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	254832	254832	254832
5°	266033	253701	241950
10°	272766	248405	226800
15°	278405	241781	210432
20°	276923	230036	192705
25°	265294	212692	175306
30°	245089	194214	158892
35°	214829	172742	143831
40°	187069	152627	129538
45°	162802	133130	115739
50°	145051	114732	102144
55°	129630	100878	88320
60°	115723	88143	76154
65°	102852	77314	72381
70°	90268	66610	67512
75°	76442	56760	62574
80°	58672	48302	57039
85°	34390	37928	48259



TEST NUMBER: P580667
 CATALOG NUMBER: HCC4W40D010MB-HM43040935-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	5.2
10°-20°	534.2	14.5
20°-30°	729.8	19.8
30°-40°	732.8	19.9
40°-50°	606.2	16.4
50°-60°	439.3	11.9
60°-70°	278.3	7.5
70°-80°	140.7	3.8
80°-90°	34.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1457.6	39.5
0°-40°	2190.4	59.4
0°-60°	3236.0	87.7
0°-90°	3689.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3689.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2066	2066	2066	2066	2066	
5°	2149	2117	2049	1981	1954	206
15°	2180	2095	1893	1718	1648	613
25°	1949	1820	1563	1366	1288	891
35°	1427	1342	1147	1006	955	894
45°	933	880	763	688	664	726
55°	603	549	469	428	411	542
65°	352	314	265	238	248	351
75°	160	139	119	124	131	171
85°	24	24	27	32	34	34
90°	0	0	0	0	0	



TEST NUMBER: P580667

CATALOG NUMBER: HCC4W40D010MB-HM43040935-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2066.0	2066.0	2066.0	2066.0	2066.0	2066.0	2066.0	2066.0	2066.0
2.5°	2104.8	2097.5	2085.4	2070.8	2053.8	2034.4	2017.4	2007.6	2002.8
5°	2148.6	2138.9	2117.0	2085.4	2049.0	2012.5	1980.9	1961.4	1954.1
7.5°	2175.3	2160.7	2129.1	2080.6	2024.6	1971.2	1925.0	1898.3	1890.9
10°	2177.8	2160.7	2119.5	2053.8	1983.3	1912.9	1856.9	1818.0	1810.8
12.5°	2180.2	2158.3	2107.3	2029.5	1942.0	1854.5	1786.4	1740.2	1728.1
15°	2180.2	2158.3	2095.1	2002.8	1893.4	1793.7	1718.4	1664.9	1647.9
17.5°	2160.7	2136.4	2061.1	1954.1	1835.1	1723.2	1635.8	1579.8	1562.8
20°	2109.7	2082.9	1997.8	1881.3	1752.5	1635.8	1548.2	1489.9	1468.1
22.5°	2036.7	2005.2	1915.2	1788.9	1660.1	1540.9	1455.8	1395.1	1375.7
25°	1949.3	1917.7	1820.5	1696.5	1562.8	1451.0	1365.9	1310.1	1288.1
27.5°	1842.4	1808.3	1713.6	1589.6	1465.6	1353.8	1276.0	1225.0	1203.2
30°	1720.8	1684.4	1594.4	1475.3	1363.6	1256.6	1181.2	1139.9	1115.6
32.5°	1579.8	1548.2	1468.1	1361.1	1256.6	1154.5	1091.3	1054.9	1035.4
35°	1426.7	1409.7	1341.6	1249.2	1147.2	1062.1	1006.2	972.2	955.2
37.5°	1290.6	1273.6	1215.3	1137.5	1047.6	969.8	923.6	894.4	879.9
40°	1161.8	1147.2	1091.3	1025.7	947.9	879.9	841.0	819.1	804.5
42.5°	1035.4	1028.1	981.9	921.1	853.1	794.8	763.2	746.1	734.0
45°	933.3	923.6	879.9	821.5	763.2	714.5	687.8	675.7	663.5
47.5°	843.4	831.2	785.0	734.0	680.6	636.8	612.5	600.3	595.5
50°	755.9	743.8	702.4	651.4	597.9	566.3	546.8	534.7	532.3
52.5°	678.1	666.0	619.8	571.1	529.9	503.1	486.1	474.0	469.1
55°	602.8	588.2	549.3	503.1	469.1	444.8	427.8	415.7	410.7
57.5°	534.7	520.1	486.1	442.3	410.7	388.9	374.3	362.2	357.3
60°	469.1	456.9	425.3	384.1	357.3	337.9	323.3	313.5	308.7
62.5°	408.4	398.6	367.0	330.6	308.7	291.7	279.5	269.8	274.6
65°	352.4	342.7	313.5	281.9	264.9	248.0	238.2	238.2	248.0
67.5°	299.0	289.2	264.9	238.2	223.6	211.4	204.1	211.4	218.7
70°	250.3	240.7	218.7	196.8	184.7	175.0	175.0	182.3	187.2
72.5°	204.1	194.5	177.5	160.4	150.7	143.4	150.7	155.6	160.4
75°	160.4	153.1	138.6	126.3	119.1	116.7	124.0	128.8	131.3
77.5°	119.1	114.2	104.5	94.8	89.9	92.4	99.7	102.1	104.5
80°	82.6	80.3	72.9	68.0	68.0	70.5	75.3	77.8	80.3
82.5°	51.0	51.0	46.2	43.7	46.2	51.0	53.5	55.9	55.9
85°	24.3	26.8	24.3	24.3	26.8	31.6	31.6	34.1	34.1
87.5°	7.3	7.3	9.8	9.8	12.1	12.1	12.1	12.1	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)