

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580664

Luminaire Tested: **HCC4S40D010SL-HM43040935-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S40D010SL-HM43040935-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3747.7 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580664
CATALOG NUMBER: HCC4S40D010SL-HM43040935-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580664

CATALOG NUMBER: HCC4S40D010SL-HM43040935-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	221825	221825	221825
5°	230807	223886	221483
10°	238348	225873	221001
15°	246736	226547	220967
20°	247560	221071	218196
25°	238809	210038	211685
30°	222229	195567	201107
35°	200177	178961	185541
40°	176490	162787	170226
45°	154324	146684	153888
50°	136646	131964	138987
55°	120190	116555	121265
60°	107335	99515	102525
65°	94329	80875	79444
70°	82406	59577	54348
75°	68340	35886	28976
80°	51782	13780	8595
85°	24059	3538	3538



TEST NUMBER: P580664

CATALOG NUMBER: HCC4S40D010SL-HM43040935-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.5	4.6
10°-20°	506.2	13.5
20°-30°	733.1	19.6
30°-40°	773.5	20.6
40°-50°	669.4	17.9
50°-60°	495.9	13.2
60°-70°	285.8	7.6
70°-80°	99.8	2.7
80°-90°	10.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1412.8	37.7
0°-40°	2186.3	58.3
0°-60°	3351.5	89.4
0°-90°	3747.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3747.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1798	1798	1798	1798	1798	
5°	1864	1840	1808	1794	1789	179
15°	1932	1869	1774	1733	1730	543
25°	1755	1667	1543	1534	1555	803
35°	1329	1269	1188	1215	1232	830
45°	885	860	841	872	882	687
55°	559	547	542	561	564	504
65°	323	304	277	262	272	323
75°	143	122	75	61	61	154
85°	17	10	2	2	2	26
90°	0	0	0	0	0	



TEST NUMBER: P580664

CATALOG NUMBER: HCC4S40D010SL-HM43040935-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1798.4	1798.4	1798.4	1798.4	1798.4	1798.4	1798.4	1798.4	1798.4
2.5°	1825.2	1820.3	1813.0	1803.4	1793.6	1786.3	1783.8	1781.5	1781.5
5°	1864.1	1854.4	1839.8	1820.3	1808.2	1800.9	1793.6	1788.8	1788.8
7.5°	1890.8	1881.0	1859.2	1832.5	1815.5	1800.9	1791.1	1783.8	1783.8
10°	1903.0	1890.8	1864.1	1830.0	1803.4	1783.8	1769.3	1764.5	1764.5
12.5°	1917.6	1903.0	1866.5	1822.7	1788.8	1764.5	1749.9	1744.9	1744.9
15°	1932.2	1915.1	1868.9	1817.9	1774.1	1744.9	1732.8	1730.4	1730.4
17.5°	1924.9	1903.0	1849.5	1788.8	1740.1	1711.0	1698.8	1698.8	1701.2
20°	1886.0	1864.1	1803.4	1735.3	1684.2	1662.3	1652.6	1657.5	1662.3
22.5°	1827.6	1800.9	1735.3	1669.6	1616.1	1596.8	1596.8	1604.0	1611.3
25°	1754.7	1730.4	1667.3	1594.3	1543.3	1528.7	1533.5	1545.7	1555.4
27.5°	1672.1	1645.3	1579.7	1511.7	1460.7	1453.4	1465.5	1482.5	1487.3
30°	1560.3	1538.5	1482.5	1416.8	1373.1	1370.8	1387.7	1399.9	1412.0
32.5°	1453.4	1429.1	1375.6	1312.4	1280.7	1283.2	1302.7	1317.3	1324.6
35°	1329.4	1307.5	1268.6	1217.6	1188.5	1193.3	1215.2	1229.7	1232.2
37.5°	1212.7	1198.1	1159.2	1120.4	1098.5	1108.2	1127.7	1144.7	1144.7
40°	1096.1	1083.9	1054.7	1023.1	1011.0	1023.1	1042.6	1057.2	1057.2
42.5°	984.2	977.0	952.7	930.8	923.5	940.5	957.6	969.7	967.3
45°	884.7	877.4	860.4	843.3	840.9	857.9	872.5	879.8	882.2
47.5°	794.7	789.9	775.3	763.2	763.2	780.1	792.3	799.6	802.0
50°	712.1	707.2	695.1	685.4	687.7	704.8	714.5	721.8	724.3
52.5°	629.4	627.0	617.3	605.1	612.4	624.6	636.7	641.7	644.0
55°	558.9	558.9	546.8	537.1	542.0	554.1	561.4	563.9	563.9
57.5°	495.8	493.4	478.8	469.0	471.5	483.6	488.5	490.9	490.9
60°	435.1	432.6	418.0	403.4	403.4	410.7	413.2	415.6	415.6
62.5°	376.7	374.3	357.3	345.2	340.2	337.9	337.9	342.7	352.4
65°	323.2	320.8	303.8	284.4	277.1	269.7	262.4	267.4	272.2
67.5°	274.6	269.7	252.8	235.7	218.7	206.6	194.4	201.7	211.4
70°	228.5	223.6	204.1	184.7	165.2	145.8	136.1	145.8	150.7
72.5°	184.7	179.8	160.4	140.9	116.7	97.2	94.8	97.2	99.7
75°	143.4	140.9	121.5	99.7	75.3	60.8	60.8	60.8	60.8
77.5°	106.9	102.1	82.6	63.2	43.7	34.1	31.6	31.6	31.6
80°	72.9	68.0	51.0	36.4	19.4	14.6	14.6	12.1	12.1
82.5°	41.4	38.9	26.7	14.6	7.3	4.8	4.8	4.8	4.8
85°	17.0	14.6	9.8	4.8	2.5	2.5	2.5	2.5	2.5
87.5°	2.5	2.5	2.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)