

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580678

Luminaire Tested: **HCC4S40D010MW-HM43040940-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580678  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S40D010MW-HM43040940-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3507.1 lumens  
Efficiency: N/A  
Efficacy: 85.5 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580678  
CATALOG NUMBER: HCC4S40D010MW-HM43040940-41MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P580678

CATALOG NUMBER: HCC4S40D010MW-HM43040940-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79					79			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70					70			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63					63			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57					57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52					52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47					47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44					44			
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40					40			
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37					37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	297325
5°	295749
10°	290338
15°	284240
20°	272066
25°	253004
30°	223924
35°	176732
40°	132259
45°	101714
50°	82533
55°	68471
60°	60538
65°	56008
70°	51716
75°	47514
80°	43187
85°	34390



TEST NUMBER: P580678  
 CATALOG NUMBER: HCC4S40D010MW-HM43040940-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	225.8	6.4
10°-20°	624.2	17.8
20°-30°	847.6	24.2
30°-40°	734.2	20.9
40°-50°	460.9	13.1
50°-60°	290.0	8.3
60°-70°	190.5	5.4
70°-80°	105.1	3.0
80°-90°	28.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1697.6	48.4
0°-40°	2431.8	69.3
0°-60°	3182.7	90.8
0°-90°	3507.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3507.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2410	
5°	2389	226
15°	2226	624
25°	1859	848
35°	1174	734
45°	583	461
55°	318	290
65°	192	190
75°	100	105
85°	24	29
90°	0	



TEST NUMBER: P580678  
CATALOG NUMBER: HCC4S40D010MW-HM43040940-41MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2410.5
2.5°	2395.9
5°	2388.6
7.5°	2364.3
10°	2318.1
12.5°	2272.0
15°	2225.9
17.5°	2162.6
20°	2072.7
22.5°	1970.7
25°	1859.0
27.5°	1730.2
30°	1572.2
32.5°	1380.2
35°	1173.7
37.5°	984.1
40°	821.4
42.5°	692.6
45°	583.1
47.5°	500.5
50°	430.1
52.5°	369.4
55°	318.4
57.5°	274.5
60°	245.4
62.5°	218.7
65°	191.9
67.5°	165.2
70°	143.4
72.5°	119.1
75°	99.7
77.5°	77.8
80°	60.8
82.5°	41.4
85°	24.3
87.5°	9.8
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)