

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580685

Luminaire Tested: **HCC4W40D010BZ-HM43040940-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W40D010BZ-HM43040940-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3686.8 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580685
CATALOG NUMBER: HCC4W40D010BZ-HM43040940-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580685

CATALOG NUMBER: HCC4W40D010BZ-HM43040940-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	254635	254635	254635
5°	265847	253515	241789
10°	272566	248230	226637
15°	278213	241602	210278
20°	276726	229865	192574
25°	265089	212556	175184
30°	244918	194071	158778
35°	214678	172622	143726
40°	186940	152515	129457
45°	162697	133026	115669
50°	144936	114655	102067
55°	129523	100814	88277
60°	115649	88069	76104
65°	102793	77285	72294
70°	90232	66574	67439
75°	76394	56760	62526
80°	58672	48302	56968
85°	34390	37787	48118



TEST NUMBER: P580685
 CATALOG NUMBER: HCC4W40D010BZ-HM43040940-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.5	5.2
10°-20°	533.8	14.5
20°-30°	729.3	19.8
30°-40°	732.3	19.9
40°-50°	605.8	16.4
50°-60°	439.0	11.9
60°-70°	278.1	7.5
70°-80°	140.6	3.8
80°-90°	34.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.6	39.5
0°-40°	2188.9	59.4
0°-60°	3233.7	87.7
0°-90°	3686.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3686.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2064	2064	2064	2064	2064	
5°	2147	2115	2048	1980	1953	206
15°	2179	2094	1892	1717	1647	613
25°	1948	1819	1562	1365	1287	890
35°	1426	1341	1146	1006	954	894
45°	933	879	763	687	663	725
55°	602	549	469	427	410	542
65°	352	313	265	238	248	351
75°	160	138	119	124	131	171
85°	24	24	27	32	34	34
90°	0	0	0	0	0	



TEST NUMBER: P580685

CATALOG NUMBER: HCC4W40D010BZ-HM43040940-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	2064.4	2064.4	2064.4	2064.4	2064.4	2064.4	2064.4	2064.4	2064.4
2.5°	2103.3	2096.0	2083.9	2069.4	2052.3	2032.9	2015.9	2006.1	2001.3
5°	2147.1	2137.3	2115.4	2083.9	2047.5	2011.1	1979.5	1960.1	1952.8
7.5°	2173.7	2159.2	2127.7	2079.0	2023.2	1969.7	1923.6	1896.8	1889.6
10°	2176.2	2159.2	2117.9	2052.3	1981.9	1911.4	1855.6	1816.8	1809.5
12.5°	2178.7	2156.8	2105.8	2028.0	1940.6	1853.1	1785.2	1739.0	1726.9
15°	2178.7	2156.8	2093.6	2001.3	1892.0	1792.5	1717.1	1663.8	1646.7
17.5°	2159.2	2134.9	2059.6	1952.8	1833.7	1722.1	1634.6	1578.7	1561.8
20°	2108.2	2081.5	1996.5	1879.9	1751.2	1634.6	1547.2	1488.9	1467.1
22.5°	2035.3	2003.8	1913.9	1787.7	1658.9	1539.9	1454.8	1394.2	1374.7
25°	1947.8	1916.3	1819.2	1695.3	1561.8	1450.0	1365.0	1309.1	1287.2
27.5°	1841.0	1807.1	1712.3	1588.5	1464.6	1352.8	1275.1	1224.1	1202.3
30°	1719.6	1683.2	1593.3	1474.3	1362.6	1255.7	1180.4	1139.2	1114.8
32.5°	1578.7	1547.2	1467.1	1360.1	1255.7	1153.7	1090.5	1054.1	1034.7
35°	1425.7	1408.8	1340.7	1248.5	1146.4	1061.4	1005.5	971.6	954.5
37.5°	1289.7	1272.7	1214.4	1136.7	1046.8	969.1	922.9	893.8	879.2
40°	1161.0	1146.4	1090.5	1024.9	947.2	879.2	840.4	818.6	804.0
42.5°	1034.7	1027.4	981.2	920.6	852.5	794.2	762.6	745.7	733.5
45°	932.7	922.9	879.2	820.9	762.6	714.1	687.4	675.2	663.1
47.5°	842.8	830.7	784.5	733.5	680.1	636.4	612.1	600.0	595.0
50°	755.3	743.2	702.0	651.0	597.5	565.9	546.5	534.4	531.9
52.5°	677.6	665.5	619.4	570.8	529.4	502.8	485.7	473.6	468.8
55°	602.3	587.7	549.0	502.8	468.8	444.5	427.4	415.3	410.5
57.5°	534.4	519.8	485.7	442.0	410.5	388.7	374.1	361.9	357.0
60°	468.8	456.6	425.1	383.7	357.0	337.6	323.1	313.3	308.5
62.5°	408.0	398.3	366.8	330.4	308.5	291.5	279.4	269.6	274.4
65°	352.2	342.5	313.3	281.7	264.8	247.7	238.0	238.0	247.7
67.5°	298.7	289.0	264.8	238.0	223.4	211.3	204.0	211.3	218.6
70°	250.2	240.5	218.6	196.7	184.6	174.9	174.9	182.2	187.0
72.5°	204.0	194.3	177.3	160.3	150.6	143.3	150.6	155.5	160.3
75°	160.3	153.0	138.4	126.3	119.1	116.6	123.9	128.7	131.2
77.5°	119.1	114.1	104.5	94.7	89.9	92.3	99.5	102.0	104.5
80°	82.6	80.2	72.9	68.0	68.0	70.4	75.3	77.7	80.2
82.5°	51.0	51.0	46.2	43.7	46.2	51.0	53.5	55.8	55.8
85°	24.3	26.7	24.3	24.3	26.7	31.6	31.6	34.0	34.0
87.5°	7.3	7.3	9.8	9.8	12.1	12.1	12.1	12.1	14.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)