

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580991

Luminaire Tested: **HCC4W05D010MW-HM40525827-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010MW-HM40525827-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 606.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580991
CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580991

CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47				47				
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35				35				
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41864	41864	41864
5°	43707	41664	39745
10°	44814	40793	37261
15°	45728	39714	34568
20°	45482	37777	31660
25°	43578	34936	28798
30°	40250	31889	26107
35°	35295	28369	23626
40°	30722	25070	21270
45°	26741	21874	19014
50°	23833	18844	16771
55°	21290	16580	14494
60°	19020	14481	12507
65°	16899	12696	11879
70°	14822	10927	11108
75°	12534	9293	10294
80°	9660	7885	9376
85°	5661	6227	7925



TEST NUMBER: P580991
 CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.8	5.2
10°-20°	87.7	14.5
20°-30°	119.9	19.8
30°-40°	120.4	19.9
40°-50°	99.6	16.4
50°-60°	72.2	11.9
60°-70°	45.7	7.5
70°-80°	23.1	3.8
80°-90°	5.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.4	39.5
0°-40°	359.8	59.4
0°-60°	531.5	87.7
0°-90°	606.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	339	339	339	339	339	
5°	353	348	336	325	321	34
15°	358	344	311	282	271	101
25°	320	299	257	224	212	146
35°	234	220	188	165	157	147
45°	153	144	125	113	109	119
55°	99	90	77	70	67	89
65°	58	52	44	39	41	58
75°	26	23	20	20	22	28
85°	4	4	4	5	6	6
90°	0	0	0	0	0	



TEST NUMBER: P580991

CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	339.4	339.4	339.4	339.4	339.4	339.4	339.4	339.4	339.4
2.5°	345.7	344.6	342.5	340.2	337.3	334.1	331.4	329.7	328.9
5°	353.0	351.3	347.8	342.5	336.5	330.6	325.4	322.2	321.0
7.5°	357.3	354.9	349.7	341.7	332.6	323.8	316.2	311.8	310.6
10°	357.8	354.9	348.1	337.3	325.7	314.2	305.0	298.6	297.5
12.5°	358.1	354.6	346.2	333.3	319.0	304.6	293.4	285.9	283.9
15°	358.1	354.6	344.1	328.9	311.0	294.6	282.3	273.5	270.7
17.5°	354.9	350.9	338.6	321.0	301.5	283.1	268.7	259.5	256.7
20°	346.5	342.2	328.1	309.1	287.8	268.7	254.4	244.7	241.2
22.5°	334.6	329.4	314.6	293.9	272.6	253.1	239.1	229.2	226.0
25°	320.2	315.0	299.1	278.6	256.7	238.4	224.4	215.2	211.6
27.5°	302.6	297.0	281.5	261.0	240.7	222.3	209.6	201.2	197.6
30°	282.6	276.7	262.0	242.3	223.9	206.5	194.1	187.3	183.3
32.5°	259.5	254.4	241.2	223.6	206.5	189.7	179.2	173.3	170.0
35°	234.4	231.5	220.4	205.2	188.4	174.4	165.3	159.7	156.9
37.5°	212.0	209.2	199.6	186.8	172.1	159.2	151.7	146.9	144.5
40°	190.8	188.4	179.2	168.4	155.7	144.5	138.1	134.5	132.1
42.5°	170.0	168.9	161.3	151.3	140.2	130.5	125.4	122.6	120.5
45°	153.3	151.7	144.5	135.0	125.4	117.4	112.9	111.0	109.0
47.5°	138.6	136.5	128.9	120.5	111.8	104.6	100.6	98.6	97.8
50°	124.2	122.1	115.4	107.0	98.2	93.1	89.8	87.8	87.4
52.5°	111.3	109.4	101.8	93.9	87.1	82.6	79.9	77.9	77.1
55°	99.0	96.6	90.2	82.6	77.1	73.1	70.3	68.2	67.4
57.5°	87.8	85.5	79.9	72.6	67.4	63.9	61.5	59.5	58.7
60°	77.1	75.0	69.9	63.1	58.7	55.5	53.1	51.5	50.7
62.5°	67.1	65.5	60.3	54.3	50.7	47.9	46.0	44.3	45.1
65°	57.9	56.3	51.5	46.3	43.5	40.7	39.2	39.2	40.7
67.5°	49.1	47.6	43.5	39.2	36.8	34.7	33.5	34.7	36.0
70°	41.1	39.5	36.0	32.3	30.3	28.7	28.7	30.0	30.8
72.5°	33.5	31.9	29.2	26.3	24.7	23.6	24.7	25.5	26.3
75°	26.3	25.2	22.7	20.8	19.5	19.2	20.3	21.1	21.6
77.5°	19.5	18.7	17.1	15.5	14.8	15.2	16.3	16.8	17.1
80°	13.6	13.2	12.0	11.1	11.1	11.6	12.4	12.8	13.2
82.5°	8.4	8.4	7.6	7.2	7.6	8.4	8.7	9.2	9.2
85°	4.0	4.4	4.0	4.0	4.4	5.2	5.2	5.6	5.6
87.5°	1.2	1.2	1.6	1.6	2.0	2.0	2.0	2.0	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)