

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580987

Luminaire Tested: **HCC4S05D010BZ-HM40525827-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010BZ-HM40525827-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 594.9 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580987
CATALOG NUMBER: HCC4S05D010BZ-HM40525827-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P580987

CATALOG NUMBER: HCC4S05D010BZ-HM40525827-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	47562	47562	47562
5°	47447	47484	47484
10°	46880	46943	46880
15°	46316	46316	46316
20°	44432	44537	44576
25°	41550	41618	41727
30°	37230	37344	37344
35°	30236	30477	30522
40°	22800	22929	23009
45°	17479	17409	17409
50°	14392	14334	14334
55°	12344	12279	12279
60°	11027	10928	10928
65°	10361	10361	10361
70°	9665	9665	9665
75°	8769	8912	8769
80°	8240	7885	8240
85°	6793	6793	6793



TEST NUMBER: P580987
 CATALOG NUMBER: HCC4S05D010BZ-HM40525827-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.3	6.1
10°-20°	101.6	17.1
20°-30°	139.7	23.5
30°-40°	125.6	21.1
40°-50°	79.4	13.3
50°-60°	51.8	8.7
60°-70°	35.1	5.9
70°-80°	19.8	3.3
80°-90°	5.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.7	46.7
0°-40°	403.3	67.8
0°-60°	534.4	89.8
0°-90°	594.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	594.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	386	386	386	386	386	
5°	383	383	384	384	384	36
15°	363	363	363	363	363	102
25°	305	306	306	307	307	139
35°	201	202	202	203	203	125
45°	100	100	100	100	100	79
55°	57	57	57	57	57	52
65°	36	36	36	36	36	35
75°	18	19	19	19	18	20
85°	5	5	5	5	5	6
90°	0	0	0	0	0	



TEST NUMBER: P580987

CATALOG NUMBER: HCC4S05D010BZ-HM40525827-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	385.6	385.6	385.6	385.6	385.6
2.5°	383.5	383.5	383.5	383.5	383.5
5°	383.2	383.2	383.5	383.5	383.5
7.5°	380.3	380.8	380.8	380.8	380.8
10°	374.3	374.3	374.8	374.8	374.3
12.5°	368.8	368.8	368.8	369.2	368.8
15°	362.7	362.7	362.7	362.7	362.7
17.5°	352.4	352.8	352.8	352.8	352.8
20°	338.5	339.3	339.3	339.6	339.6
22.5°	322.5	322.9	323.2	323.7	323.2
25°	305.3	305.8	305.8	306.6	306.6
27.5°	285.3	285.8	286.6	286.6	286.6
30°	261.4	261.8	262.2	262.2	262.2
32.5°	233.1	233.1	233.9	234.3	233.9
35°	200.8	201.6	202.4	203.2	202.7
37.5°	170.0	170.8	171.3	171.3	171.6
40°	141.6	142.4	142.4	143.2	142.9
42.5°	119.3	118.9	118.9	119.7	119.3
45°	100.2	99.8	99.8	99.8	99.8
47.5°	86.3	85.8	85.8	85.8	85.8
50°	75.0	74.7	74.7	74.7	74.7
52.5°	65.8	65.5	65.5	65.5	65.0
55°	57.4	57.4	57.1	57.4	57.1
57.5°	49.9	49.9	49.9	49.9	49.9
60°	44.7	44.3	44.3	44.3	44.3
62.5°	40.0	40.0	40.0	40.0	40.0
65°	35.5	35.5	35.5	35.5	35.5
67.5°	31.1	30.8	31.1	31.1	30.8
70°	26.8	26.3	26.8	26.8	26.8
72.5°	22.4	22.4	22.4	22.7	22.4
75°	18.4	18.7	18.7	18.7	18.4
77.5°	14.8	15.2	14.8	14.8	14.8
80°	11.6	11.1	11.1	11.1	11.6
82.5°	7.9	7.9	7.9	7.9	7.9
85°	4.8	4.8	4.8	4.8	4.8
87.5°	2.0	2.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)