

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580984

Luminaire Tested: **HCC4S05D010MB-HM40525827-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010MB-HM40525827-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 576.5 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580984
CATALOG NUMBER: HCC4S05D010MB-HM40525827-41MDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580984

CATALOG NUMBER: HCC4S05D010MB-HM40525827-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52																			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47																			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44																			
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48870
5°	48610
10°	47720
15°	46724
20°	44721
25°	41578
30°	36803
35°	29061
40°	21737
45°	16729
50°	13567
55°	11247
60°	9942
65°	9223
70°	8511
75°	7768
80°	7103
85°	5661



TEST NUMBER: P580984
 CATALOG NUMBER: HCC4S05D010MB-HM40525827-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.1	6.4
10°-20°	102.6	17.8
20°-30°	139.3	24.2
30°-40°	120.7	20.9
40°-50°	75.8	13.1
50°-60°	47.7	8.3
60°-70°	31.3	5.4
70°-80°	17.2	3.0
80°-90°	4.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.0	48.4
0°-40°	399.7	69.3
0°-60°	523.2	90.8
0°-90°	576.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	396	
5°	393	37
15°	366	103
25°	306	139
35°	193	121
45°	96	76
55°	52	48
65°	32	31
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P580984
CATALOG NUMBER: HCC4S05D010MB-HM40525827-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	396.2
2.5°	393.8
5°	392.6
7.5°	388.6
10°	381.0
12.5°	373.4
15°	365.9
17.5°	355.5
20°	340.7
22.5°	323.9
25°	305.5
27.5°	284.4
30°	258.4
32.5°	226.9
35°	193.0
37.5°	161.7
40°	135.0
42.5°	113.8
45°	95.9
47.5°	82.3
50°	70.7
52.5°	60.7
55°	52.3
57.5°	45.2
60°	40.3
62.5°	36.0
65°	31.6
67.5°	27.1
70°	23.6
72.5°	19.5
75°	16.3
77.5°	12.8
80°	10.0
82.5°	6.8
85°	4.0
87.5°	1.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)