

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580992

Luminaire Tested: **HCC4W05D010MW-HM40525827-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010MW-HM40525827-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 603.2 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580992
CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580992

CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	38360	38360	38360
5°	40352	38309	36873
10°	41745	37863	35207
15°	43034	37173	33699
20°	43080	35638	31765
25°	41455	33317	29778
30°	38512	30650	27802
35°	34512	27601	25734
40°	30287	24619	23798
45°	26462	21805	21944
50°	23372	19074	19784
55°	20601	16924	17763
60°	18428	14974	15566
65°	16344	13192	13192
70°	14245	11216	11216
75°	12153	9531	10675
80°	9660	8524	9660
85°	6227	7359	9057



TEST NUMBER: P580992

CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	4.9
10°-20°	83.0	13.8
20°-30°	116.3	19.3
30°-40°	119.8	19.9
40°-50°	102.0	16.9
50°-60°	75.6	12.5
60°-70°	47.4	7.9
70°-80°	23.5	3.9
80°-90°	6.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.7	37.9
0°-40°	348.5	57.8
0°-60°	526.1	87.2
0°-90°	603.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	311	311	311	311	311	
5°	326	320	309	301	298	31
15°	337	322	291	270	264	95
25°	305	284	245	224	219	139
35°	229	212	183	171	171	143
45°	152	141	125	123	126	118
55°	96	88	79	80	83	87
65°	56	50	45	44	45	56
75°	26	23	20	22	22	27
85°	4	4	5	6	6	6
90°	0	0	0	0	0	



TEST NUMBER: P580992

CATALOG NUMBER: HCC4W05D010MW-HM40525827-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	311.0	311.0	311.0	311.0	311.0	311.0	311.0	311.0	311.0
2.5°	317.8	316.7	315.1	312.2	309.4	307.0	304.6	303.5	303.0
5°	325.9	323.5	320.2	315.1	309.4	304.6	300.7	298.6	297.8
7.5°	331.4	329.0	323.8	315.9	307.8	300.7	294.3	291.5	290.7
10°	333.3	330.6	323.5	312.7	302.3	293.5	286.2	282.7	281.1
12.5°	335.1	331.4	322.2	309.4	296.7	285.9	278.3	273.5	272.3
15°	337.0	333.0	321.8	306.2	291.1	278.3	269.9	265.5	263.9
17.5°	335.1	330.6	317.5	299.9	282.7	268.8	259.6	255.5	253.9
20°	328.2	323.5	308.6	289.9	271.5	257.2	248.0	243.9	242.0
22.5°	317.8	312.7	297.5	277.5	258.8	244.8	236.0	232.0	230.7
25°	304.6	299.4	283.5	263.1	244.8	231.2	223.6	220.0	218.8
27.5°	289.1	283.9	268.3	248.3	230.7	218.0	212.0	208.4	207.6
30°	270.4	265.1	249.9	231.5	215.2	203.3	198.4	195.7	195.2
32.5°	249.6	245.2	231.2	214.4	198.9	188.9	185.2	183.3	182.8
35°	229.2	224.4	212.0	196.8	183.3	174.4	171.3	170.9	170.9
37.5°	208.4	203.6	193.6	179.7	168.1	160.1	158.9	159.4	159.4
40°	188.1	183.6	174.9	163.3	152.9	147.0	146.5	147.3	147.8
42.5°	168.9	165.3	157.3	147.3	138.6	133.8	134.2	135.7	137.0
45°	151.7	148.6	141.3	132.6	125.0	121.3	122.6	124.6	125.8
47.5°	136.2	133.4	126.6	118.6	112.3	109.8	111.5	113.8	115.4
50°	121.8	119.4	113.0	104.6	99.4	97.8	99.8	102.3	103.1
52.5°	109.0	106.6	99.8	92.6	88.6	87.8	89.9	91.8	93.1
55°	95.8	93.9	88.2	81.8	78.7	78.3	80.2	81.8	82.6
57.5°	85.0	83.1	77.9	72.3	69.5	69.1	71.1	72.3	72.6
60°	74.7	72.6	67.9	62.7	60.7	60.7	61.9	62.7	63.1
62.5°	65.0	63.1	58.7	54.3	52.7	52.7	52.7	53.1	54.3
65°	56.0	54.3	50.3	46.3	45.2	44.3	44.3	44.3	45.2
67.5°	47.6	46.0	42.7	39.2	37.9	36.8	36.3	37.1	37.1
70°	39.5	38.4	35.2	32.3	31.1	30.0	29.5	31.1	31.1
72.5°	32.3	31.1	29.2	26.3	25.2	24.7	25.5	26.3	26.8
75°	25.5	24.4	22.8	21.1	20.0	20.3	21.6	21.9	22.4
77.5°	19.2	18.7	17.1	16.0	16.0	16.3	17.1	17.9	18.4
80°	13.6	13.2	12.4	11.6	12.0	12.8	13.2	14.0	13.6
82.5°	8.4	8.4	7.9	7.9	8.4	9.2	9.5	10.0	10.3
85°	4.4	4.4	4.4	4.8	5.2	5.6	6.0	6.4	6.4
87.5°	1.2	1.6	1.6	2.0	2.4	2.4	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)