

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581027

Luminaire Tested: **HCC4S05D010SL-HM40525835-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010SL-HM40525835-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 680.3 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581027
CATALOG NUMBER: HCC4S05D010SL-HM40525835-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581027

CATALOG NUMBER: HCC4S05D010SL-HM40525835-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			87
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58			58
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52			52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47			47
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42			42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	46995	46995	46995
5°	49056	46778	44624
10°	50300	45803	41820
15°	51334	44579	38794
20°	51074	42411	35533
25°	48927	39223	32337
30°	45192	35806	29312
35°	39617	31862	26532
40°	34506	28146	23879
45°	30021	24543	21351
50°	26750	21146	18844
55°	23892	18602	16279
60°	21339	16257	14061
65°	18971	14243	13338
70°	16661	12262	12442
75°	14106	10485	11533
80°	10797	8950	10513
85°	6227	6935	8774



TEST NUMBER: P581027
 CATALOG NUMBER: HCC4S05D010SL-HM40525835-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	5.2
10°-20°	98.5	14.5
20°-30°	134.6	19.8
30°-40°	135.1	19.9
40°-50°	111.8	16.4
50°-60°	81.0	11.9
60°-70°	51.3	7.5
70°-80°	25.9	3.8
80°-90°	6.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.8	39.5
0°-40°	404.0	59.4
0°-60°	596.8	87.7
0°-90°	680.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	680.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	381	381	381	381	381	
5°	396	390	378	365	360	38
15°	402	386	349	317	304	113
25°	360	336	288	252	238	164
35°	263	247	212	186	176	165
45°	172	162	141	127	122	134
55°	111	101	86	79	76	100
65°	65	58	49	44	46	65
75°	30	26	22	23	24	32
85°	4	4	5	6	6	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581027

CATALOG NUMBER: HCC4S05D010SL-HM40525835-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	381.0	381.0	381.0	381.0	381.0	381.0	381.0	381.0	381.0
2.5°	388.2	386.8	384.5	381.9	378.7	375.1	372.1	370.2	369.3
5°	396.2	394.4	390.4	384.5	377.8	371.1	365.4	361.7	360.4
7.5°	401.1	398.5	392.6	383.6	373.4	363.5	355.0	350.0	348.7
10°	401.6	398.5	390.9	378.7	365.7	352.8	342.4	335.3	333.9
12.5°	402.0	398.0	388.6	374.3	358.1	342.0	329.5	321.0	318.7
15°	402.0	398.0	386.4	369.3	349.1	330.7	316.9	307.0	303.8
17.5°	398.5	394.0	380.1	360.4	338.5	317.8	301.7	291.4	288.2
20°	389.1	384.1	368.4	347.0	323.1	301.7	285.6	274.8	270.7
22.5°	375.6	369.8	353.2	329.9	306.1	284.2	268.5	257.3	253.7
25°	359.5	353.7	335.7	312.8	288.2	267.6	251.9	241.6	237.6
27.5°	339.7	333.5	316.0	293.2	270.2	249.7	235.3	225.9	221.9
30°	317.3	310.6	294.1	272.1	251.4	231.8	217.8	210.2	205.8
32.5°	291.4	285.6	270.7	251.1	231.8	212.9	201.2	194.5	190.9
35°	263.1	259.9	247.4	230.4	211.6	195.9	185.6	179.3	176.2
37.5°	238.0	234.8	224.2	209.7	193.2	178.9	170.4	164.9	162.3
40°	214.3	211.6	201.2	189.2	174.8	162.3	155.0	151.1	148.3
42.5°	190.9	189.5	181.0	169.9	157.3	146.5	140.7	137.6	135.4
45°	172.1	170.4	162.3	151.5	140.7	131.8	126.9	124.6	122.4
47.5°	155.5	153.3	144.8	135.4	125.5	117.5	112.9	110.7	109.9
50°	139.4	137.1	129.5	120.1	110.2	104.4	100.9	98.6	98.2
52.5°	125.1	122.8	114.3	105.3	97.7	92.7	89.7	87.4	86.5
55°	111.1	108.5	101.2	92.7	86.5	82.1	78.9	76.6	75.7
57.5°	98.6	95.9	89.7	81.6	75.7	71.7	69.0	66.7	65.9
60°	86.5	84.2	78.4	70.8	65.9	62.3	59.6	57.8	57.0
62.5°	75.3	73.5	67.6	60.9	57.0	53.8	51.5	49.7	50.6
65°	65.0	63.2	57.8	52.0	48.8	45.7	43.9	43.9	45.7
67.5°	55.2	53.3	48.8	43.9	41.2	39.0	37.7	39.0	40.3
70°	46.2	44.4	40.3	36.3	34.0	32.2	32.2	33.6	34.5
72.5°	37.7	35.9	32.7	29.6	27.8	26.4	27.8	28.7	29.6
75°	29.6	28.3	25.5	23.3	22.0	21.6	22.8	23.7	24.2
77.5°	22.0	21.1	19.3	17.5	16.6	17.0	18.4	18.8	19.3
80°	15.2	14.8	13.4	12.6	12.6	13.1	13.8	14.3	14.8
82.5°	9.4	9.4	8.5	8.1	8.5	9.4	9.9	10.3	10.3
85°	4.4	4.9	4.4	4.4	4.9	5.8	5.8	6.2	6.2
87.5°	1.4	1.4	1.8	1.8	2.3	2.3	2.3	2.3	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)