

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581007

Luminaire Tested: **HCC4W05D010SL-HM40525830-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010SL-HM40525830-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 663.4 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581007
CATALOG NUMBER: HCC4W05D010SL-HM40525830-41RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P581007

CATALOG NUMBER: HCC4W05D010SL-HM40525830-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88				
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77				77				
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67				67				
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59				59				
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52				52				
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47				
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42				
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38				
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35				
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	42924	42924	42924
5°	44054	42927	42135
10°	45052	42559	40881
15°	46316	41961	39803
20°	46178	40350	38184
25°	44245	37767	36365
30°	40706	34795	34410
35°	35807	31561	31847
40°	30980	28258	29434
45°	26933	25101	26637
50°	23891	22144	23660
55°	21182	19419	20257
60°	18872	16849	16849
65°	16782	14009	13105
70°	14498	10603	9377
75°	12153	7053	5767
80°	9163	3410	3054
85°	4812	1274	1274



TEST NUMBER: P581007
 CATALOG NUMBER: HCC4W05D010SL-HM40525830-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.0	5.0
10°-20°	93.4	14.1
20°-30°	131.8	19.9
30°-40°	136.1	20.5
40°-50°	115.4	17.4
50°-60°	84.0	12.7
60°-70°	49.1	7.4
70°-80°	18.2	2.7
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.2	38.9
0°-40°	394.3	59.4
0°-60°	593.6	89.5
0°-90°	663.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	663.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	348	348	348	348	348	
5°	356	353	347	342	340	34
15°	363	352	329	315	312	102
25°	325	307	278	268	267	149
35°	238	227	210	210	212	149
45°	154	150	144	149	153	120
55°	98	94	90	93	94	89
65°	58	53	48	45	45	57
75°	26	21	15	12	12	27
85°	3	2	1	1	1	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581007

CATALOG NUMBER: HCC4W05D010SL-HM40525830-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	348.0	348.0	348.0	348.0	348.0	348.0	348.0	348.0	348.0
2.5°	351.1	350.1	349.4	348.0	346.3	344.9	343.7	342.8	342.8
5°	355.8	354.5	352.8	349.7	346.7	344.1	341.5	340.3	340.3
7.5°	359.2	357.5	354.0	349.7	344.6	340.6	336.8	335.1	334.1
10°	359.7	358.0	353.2	346.7	339.8	333.7	329.4	326.8	326.4
12.5°	360.6	358.4	352.3	343.2	334.1	326.8	322.1	319.5	318.6
15°	362.7	359.7	351.5	339.8	328.6	320.0	314.7	312.6	311.7
17.5°	360.6	356.2	346.3	332.4	320.0	310.4	305.2	303.0	303.0
20°	351.8	347.5	335.8	320.8	307.4	298.3	293.1	291.8	290.9
22.5°	339.8	335.1	322.5	306.4	293.1	284.9	281.5	279.7	279.3
25°	325.1	320.3	306.9	290.6	277.5	270.6	267.6	267.6	267.2
27.5°	308.7	302.6	288.7	274.6	262.0	256.7	255.5	255.5	255.9
30°	285.8	281.5	269.8	255.9	244.3	240.8	240.8	241.6	241.6
32.5°	261.2	258.1	247.7	235.6	226.5	224.4	225.2	227.0	227.3
35°	237.8	234.3	227.3	216.6	209.6	208.8	210.1	211.5	211.5
37.5°	214.9	211.5	206.7	197.9	192.8	193.3	195.0	196.7	197.9
40°	192.4	189.8	186.4	179.4	175.5	177.3	179.4	181.1	182.8
42.5°	172.5	169.9	167.3	162.1	159.5	161.7	164.2	166.1	167.8
45°	154.4	152.7	150.0	145.7	143.9	146.1	149.1	150.8	152.7
47.5°	138.8	137.9	134.5	130.5	129.7	131.9	134.5	136.7	137.9
50°	124.5	123.3	120.2	116.3	115.4	118.8	120.7	121.9	123.3
52.5°	110.7	109.4	105.9	102.5	102.5	105.1	106.3	106.8	108.1
55°	98.5	97.3	93.9	91.3	90.3	92.5	93.4	93.4	94.2
57.5°	87.3	86.0	82.5	79.6	79.1	80.4	80.4	80.4	80.8
60°	76.5	75.3	71.7	69.1	68.3	68.8	68.3	67.9	68.3
62.5°	66.6	65.3	61.9	58.8	57.9	57.9	56.6	56.2	56.6
65°	57.5	55.4	52.8	49.7	48.0	46.6	44.9	44.9	44.9
67.5°	48.5	46.6	43.7	40.6	38.5	36.3	33.7	34.6	35.1
70°	40.2	38.9	35.4	32.5	29.4	26.8	24.6	25.5	26.0
72.5°	32.8	31.1	28.1	24.6	22.0	18.6	17.3	18.2	18.2
75°	25.5	23.7	21.2	17.7	14.8	11.7	11.7	12.1	12.1
77.5°	19.1	17.3	14.8	11.7	9.1	6.9	7.4	7.4	7.4
80°	12.9	11.7	9.5	6.9	4.8	3.9	3.9	3.9	4.3
82.5°	7.4	6.5	5.2	3.4	2.2	2.2	2.2	2.2	2.2
85°	3.4	2.6	2.2	1.2	0.9	0.9	0.9	0.9	0.9
87.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)