

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581026

Luminaire Tested: **HCC4W05D010MW-HM40525835-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581026  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W05D010MW-HM40525835-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 544.1 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581026  
CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P581026

CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	38854	38854	38854
5°	41157	38730	36774
10°	42873	38113	34631
15°	44528	37185	32550
20°	44931	35414	30111
25°	43483	32745	27560
30°	40663	29682	25096
35°	36229	26381	22541
40°	31672	22929	20063
45°	27596	19467	17339
50°	24063	16503	14872
55°	21118	13698	12043
60°	18453	11052	8856
65°	16111	8260	4962
70°	14029	5337	1587
75°	11533	2764	429
80°	8595	1279	355
85°	5095	708	708



TEST NUMBER: P581026  
 CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.7	5.5
10°-20°	83.2	15.3
20°-30°	115.0	21.1
30°-40°	115.7	21.3
40°-50°	93.3	17.2
50°-60°	63.1	11.6
60°-70°	32.1	5.9
70°-80°	10.3	1.9
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.0	41.9
0°-40°	343.7	63.2
0°-60°	500.1	91.9
0°-90°	544.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	315	315	315	315	315	
5°	332	326	313	302	297	32
15°	349	330	291	263	255	98
25°	320	292	241	211	202	146
35°	241	217	175	153	150	150
45°	158	142	112	99	99	123
55°	98	85	64	56	56	88
65°	55	45	28	18	17	55
75°	24	17	6	1	1	26
85°	4	2	0	0	0	5
90°	0	0	0	0	0	



TEST NUMBER: P581026

CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0
2.5°	323.5	321.8	320.0	316.8	313.3	309.6	307.4	305.5	304.7
5°	332.4	330.3	326.2	319.5	312.8	306.4	301.6	298.4	297.0
7.5°	339.7	336.5	329.8	320.4	310.1	300.2	294.0	289.4	287.7
10°	342.3	338.8	329.8	317.2	304.3	292.1	283.2	278.8	276.5
12.5°	345.5	341.4	330.3	314.5	298.4	284.1	273.8	268.0	265.7
15°	348.7	343.2	329.8	310.5	291.2	274.7	263.4	257.6	254.9
17.5°	348.7	342.3	326.2	303.8	281.8	264.3	251.9	245.2	242.9
20°	342.3	335.2	317.7	293.1	269.8	250.9	238.8	232.1	229.4
22.5°	332.4	324.4	305.5	280.0	255.4	237.0	225.0	218.7	216.0
25°	319.5	311.4	291.7	265.2	240.6	222.2	211.0	205.2	202.5
27.5°	304.3	295.3	275.6	249.1	225.0	207.5	197.1	191.8	189.5
30°	285.5	276.9	257.6	231.7	208.4	192.3	182.8	177.9	176.2
32.5°	263.4	256.3	237.4	213.3	191.4	176.5	168.0	164.0	162.2
35°	240.6	233.9	217.4	194.9	175.2	161.3	153.2	150.6	149.7
37.5°	219.2	213.3	197.1	176.5	158.7	146.5	139.4	137.6	136.7
40°	196.7	192.7	177.9	159.1	142.4	131.8	125.9	124.6	124.6
42.5°	176.5	172.1	159.1	142.0	127.2	116.5	112.5	111.1	111.6
45°	158.2	153.7	141.6	125.9	111.6	102.6	99.4	99.4	99.4
47.5°	141.2	137.1	125.9	109.8	98.2	90.9	87.8	87.8	88.3
50°	125.4	122.8	110.2	96.4	86.0	79.3	77.1	76.6	77.5
52.5°	110.7	107.6	96.4	83.8	73.9	68.6	66.3	65.8	66.3
55°	98.2	94.5	84.7	72.6	63.7	58.2	55.6	55.2	56.0
57.5°	86.0	83.3	73.1	62.3	53.8	48.4	46.2	45.3	45.7
60°	74.8	72.2	62.8	52.4	44.8	39.4	36.3	35.4	35.9
62.5°	64.6	62.3	53.3	43.5	35.9	30.9	27.8	25.5	26.4
65°	55.2	52.9	44.8	35.0	28.3	22.8	18.4	16.6	17.0
67.5°	47.1	44.4	36.8	27.8	21.1	15.2	10.3	9.4	9.4
70°	38.9	36.3	29.6	21.6	14.8	8.1	4.4	4.4	4.4
72.5°	31.3	29.2	22.8	16.1	9.4	3.6	1.8	1.8	1.8
75°	24.2	22.4	17.0	11.2	5.8	1.8	1.4	0.9	0.9
77.5°	17.9	16.1	12.1	7.6	3.6	0.9	0.9	0.9	0.9
80°	12.1	10.8	8.1	4.4	1.8	0.5	0.5	0.5	0.5
82.5°	7.2	6.2	4.4	2.3	0.9	0.5	0.5	0.5	0.5
85°	3.6	2.7	1.8	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.9	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)