

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581028

Luminaire Tested: **HCC4W05D010MW-HM40525835-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581028
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010MW-HM40525835-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 677.2 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581028
CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P581028

CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	43072	43072	43072
5°	45292	43014	41404
10°	46880	42509	39528
15°	48308	41731	37837
20°	48370	40022	35651
25°	46559	37399	33425
30°	43227	34410	31220
35°	38744	30989	28881
40°	33991	27646	26696
45°	29724	24474	24631
50°	26251	21415	22202
55°	23139	18989	19956
60°	20697	16800	17466
65°	18329	14768	14768
70°	16012	12622	12622
75°	13678	10675	11962
80°	10797	9518	10797
85°	6935	8208	10190



TEST NUMBER: P581028
 CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.1	4.9
10°-20°	93.2	13.8
20°-30°	130.5	19.3
30°-40°	134.5	19.9
40°-50°	114.5	16.9
50°-60°	84.8	12.5
60°-70°	53.2	7.9
70°-80°	26.5	3.9
80°-90°	6.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.8	37.9
0°-40°	391.3	57.8
0°-60°	590.6	87.2
0°-90°	677.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	349	349	349	349	349	
5°	366	360	347	338	334	35
15°	378	361	327	303	296	106
25°	342	318	275	251	246	156
35°	257	238	206	192	192	160
45°	170	159	140	138	141	132
55°	108	99	88	90	93	97
65°	63	56	51	50	51	63
75°	29	26	22	24	25	31
85°	5	5	6	7	7	6
90°	0	0	0	0	0	



TEST NUMBER: P581028

CATALOG NUMBER: HCC4W05D010MW-HM40525835-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.2	349.2
2.5°	356.8	355.5	353.7	350.6	347.4	344.7	342.1	340.7	340.3
5°	365.8	363.1	359.6	353.7	347.4	342.1	337.5	335.3	334.4
7.5°	372.1	369.3	363.5	354.6	345.6	337.5	330.4	327.2	326.3
10°	374.3	371.1	363.1	351.1	339.4	329.5	321.4	317.3	315.6
12.5°	376.1	372.1	361.7	347.4	333.1	321.0	312.5	307.0	305.8
15°	378.3	373.9	361.3	343.8	326.8	312.5	303.0	298.1	296.3
17.5°	376.1	371.1	356.4	336.6	317.3	301.7	291.4	286.9	285.1
20°	368.5	363.1	346.5	325.4	304.9	288.7	278.4	273.9	271.6
22.5°	356.8	351.1	333.9	311.6	290.4	274.8	264.9	260.5	259.1
25°	342.1	336.2	318.3	295.4	274.8	259.6	251.1	247.0	245.6
27.5°	324.5	318.7	301.2	278.9	259.1	244.7	238.0	234.0	233.1
30°	303.5	297.7	280.6	260.0	241.6	228.1	222.8	219.6	219.2
32.5°	280.1	275.2	259.6	240.7	223.3	212.0	208.0	205.8	205.3
35°	257.3	252.0	238.0	221.0	205.8	195.9	192.3	191.8	191.8
37.5°	234.0	228.6	217.5	201.7	188.8	179.8	178.4	178.9	178.9
40°	211.1	206.2	196.4	183.3	171.7	164.9	164.5	165.4	165.8
42.5°	189.7	185.6	176.6	165.4	155.6	150.2	150.6	152.4	153.8
45°	170.4	166.7	158.7	148.8	140.3	136.3	137.7	139.8	141.2
47.5°	152.9	149.7	142.1	133.1	126.0	123.3	125.1	127.8	129.5
50°	136.8	134.0	126.9	117.5	111.6	109.9	112.0	114.7	115.7
52.5°	122.4	119.7	112.0	104.0	99.5	98.6	100.9	103.1	104.4
55°	107.6	105.3	99.1	91.9	88.3	87.8	90.1	91.9	92.8
57.5°	95.5	93.3	87.4	81.2	78.0	77.5	79.8	81.2	81.6
60°	83.9	81.6	76.2	70.4	68.1	68.1	69.5	70.4	70.8
62.5°	73.1	70.8	65.9	60.9	59.1	59.1	59.1	59.6	60.9
65°	62.8	60.9	56.5	52.0	50.6	49.7	49.7	49.7	50.6
67.5°	53.3	51.5	48.0	43.9	42.6	41.2	40.7	41.7	41.7
70°	44.4	43.0	39.5	36.3	35.0	33.6	33.1	35.0	35.0
72.5°	36.3	35.0	32.7	29.6	28.3	27.8	28.7	29.6	30.1
75°	28.7	27.4	25.5	23.7	22.4	22.8	24.2	24.6	25.1
77.5°	21.6	21.1	19.3	17.9	17.9	18.4	19.3	20.2	20.7
80°	15.2	14.8	13.8	13.1	13.4	14.3	14.8	15.7	15.2
82.5°	9.4	9.4	9.0	9.0	9.4	10.3	10.8	11.2	11.7
85°	4.9	4.9	4.9	5.3	5.8	6.2	6.7	7.2	7.2
87.5°	1.4	1.8	1.8	2.3	2.7	2.7	3.2	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)