

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581023

Luminaire Tested: **HCC4W05D010SL-HM40525835-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010SL-HM40525835-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 667.8 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581023
CATALOG NUMBER: HCC4W05D010SL-HM40525835-41WDW

Luminous Intensity Polar Plot





TEST NUMBER: P581023

CATALOG NUMBER: HCC4W05D010SL-HM40525835-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	53396	53396	53396
5°	53266	53316	53316
10°	52642	52692	52642
15°	52024	52024	52024
20°	49879	49998	50063
25°	46654	46708	46831
30°	41802	41931	41931
35°	33940	34211	34271
40°	25602	25747	25827
45°	19624	19537	19537
50°	16157	16081	16081
55°	13871	13784	13784
60°	12384	12261	12261
65°	11616	11616	11616
70°	10855	10855	10855
75°	9865	10056	9865
80°	9163	8950	9163
85°	7501	7501	7501



TEST NUMBER: P581023
 CATALOG NUMBER: HCC4W05D010SL-HM40525835-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	6.1
10°-20°	114.1	17.1
20°-30°	156.8	23.5
30°-40°	141.0	21.1
40°-50°	89.1	13.3
50°-60°	58.1	8.7
60°-70°	39.4	5.9
70°-80°	22.2	3.3
80°-90°	6.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.8	46.7
0°-40°	452.8	67.8
0°-60°	600.0	89.8
0°-90°	667.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	667.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	433	433	433	433	433	
5°	430	430	431	431	431	41
15°	407	407	407	407	407	114
25°	343	343	343	344	344	156
35°	225	226	227	228	228	140
45°	112	112	112	112	112	89
55°	64	64	64	64	64	58
65°	40	40	40	40	40	40
75°	21	21	21	21	21	22
85°	5	5	5	5	5	6
90°	0	0	0	0	0	



TEST NUMBER: P581023

CATALOG NUMBER: HCC4W05D010SL-HM40525835-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	432.9	432.9	432.9	432.9	432.9
2.5°	430.6	430.6	430.6	430.6	430.6
5°	430.2	430.2	430.6	430.6	430.6
7.5°	427.0	427.4	427.4	427.4	427.4
10°	420.3	420.3	420.7	420.7	420.3
12.5°	414.0	414.0	414.0	414.5	414.0
15°	407.4	407.4	407.4	407.4	407.4
17.5°	395.7	396.1	396.1	396.1	396.1
20°	380.0	380.9	380.9	381.4	381.4
22.5°	362.1	362.5	363.0	363.4	363.0
25°	342.8	343.2	343.2	344.1	344.1
27.5°	320.4	320.9	321.8	321.8	321.8
30°	293.5	294.0	294.4	294.4	294.4
32.5°	261.7	261.7	262.5	263.0	262.5
35°	225.4	226.3	227.2	228.0	227.6
37.5°	190.9	191.8	192.3	192.3	192.7
40°	159.0	159.9	159.9	160.8	160.4
42.5°	133.9	133.5	133.5	134.4	133.9
45°	112.5	112.0	112.0	112.0	112.0
47.5°	96.8	96.4	96.4	96.4	96.4
50°	84.2	83.8	83.8	83.8	83.8
52.5°	73.9	73.4	73.4	73.4	73.0
55°	64.5	64.5	64.1	64.5	64.1
57.5°	56.0	56.0	56.0	56.0	56.0
60°	50.2	49.7	49.7	49.7	49.7
62.5°	44.8	44.8	44.8	44.8	44.8
65°	39.8	39.8	39.8	39.8	39.8
67.5°	35.0	34.5	35.0	35.0	34.5
70°	30.1	29.6	30.1	30.1	30.1
72.5°	25.1	25.1	25.1	25.5	25.1
75°	20.7	21.1	21.1	21.1	20.7
77.5°	16.6	17.0	16.6	16.6	16.6
80°	12.9	12.6	12.6	12.6	12.9
82.5°	9.0	9.0	9.0	9.0	9.0
85°	5.3	5.3	5.3	5.3	5.3
87.5°	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)