

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592546

Luminaire Tested: **HCC4S05D010MB-HM40525850-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010MB-HM40525850-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 699.2 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592546
CATALOG NUMBER: HCC4S05D010MB-HM40525850-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P592546

CATALOG NUMBER: HCC4S05D010MB-HM40525850-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87	87	87	87
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58	58	58	58
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52	52	52	52
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47	47	47	47
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42	42	42	42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38	38	38	38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35	35	35	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32	32	32	32

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	48290	48290	48290
5°	50406	48078	45862
10°	51690	47068	42973
15°	52752	45818	39867
20°	52465	43592	36517
25°	50274	40298	33221
30°	46446	36803	30123
35°	40716	32735	27254
40°	35456	28935	24539
45°	30840	25224	21944
50°	27479	21741	19362
55°	24558	19118	16752
60°	21931	16726	14431
65°	19467	14651	13717
70°	17094	12622	12767
75°	14488	10771	11867
80°	11152	9163	10797
85°	6652	7218	9199



TEST NUMBER: P592546
 CATALOG NUMBER: HCC4S05D010MB-HM40525850-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	5.2
10°-20°	101.2	14.5
20°-30°	138.3	19.8
30°-40°	138.9	19.9
40°-50°	114.9	16.4
50°-60°	83.3	11.9
60°-70°	52.7	7.5
70°-80°	26.7	3.8
80°-90°	6.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.2	39.5
0°-40°	415.1	59.4
0°-60°	613.2	87.7
0°-90°	699.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	699.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	392	392	392	392	392	
5°	407	401	388	375	370	39
15°	413	397	359	326	312	116
25°	369	345	296	259	244	169
35°	270	254	217	191	181	169
45°	177	167	145	130	126	138
55°	114	104	89	81	78	103
65°	67	60	50	45	47	66
75°	30	26	23	24	25	32
85°	5	5	5	6	6	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P592546

CATALOG NUMBER: HCC4S05D010MB-HM40525850-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	391.5	391.5	391.5	391.5	391.5	391.5	391.5	391.5	391.5
2.5°	398.8	397.5	395.2	392.5	389.2	385.6	382.3	380.5	379.5
5°	407.1	405.3	401.2	395.2	388.3	381.4	375.3	371.7	370.4
7.5°	412.2	409.5	403.5	394.3	383.6	373.5	364.8	359.7	358.3
10°	412.7	409.5	401.7	389.2	375.8	362.5	351.8	344.6	343.1
12.5°	413.1	409.1	399.3	384.7	368.0	351.4	338.6	329.8	327.4
15°	413.1	409.1	397.0	379.5	358.8	339.9	325.6	315.5	312.2
17.5°	409.5	404.9	390.6	370.4	347.8	326.5	310.0	299.4	296.1
20°	399.7	394.8	378.6	356.5	332.1	310.0	293.4	282.4	278.2
22.5°	386.0	380.0	363.0	339.0	314.6	292.0	275.9	264.3	260.7
25°	369.4	363.4	345.0	321.5	296.1	275.0	258.9	248.2	244.1
27.5°	349.1	342.7	324.7	301.2	277.7	256.5	241.9	232.1	228.0
30°	326.1	319.2	302.1	279.6	258.4	238.1	223.8	216.0	211.5
32.5°	299.4	293.4	278.2	258.0	238.1	218.8	206.8	199.9	196.2
35°	270.4	267.2	254.2	236.8	217.4	201.2	190.7	184.2	181.0
37.5°	244.6	241.3	230.3	215.5	198.5	183.8	175.0	169.5	166.7
40°	220.2	217.4	206.8	194.4	179.7	166.7	159.4	155.3	152.4
42.5°	196.2	194.9	186.0	174.6	161.6	150.6	144.6	141.4	139.2
45°	176.8	175.0	166.7	155.7	144.6	135.4	130.3	128.0	125.8
47.5°	159.8	157.5	148.8	139.2	128.9	120.7	116.1	113.7	112.8
50°	143.2	141.0	133.1	123.5	113.3	107.4	103.6	101.4	100.9
52.5°	128.5	126.2	117.5	108.3	100.4	95.3	92.2	89.8	88.9
55°	114.2	111.5	104.1	95.3	88.9	84.3	81.0	78.8	77.9
57.5°	101.4	98.5	92.2	83.9	77.9	73.7	70.9	68.7	67.8
60°	88.9	86.6	80.6	72.8	67.8	64.0	61.3	59.5	58.5
62.5°	77.4	75.6	69.6	62.7	58.5	55.3	53.0	51.1	52.1
65°	66.7	64.9	59.5	53.5	50.2	47.0	45.2	45.2	47.0
67.5°	56.6	54.8	50.2	45.2	42.3	40.1	38.7	40.1	41.4
70°	47.4	45.6	41.4	37.3	35.0	33.1	33.1	34.5	35.4
72.5°	38.7	36.9	33.6	30.4	28.6	27.1	28.6	29.5	30.4
75°	30.4	29.1	26.2	23.9	22.6	22.1	23.5	24.4	24.9
77.5°	22.6	21.7	19.9	17.9	17.0	17.5	18.8	19.3	19.9
80°	15.7	15.2	13.8	12.9	12.9	13.4	14.3	14.8	15.2
82.5°	9.6	9.6	8.7	8.3	8.7	9.6	10.1	10.6	10.6
85°	4.7	5.1	4.7	4.7	5.1	6.0	6.0	6.5	6.5
87.5°	1.4	1.4	1.8	1.8	2.3	2.3	2.3	2.3	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)