

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581069

Luminaire Tested: **HCC4S05D010BZ-HM40525930-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010BZ-HM40525930-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 606.8 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581069
CATALOG NUMBER: HCC4S05D010BZ-HM40525930-41WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581069

CATALOG NUMBER: HCC4S05D010BZ-HM40525930-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92			92																
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84			84																
3	100	93	87	83	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76																
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69																
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63			63																
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53			53																
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51028
5°	51409
10°	52041
15°	53352
20°	53752
25°	52207
30°	47870
35°	39391
40°	28709
45°	18630
50°	10496
55°	4989
60°	1949
65°	1226
70°	829
75°	524
80°	213
85°	425



TEST NUMBER: P581069
 CATALOG NUMBER: HCC4S05D010BZ-HM40525930-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	6.5
10°-20°	117.8	19.4
20°-30°	174.7	28.8
30°-40°	161.4	26.6
40°-50°	84.2	13.9
50°-60°	23.1	3.8
60°-70°	4.5	0.7
70°-80°	1.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.2	54.7
0°-40°	493.5	81.3
0°-60°	600.9	99.0
0°-90°	606.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	414	
5°	415	40
15°	418	118
25°	384	175
35°	262	161
45°	107	84
55°	23	23
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581069

CATALOG NUMBER: HCC4S05D010BZ-HM40525930-41WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	413.7
2.5°	412.6
5°	415.2
7.5°	416.3
10°	415.5
12.5°	416.3
15°	417.8
17.5°	416.3
20°	409.5
22.5°	398.5
25°	383.6
27.5°	363.4
30°	336.1
32.5°	301.5
35°	261.6
37.5°	219.7
40°	178.3
42.5°	140.3
45°	106.8
47.5°	78.3
50°	54.7
52.5°	36.5
55°	23.2
57.5°	13.7
60°	7.9
62.5°	5.7
65°	4.2
67.5°	3.1
70°	2.3
72.5°	1.5
75°	1.1
77.5°	0.8
80°	0.3
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)