

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581079

Luminaire Tested: **HCC4W05D010BZ-HM40525930-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010BZ-HM40525930-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 582.9 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581079
CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581079

CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	37731	37731	37731
5°	38718	37715	37021
10°	39591	37399	35921
15°	40697	36866	34976
20°	40599	35454	33564
25°	38883	33194	31956
30°	35778	30565	30252
35°	31471	27736	27977
40°	27228	24829	25875
45°	23654	22084	23409
50°	20993	19477	20782
55°	18623	17075	17827
60°	16578	14801	14801
65°	14739	12317	11528
70°	12731	9341	8223
75°	10675	6148	5099
80°	8098	2983	2628
85°	4387	1132	1132



TEST NUMBER: P581079
 CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	5.0
10°-20°	82.1	14.1
20°-30°	115.8	19.9
30°-40°	119.6	20.5
40°-50°	101.4	17.4
50°-60°	73.8	12.7
60°-70°	43.1	7.4
70°-80°	16.0	2.7
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	226.9	38.9
0°-40°	346.5	59.4
0°-60°	521.7	89.5
0°-90°	582.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	306	306	306	306	306	
5°	313	310	305	300	299	30
15°	319	309	289	277	274	90
25°	286	270	244	235	235	131
35°	209	200	184	185	186	131
45°	136	132	127	131	134	106
55°	87	82	79	82	83	78
65°	50	46	42	40	40	50
75°	22	19	13	10	11	24
85°	3	2	1	1	1	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581079

CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9
2.5°	308.5	307.7	307.0	305.9	304.3	303.2	302.0	301.2	301.2
5°	312.7	311.6	310.0	307.4	304.6	302.4	300.1	299.0	299.0
7.5°	315.8	314.2	311.1	307.4	302.8	299.4	296.0	294.4	293.6
10°	316.1	314.6	310.4	304.6	298.6	293.3	289.5	287.3	286.8
12.5°	316.9	315.0	309.6	301.7	293.6	287.3	283.1	280.8	280.0
15°	318.7	316.1	308.8	298.6	288.7	281.1	276.6	274.7	273.9
17.5°	316.9	313.0	304.3	292.1	281.1	272.7	268.2	266.3	266.3
20°	309.3	305.4	295.2	281.9	270.1	262.2	257.5	256.4	255.7
22.5°	298.6	294.4	283.4	269.3	257.5	250.4	247.3	245.8	245.4
25°	285.7	281.5	269.8	255.3	243.9	237.8	235.2	235.2	234.8
27.5°	271.3	265.9	253.8	241.3	230.2	225.6	224.5	224.5	225.0
30°	251.2	247.3	237.1	225.0	214.6	211.6	211.6	212.4	212.4
32.5°	229.5	226.8	217.7	207.0	199.1	197.1	197.9	199.4	199.9
35°	209.0	205.9	199.9	190.3	184.2	183.5	184.7	185.8	185.8
37.5°	188.9	185.8	181.6	174.0	169.5	169.8	171.4	172.9	174.0
40°	169.1	166.7	163.8	157.7	154.2	155.7	157.7	159.1	160.7
42.5°	151.6	149.3	147.0	142.4	140.2	142.1	144.4	145.8	147.4
45°	135.6	134.2	131.8	128.0	126.6	128.4	131.1	132.6	134.2
47.5°	121.9	121.2	118.2	114.7	114.0	115.9	118.2	120.1	121.2
50°	109.4	108.3	105.7	102.2	101.5	104.4	106.0	107.1	108.3
52.5°	97.3	96.1	93.1	90.0	90.0	92.3	93.4	93.9	95.0
55°	86.6	85.5	82.4	80.1	79.4	81.3	82.1	82.1	82.9
57.5°	76.7	75.6	72.5	69.9	69.6	70.7	70.7	70.7	71.1
60°	67.2	66.1	63.1	60.8	60.0	60.4	60.0	59.7	60.0
62.5°	58.5	57.3	54.4	51.6	51.0	51.0	49.7	49.4	49.7
65°	50.5	48.6	46.3	43.7	42.2	41.1	39.5	39.5	39.5
67.5°	42.6	41.1	38.4	35.8	33.8	31.9	29.6	30.4	30.8
70°	35.3	34.2	31.1	28.5	25.9	23.6	21.7	22.4	22.8
72.5°	28.8	27.4	24.7	21.7	19.4	16.3	15.2	16.0	16.0
75°	22.4	20.9	18.6	15.5	12.9	10.2	10.2	10.7	10.7
77.5°	16.7	15.2	12.9	10.2	7.9	6.1	6.5	6.5	6.5
80°	11.4	10.2	8.4	6.1	4.2	3.4	3.4	3.4	3.7
82.5°	6.5	5.7	4.5	3.1	1.9	1.9	1.9	1.9	1.9
85°	3.1	2.3	1.9	1.1	0.8	0.8	0.8	0.8	0.8
87.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)