

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581081

Luminaire Tested: **HCC4W05D010BZ-HM40525930-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581081
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010BZ-HM40525930-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 576.8 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581081
CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581081

CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39841	39841	39841
5°	41602	39659	37826
10°	42647	38840	35458
15°	43519	37798	32895
20°	43290	35966	30125
25°	41469	33262	27424
30°	38313	30365	24839
35°	33579	26998	22496
40°	29241	23863	20256
45°	25468	20810	18089
50°	22682	17942	15965
55°	20257	15763	13806
60°	18082	13765	11891
65°	16052	12083	11324
70°	14137	10386	10567
75°	11962	8864	9770
80°	9163	7600	8879
85°	5236	5944	7501



TEST NUMBER: P581081
 CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.3	5.2
10°-20°	83.5	14.5
20°-30°	114.1	19.8
30°-40°	114.6	19.9
40°-50°	94.8	16.4
50°-60°	68.7	11.9
60°-70°	43.5	7.5
70°-80°	22.0	3.8
80°-90°	5.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.9	39.5
0°-40°	342.5	59.4
0°-60°	505.9	87.7
0°-90°	576.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	323	323	323	323	323	
5°	336	331	320	310	306	32
15°	341	328	296	269	258	96
25°	305	285	244	214	202	139
35°	223	210	179	157	149	140
45°	146	138	119	108	104	114
55°	94	86	73	67	64	85
65°	55	49	41	37	39	55
75°	25	22	19	19	20	27
85°	4	4	4	5	5	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581081

CATALOG NUMBER: HCC4W05D010BZ-HM40525930-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	323.0	323.0	323.0	323.0	323.0	323.0	323.0	323.0	323.0
2.5°	329.2	327.9	326.1	323.8	321.1	318.0	315.4	313.9	313.1
5°	336.0	334.4	331.0	326.1	320.3	314.6	309.7	306.7	305.5
7.5°	340.2	337.9	332.9	325.3	316.6	308.2	301.0	296.8	295.7
10°	340.5	337.9	331.4	321.1	310.1	299.1	290.3	284.2	283.1
12.5°	340.8	337.4	329.5	317.3	303.6	290.0	279.3	272.1	270.2
15°	340.8	337.4	327.6	313.1	296.0	280.5	268.7	260.3	257.6
17.5°	337.9	334.0	322.2	305.5	286.9	269.4	255.7	247.0	244.4
20°	329.8	325.6	312.4	294.1	274.0	255.7	242.1	232.9	229.5
22.5°	318.5	313.5	299.4	279.7	259.6	241.0	227.7	218.1	215.1
25°	304.7	299.9	284.7	265.2	244.4	226.9	213.6	204.9	201.5
27.5°	288.1	282.7	267.9	248.6	229.2	211.7	199.5	191.5	188.1
30°	269.0	263.3	249.2	230.6	213.2	196.5	184.7	178.2	174.4
32.5°	247.0	242.1	229.5	212.8	196.5	180.5	170.6	164.9	161.9
35°	223.0	220.4	209.7	195.3	179.3	166.1	157.3	152.0	149.4
37.5°	201.8	199.1	190.0	177.9	163.8	151.6	144.4	139.8	137.6
40°	181.6	179.3	170.6	160.4	148.2	137.6	131.4	128.0	125.8
42.5°	161.9	160.7	153.6	144.0	133.4	124.3	119.3	116.7	114.7
45°	146.0	144.4	137.6	128.5	119.3	111.7	107.6	105.7	103.7
47.5°	131.9	130.0	122.7	114.7	106.3	99.5	95.8	93.9	93.1
50°	118.2	116.3	109.9	101.8	93.5	88.5	85.5	83.6	83.2
52.5°	106.0	104.1	96.9	89.3	82.9	78.7	76.0	74.1	73.3
55°	94.2	91.9	85.9	78.7	73.3	69.6	66.9	65.0	64.2
57.5°	83.6	81.4	76.0	69.1	64.2	60.8	58.6	56.6	55.8
60°	73.3	71.4	66.5	60.0	55.8	52.8	50.5	49.0	48.2
62.5°	63.8	62.3	57.4	51.6	48.2	45.6	43.7	42.2	42.9
65°	55.0	53.6	49.0	44.0	41.4	38.8	37.2	37.2	38.8
67.5°	46.8	45.2	41.4	37.2	35.0	33.0	31.9	33.0	34.2
70°	39.2	37.6	34.2	30.8	28.8	27.4	27.4	28.5	29.3
72.5°	31.9	30.4	27.7	25.1	23.6	22.5	23.6	24.3	25.1
75°	25.1	23.9	21.7	19.7	18.6	18.3	19.4	20.1	20.5
77.5°	18.6	17.8	16.3	14.9	14.1	14.4	15.5	16.0	16.3
80°	12.9	12.5	11.4	10.7	10.7	11.0	11.8	12.1	12.5
82.5°	7.9	7.9	7.3	6.8	7.3	7.9	8.4	8.7	8.7
85°	3.7	4.2	3.7	3.7	4.2	5.0	5.0	5.3	5.3
87.5°	1.1	1.1	1.5	1.5	1.9	1.9	1.9	1.9	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)