

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581082

Luminaire Tested: **HCC4W05D010SL-HM40525930-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W05D010SL-HM40525930-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 574.1 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581082
CATALOG NUMBER: HCC4W05D010SL-HM40525930-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581082

CATALOG NUMBER: HCC4W05D010SL-HM40525930-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36523	36523	36523
5°	38396	36464	35102
10°	39741	36034	33504
15°	40965	35385	32077
20°	41019	33918	30230
25°	39468	31711	28349
30°	36647	29183	26463
35°	32841	26261	24484
40°	28822	23428	22639
45°	25189	20741	20880
50°	22240	18172	18825
55°	19634	16107	16924
60°	17540	14259	14801
65°	15527	12521	12521
70°	13596	10675	10675
75°	11581	9055	10151
80°	9163	8098	9163
85°	5944	7076	8633



TEST NUMBER: P581082
 CATALOG NUMBER: HCC4W05D010SL-HM40525930-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.1	4.9
10°-20°	79.0	13.8
20°-30°	110.7	19.3
30°-40°	114.0	19.9
40°-50°	97.1	16.9
50°-60°	71.9	12.5
60°-70°	45.1	7.9
70°-80°	22.4	3.9
80°-90°	5.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.7	37.9
0°-40°	331.7	57.8
0°-60°	500.7	87.2
0°-90°	574.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	574.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	296	296	296	296	296	
5°	310	305	294	286	284	30
15°	321	306	277	257	251	90
25°	290	270	233	213	208	133
35°	218	202	174	163	163	136
45°	144	134	119	117	120	112
55°	91	84	75	76	79	82
65°	53	48	43	42	43	53
75°	24	22	19	20	21	26
85°	4	4	5	6	6	5
90°	0	0	0	0	0	



TEST NUMBER: P581082

CATALOG NUMBER: HCC4W05D010SL-HM40525930-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1	296.1
2.5°	302.5	301.3	299.9	297.3	294.5	292.3	290.0	288.9	288.5
5°	310.1	307.8	304.9	299.9	294.5	290.0	286.1	284.3	283.5
7.5°	315.4	313.1	308.3	300.7	293.1	286.1	280.1	277.4	276.7
10°	317.3	314.7	307.8	297.6	287.7	279.3	272.5	269.1	267.5
12.5°	318.8	315.4	306.7	294.5	282.4	272.2	264.9	260.4	259.2
15°	320.8	317.0	306.3	291.5	277.1	264.9	257.0	252.8	251.2
17.5°	318.8	314.7	302.1	285.5	269.1	255.8	247.1	243.2	241.8
20°	312.5	307.8	293.7	275.9	258.4	244.7	236.0	232.2	230.3
22.5°	302.5	297.6	283.2	264.1	246.3	233.0	224.6	220.9	219.6
25°	290.0	285.0	269.8	250.5	233.0	220.1	212.8	209.4	208.3
27.5°	275.1	270.2	255.4	236.4	219.6	207.5	201.8	198.4	197.6
30°	257.3	252.3	237.9	220.4	204.9	193.4	188.9	186.3	185.8
32.5°	237.6	233.4	220.1	204.1	189.3	179.8	176.4	174.4	174.1
35°	218.1	213.6	201.8	187.4	174.4	166.1	163.1	162.6	162.6
37.5°	198.4	193.9	184.3	171.0	160.0	152.4	151.3	151.6	151.6
40°	179.0	174.8	166.5	155.5	145.5	139.8	139.5	140.3	140.6
42.5°	160.7	157.3	149.7	140.3	131.9	127.3	127.7	129.3	130.4
45°	144.4	141.4	134.5	126.2	118.9	115.5	116.7	118.6	119.7
47.5°	129.6	126.9	120.4	112.9	106.8	104.5	106.0	108.3	109.9
50°	115.9	113.6	107.6	99.5	94.7	93.1	95.0	97.3	98.1
52.5°	103.7	101.5	95.0	88.2	84.3	83.6	85.5	87.4	88.5
55°	91.3	89.3	84.0	77.9	74.9	74.5	76.4	77.9	78.7
57.5°	80.9	79.0	74.1	68.8	66.2	65.7	67.6	68.8	69.1
60°	71.1	69.1	64.6	59.7	57.8	57.8	58.9	59.7	60.0
62.5°	62.0	60.0	55.8	51.6	50.2	50.2	50.2	50.5	51.6
65°	53.2	51.6	47.9	44.0	42.9	42.2	42.2	42.2	42.9
67.5°	45.2	43.7	40.6	37.2	36.1	35.0	34.6	35.3	35.3
70°	37.7	36.4	33.5	30.8	29.6	28.5	28.1	29.6	29.6
72.5°	30.8	29.6	27.7	25.1	23.9	23.6	24.3	25.1	25.4
75°	24.3	23.2	21.7	20.1	19.0	19.4	20.5	20.9	21.3
77.5°	18.3	17.8	16.3	15.2	15.2	15.5	16.3	17.1	17.5
80°	12.9	12.6	11.8	11.0	11.4	12.1	12.6	13.3	12.9
82.5°	7.9	7.9	7.6	7.6	7.9	8.7	9.1	9.5	9.9
85°	4.2	4.2	4.2	4.5	5.0	5.3	5.7	6.1	6.1
87.5°	1.1	1.5	1.5	1.9	2.3	2.3	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)