

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581048

Luminaire Tested: **HCC4W05D010MB-HM40525927-41WDWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581048  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W05D010MB-HM40525927-41WDWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 551.3 lumens  
Efficiency: N/A  
Efficacy: 91.9 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.07  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581048  
CATALOG NUMBER: HCC4W05D010MB-HM40525927-41WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P581048  
 CATALOG NUMBER: HCC4W05D010MB-HM40525927-41WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90																			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80																			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72																			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65																			
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59																			
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54																			
7	76	64	57	52	74	64	57	52	62	56	52	61	56	51	60	55	51	49																			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46																			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42																			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	45256
5°	45478
10°	45791
15°	46252
20°	45469
25°	43374
30°	39410
35°	31787
40°	22059
45°	14478
50°	9691
55°	6903
60°	5896
65°	6800
70°	7285
75°	6958
80°	6322
85°	5802



TEST NUMBER: P581048  
 CATALOG NUMBER: HCC4W05D010MB-HM40525927-41WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.0	6.3
10°-20°	101.7	18.5
20°-30°	145.3	26.4
30°-40°	129.8	23.5
40°-50°	66.6	12.1
50°-60°	30.3	5.5
60°-70°	22.6	4.1
70°-80°	15.4	2.8
80°-90°	4.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.1	51.2
0°-40°	411.9	74.7
0°-60°	508.7	92.3
0°-90°	551.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	551.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	367	
5°	367	35
15°	362	102
25°	319	145
35°	211	130
45°	83	67
55°	32	30
65°	23	23
75°	15	15
85°	4	5
90°	0	



TEST NUMBER: P581048

CATALOG NUMBER: HCC4W05D010MB-HM40525927-41WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	366.9
2.5°	365.6
5°	367.3
7.5°	367.3
10°	365.6
12.5°	363.9
15°	362.2
17.5°	357.0
20°	346.4
22.5°	333.5
25°	318.7
27.5°	300.3
30°	276.7
32.5°	246.6
35°	211.1
37.5°	173.2
40°	137.0
42.5°	106.9
45°	83.0
47.5°	64.9
50°	50.5
52.5°	39.6
55°	32.1
57.5°	27.0
60°	23.9
62.5°	23.3
65°	23.3
67.5°	22.6
70°	20.2
72.5°	17.5
75°	14.6
77.5°	11.6
80°	8.9
82.5°	6.5
85°	4.1
87.5°	1.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)