

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581092

Luminaire Tested: **HCC4S05D010BZ-HM40525935-41MDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010BZ-HM40525935-41MDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 578.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581092
CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41MDW

Luminous Intensity Polar Plot





TEST NUMBER: P581092
 CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89																			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79																			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70																			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63																			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57																			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52																			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47																			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44																			
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40																			
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48993
5°	48734
10°	47845
15°	46839
20°	44839
25°	41686
30°	36903
35°	29122
40°	21802
45°	16763
50°	13605
55°	11268
60°	9966
65°	9252
70°	8511
75°	7863
80°	7103
85°	5661



TEST NUMBER: P581092
 CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.2	6.4
10°-20°	102.9	17.8
20°-30°	139.7	24.2
30°-40°	121.0	20.9
40°-50°	76.0	13.1
50°-60°	47.8	8.3
60°-70°	31.4	5.4
70°-80°	17.3	3.0
80°-90°	4.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.8	48.4
0°-40°	400.8	69.3
0°-60°	524.5	90.7
0°-90°	578.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	578.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	397	
5°	394	37
15°	367	103
25°	306	140
35°	193	121
45°	96	76
55°	52	48
65°	32	31
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P581092
CATALOG NUMBER: HCC4S05D010BZ-HM40525935-41MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	397.2
2.5°	394.9
5°	393.6
7.5°	389.6
10°	382.0
12.5°	374.4
15°	366.8
17.5°	356.4
20°	341.6
22.5°	324.8
25°	306.3
27.5°	285.1
30°	259.1
32.5°	227.5
35°	193.4
37.5°	162.2
40°	135.4
42.5°	114.2
45°	96.1
47.5°	82.5
50°	70.9
52.5°	60.8
55°	52.4
57.5°	45.3
60°	40.4
62.5°	36.1
65°	31.7
67.5°	27.2
70°	23.6
72.5°	19.6
75°	16.5
77.5°	12.8
80°	10.0
82.5°	6.8
85°	4.0
87.5°	1.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)