

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581113

Luminaire Tested: **HCC4S05D010SL-HM40525940-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S05D010SL-HM40525940-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 618.0 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581113
CATALOG NUMBER: HCC4S05D010SL-HM40525940-41WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581113

CATALOG NUMBER: HCC4S05D010SL-HM40525940-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69					69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62					62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56					56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51					51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46					46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42					42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39					39			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36					36			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	49400	49400	49400
5°	49279	49341	49341
10°	48722	48759	48722
15°	48129	48129	48129
20°	46152	46257	46322
25°	43170	43224	43347
30°	38683	38797	38797
35°	31410	31651	31727
40°	23702	23830	23911
45°	18159	18072	18072
50°	14968	14872	14872
55°	12838	12731	12731
60°	11446	11372	11372
65°	10770	10770	10770
70°	10026	10026	10026
75°	9103	9293	9103
80°	8524	8240	8524
85°	7076	7076	7076



TEST NUMBER: P581113
 CATALOG NUMBER: HCC4S05D010SL-HM40525940-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.7	6.1
10°-20°	105.6	17.1
20°-30°	145.1	23.5
30°-40°	130.5	21.1
40°-50°	82.4	13.3
50°-60°	53.8	8.7
60°-70°	36.5	5.9
70°-80°	20.5	3.3
80°-90°	5.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.5	46.7
0°-40°	418.9	67.8
0°-60°	555.2	89.8
0°-90°	618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	618.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	400	400	400	400	400	
5°	398	398	398	398	398	38
15°	377	377	377	377	377	106
25°	317	318	318	318	318	145
35°	209	209	210	211	211	130
45°	104	104	104	104	104	83
55°	60	60	59	60	59	54
65°	37	37	37	37	37	37
75°	19	20	20	20	19	20
85°	5	5	5	5	5	6
90°	0	0	0	0	0	



TEST NUMBER: P581113

CATALOG NUMBER: HCC4S05D010SL-HM40525940-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	400.5	400.5	400.5	400.5	400.5
2.5°	398.5	398.5	398.5	398.5	398.5
5°	398.0	398.0	398.5	398.5	398.5
7.5°	395.2	395.5	395.5	395.5	395.5
10°	389.0	389.0	389.3	389.3	389.0
12.5°	383.2	383.2	383.2	383.5	383.2
15°	376.9	376.9	376.9	376.9	376.9
17.5°	366.2	366.5	366.5	366.5	366.5
20°	351.6	352.4	352.4	352.9	352.9
22.5°	335.1	335.4	335.8	336.3	335.8
25°	317.2	317.6	317.6	318.5	318.5
27.5°	296.5	296.9	297.7	297.7	297.7
30°	271.6	272.1	272.4	272.4	272.4
32.5°	242.1	242.1	243.0	243.3	243.0
35°	208.6	209.4	210.2	211.0	210.7
37.5°	176.6	177.5	177.9	177.9	178.3
40°	147.2	148.0	148.0	148.9	148.5
42.5°	123.9	123.6	123.6	124.4	123.9
45°	104.1	103.6	103.6	103.6	103.6
47.5°	89.6	89.1	89.1	89.1	89.1
50°	78.0	77.5	77.5	77.5	77.5
52.5°	68.4	68.0	68.0	68.0	67.5
55°	59.7	59.7	59.2	59.7	59.2
57.5°	51.9	51.9	51.9	51.9	51.9
60°	46.4	46.1	46.1	46.1	46.1
62.5°	41.4	41.4	41.4	41.4	41.4
65°	36.9	36.9	36.9	36.9	36.9
67.5°	32.3	31.9	32.3	32.3	31.9
70°	27.8	27.4	27.8	27.8	27.8
72.5°	23.3	23.3	23.3	23.6	23.3
75°	19.1	19.5	19.5	19.5	19.1
77.5°	15.3	15.8	15.3	15.3	15.3
80°	12.0	11.6	11.6	11.6	12.0
82.5°	8.3	8.3	8.3	8.3	8.3
85°	5.0	5.0	5.0	5.0	5.0
87.5°	2.0	2.0	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)