

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581422

Luminaire Tested: **HCC4W07D010MB-HM40525827-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010MB-HM40525827-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 641.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581422
CATALOG NUMBER: HCC4W07D010MB-HM40525827-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581422

CATALOG NUMBER: HCC4W07D010MB-HM40525827-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89					89			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78					78			
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69					69			
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61					61			
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55					55			
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49					49			
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44					44			
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40					40			
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37					37			
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34					34			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45774	45774	45774
5°	48499	45614	43323
10°	50513	44889	40793
15°	52445	43813	38347
20°	52938	41702	35480
25°	51213	38583	32459
30°	47898	34966	29554
35°	42689	31079	26547
40°	37307	27035	23621
45°	32498	22921	20444
50°	28362	19458	17520
55°	24859	16128	14193
60°	21758	13025	10410
65°	18971	9690	5837
70°	16589	6275	1875
75°	13535	3241	477
80°	10087	1563	426
85°	5944	849	849



TEST NUMBER: P581422
 CATALOG NUMBER: HCC4W07D010MB-HM40525827-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	5.5
10°-20°	98.0	15.3
20°-30°	135.5	21.1
30°-40°	136.3	21.3
40°-50°	110.0	17.2
50°-60°	74.4	11.6
60°-70°	37.8	5.9
70°-80°	12.1	1.9
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.6	41.9
0°-40°	404.8	63.2
0°-60°	589.1	91.9
0°-90°	641.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	371	371	371	371	371	
5°	392	384	368	355	350	38
15°	411	388	343	310	300	116
25°	376	344	284	249	238	172
35°	284	256	206	180	176	177
45°	186	167	131	117	117	144
55°	116	100	75	65	66	104
65°	65	53	33	22	20	65
75°	28	20	7	2	1	31
85°	4	2	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581422

CATALOG NUMBER: HCC4W07D010MB-HM40525827-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	371.1	371.1	371.1	371.1	371.1	371.1	371.1	371.1	371.1
2.5°	381.1	379.0	376.9	373.2	368.9	364.7	362.1	359.9	358.9
5°	391.7	389.0	384.3	376.3	368.4	361.1	355.3	351.5	349.9
7.5°	400.1	396.4	388.5	377.4	365.3	353.7	346.3	340.9	338.9
10°	403.3	399.0	388.5	373.7	358.4	344.1	333.5	328.3	325.7
12.5°	406.9	402.2	389.0	370.5	351.5	334.7	322.5	315.7	313.0
15°	410.7	404.3	388.5	365.8	343.1	323.5	310.3	303.5	300.3
17.5°	410.7	403.3	384.3	357.9	332.0	311.5	296.7	288.7	286.1
20°	403.3	394.8	374.2	345.2	317.7	295.5	281.3	273.5	270.3
22.5°	391.7	382.1	359.9	329.9	300.9	279.3	264.9	257.5	254.5
25°	376.3	366.9	343.6	312.5	283.5	261.9	248.7	241.7	238.5
27.5°	358.4	347.9	324.7	293.5	264.9	244.3	232.3	225.9	223.3
30°	336.3	326.2	303.5	272.9	245.5	226.5	215.3	209.5	207.5
32.5°	310.3	301.9	279.7	251.3	225.4	207.9	197.9	193.2	191.1
35°	283.5	275.5	256.0	229.6	206.4	190.0	180.5	177.3	176.3
37.5°	258.1	251.3	232.3	207.9	186.9	172.6	164.1	162.1	161.0
40°	231.7	226.9	209.5	187.4	167.9	155.2	148.3	146.7	146.7
42.5°	207.9	202.7	187.4	167.3	149.9	137.2	132.5	130.9	131.4
45°	186.3	181.1	166.8	148.3	131.4	120.9	117.2	117.2	117.2
47.5°	166.3	161.5	148.3	129.3	115.6	107.2	103.4	103.4	104.0
50°	147.8	144.6	129.8	113.5	101.4	93.4	90.8	90.2	91.3
52.5°	130.4	126.7	113.5	98.7	87.1	80.8	78.1	77.6	78.1
55°	115.6	111.4	99.8	85.5	75.0	68.6	65.4	65.0	66.0
57.5°	101.4	98.2	86.0	73.4	63.4	57.0	54.4	53.3	53.8
60°	88.2	85.0	73.9	61.8	52.8	46.4	42.8	41.7	42.2
62.5°	76.0	73.4	62.8	51.2	42.2	36.4	32.8	30.0	31.2
65°	65.0	62.2	52.8	41.2	33.2	27.0	21.6	19.6	20.0
67.5°	55.4	52.2	43.2	32.8	24.8	18.0	12.2	11.0	11.0
70°	46.0	42.8	34.8	25.4	17.4	9.4	5.2	5.2	5.2
72.5°	37.0	34.3	27.0	19.0	11.0	4.2	2.2	2.2	2.2
75°	28.4	26.4	20.0	13.2	6.8	2.2	1.6	1.0	1.0
77.5°	21.2	19.0	14.2	9.0	4.2	1.0	1.0	1.0	1.0
80°	14.2	12.6	9.4	5.2	2.2	0.6	0.6	0.6	0.6
82.5°	8.4	7.4	5.2	2.6	1.0	0.6	0.6	0.6	0.6
85°	4.2	3.2	2.2	1.0	0.6	0.6	0.6	0.6	0.6
87.5°	1.0	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)