

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581434

Luminaire Tested: **HCC4S07D010MW-HM40525830-41MDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581434  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S07D010MW-HM40525830-41MDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 825.7 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.01  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581434  
CATALOG NUMBER: HCC4S07D010MW-HM40525830-41MDW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581434

CATALOG NUMBER: HCC4S07D010MW-HM40525830-41MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89			
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47			
8	70	58	51	46	68	58	51	46	56	50	46	55	50	45	54	49	45	44			
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	46	42	40			
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	69999
5°	69635
10°	68361
15°	66913
20°	64056
25°	59570
30°	52727
35°	41604
40°	31124
45°	23968
50°	19439
55°	16128
60°	14259
65°	13192
70°	12190
75°	11152
80°	10158
85°	8067



TEST NUMBER: P581434  
 CATALOG NUMBER: HCC4S07D010MW-HM40525830-41MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.2	6.4
10°-20°	147.0	17.8
20°-30°	199.6	24.2
30°-40°	172.9	20.9
40°-50°	108.6	13.1
50°-60°	68.3	8.3
60°-70°	44.8	5.4
70°-80°	24.7	3.0
80°-90°	6.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	399.7	48.4
0°-40°	572.6	69.3
0°-60°	749.4	90.8
0°-90°	825.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	825.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	568	
5°	562	53
15°	524	147
25°	438	200
35°	276	173
45°	137	109
55°	75	68
65°	45	45
75°	23	25
85°	6	7
90°	0	



TEST NUMBER: P581434  
CATALOG NUMBER: HCC4S07D010MW-HM40525830-41MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	567.5
2.5°	564.1
5°	562.4
7.5°	556.7
10°	545.8
12.5°	535.0
15°	524.0
17.5°	509.3
20°	488.0
22.5°	464.0
25°	437.7
27.5°	407.4
30°	370.2
32.5°	325.0
35°	276.3
37.5°	231.7
40°	193.3
42.5°	163.1
45°	137.4
47.5°	117.9
50°	101.3
52.5°	86.9
55°	75.0
57.5°	64.6
60°	57.8
62.5°	51.4
65°	45.2
67.5°	38.9
70°	33.8
72.5°	28.0
75°	23.4
77.5°	18.3
80°	14.3
82.5°	9.7
85°	5.7
87.5°	2.3
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)