

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581445

Luminaire Tested: **HCC4W07D010SL-HM40525835-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581445  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010SL-HM40525835-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 871.3 lumens  
Efficiency: N/A  
Efficacy: 108.9 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581445  
CATALOG NUMBER: HCC4W07D010SL-HM40525835-41MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581445  
 CATALOG NUMBER: HCC4W07D010SL-HM40525835-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86															
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79				79															
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73				73															
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67															
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62				62															
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58				58															
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54				54															
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51				51															
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47				47															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	112800
5°	110445
10°	104382
15°	97484
20°	89153
25°	79603
30°	66855
35°	47040
40°	28999
45°	17374
50°	10247
55°	5097
60°	2640
65°	1722
70°	1082
75°	858
80°	426
85°	849



TEST NUMBER: P581445  
 CATALOG NUMBER: HCC4W07D010SL-HM40525835-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.3	9.6
10°-20°	213.4	24.5
20°-30°	266.1	30.5
30°-40°	196.0	22.5
40°-50°	80.6	9.3
50°-60°	23.6	2.7
60°-70°	6.0	0.7
70°-80°	1.9	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.8	64.6
0°-40°	758.8	87.1
0°-60°	863.0	99.0
0°-90°	871.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	871.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	914	
5°	892	83
15°	763	213
25°	585	266
35°	312	196
45°	100	81
55°	24	24
65°	6	6
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P581445  
CATALOG NUMBER: HCC4W07D010SL-HM40525835-41MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	914.5
2.5°	905.1
5°	892.0
7.5°	868.3
10°	833.4
12.5°	798.9
15°	763.4
17.5°	723.7
20°	679.2
22.5°	633.0
25°	584.9
27.5°	531.7
30°	469.4
32.5°	394.1
35°	312.4
37.5°	240.0
40°	180.1
42.5°	133.4
45°	99.6
47.5°	73.5
50°	53.4
52.5°	36.8
55°	23.7
57.5°	14.2
60°	10.7
62.5°	7.7
65°	5.9
67.5°	4.1
70°	3.0
72.5°	2.4
75°	1.8
77.5°	1.1
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)