

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581437

Luminaire Tested: **HCC4W07D010SL-HM40525830-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010SL-HM40525830-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 852.0 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581437
CATALOG NUMBER: HCC4W07D010SL-HM40525830-41WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581437

CATALOG NUMBER: HCC4W07D010SL-HM40525830-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	68124	68124	68124
5°	67963	68025	68025
10°	67158	67233	67158
15°	66351	66351	66351
20°	63636	63780	63859
25°	59515	59597	59747
30°	53325	53481	53481
35°	43306	43637	43728
40°	32670	32847	32944
45°	25032	24927	24927
50°	20609	20513	20513
55°	17698	17569	17569
60°	15813	15665	15665
65°	14856	14856	14856
70°	13849	13849	13849
75°	12534	12820	12534
80°	11791	11365	11791
85°	9624	9624	9624



TEST NUMBER: P581437
 CATALOG NUMBER: HCC4W07D010SL-HM40525830-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	6.1
10°-20°	145.6	17.1
20°-30°	200.1	23.5
30°-40°	179.9	21.1
40°-50°	113.7	13.3
50°-60°	74.2	8.7
60°-70°	50.3	5.9
70°-80°	28.3	3.3
80°-90°	7.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.7	46.7
0°-40°	577.6	67.8
0°-60°	765.5	89.8
0°-90°	852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	552	552	552	552	552	
5°	549	549	549	549	549	52
15°	520	520	520	520	520	145
25°	437	438	438	439	439	200
35°	288	289	290	291	290	179
45°	144	143	143	143	143	114
55°	82	82	82	82	82	74
65°	51	51	51	51	51	50
75°	26	27	27	27	26	28
85°	7	7	7	7	7	8
90°	0	0	0	0	0	



TEST NUMBER: P581437

CATALOG NUMBER: HCC4W07D010SL-HM40525830-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	552.3	552.3	552.3	552.3	552.3
2.5°	549.4	549.4	549.4	549.4	549.4
5°	548.9	548.9	549.4	549.4	549.4
7.5°	544.8	545.3	545.3	545.3	545.3
10°	536.2	536.2	536.8	536.8	536.2
12.5°	528.3	528.3	528.3	528.8	528.3
15°	519.6	519.6	519.6	519.6	519.6
17.5°	504.8	505.4	505.4	505.4	505.4
20°	484.8	485.9	485.9	486.5	486.5
22.5°	461.9	462.5	463.1	463.6	463.1
25°	437.3	437.9	437.9	439.0	439.0
27.5°	408.8	409.3	410.5	410.5	410.5
30°	374.4	375.0	375.5	375.5	375.5
32.5°	333.9	333.9	335.0	335.6	335.0
35°	287.6	288.7	289.8	291.0	290.4
37.5°	243.5	244.7	245.2	245.2	245.8
40°	202.9	204.0	204.0	205.2	204.6
42.5°	170.9	170.4	170.4	171.5	170.9
45°	143.5	142.9	142.9	142.9	142.9
47.5°	123.5	122.9	122.9	122.9	122.9
50°	107.4	106.9	106.9	106.9	106.9
52.5°	94.3	93.8	93.8	93.8	93.2
55°	82.3	82.3	81.7	82.3	81.7
57.5°	71.5	71.5	71.5	71.5	71.5
60°	64.1	63.5	63.5	63.5	63.5
62.5°	57.1	57.1	57.1	57.1	57.1
65°	50.9	50.9	50.9	50.9	50.9
67.5°	44.6	44.0	44.6	44.6	44.0
70°	38.4	37.8	38.4	38.4	38.4
72.5°	32.0	32.0	32.0	32.5	32.0
75°	26.3	26.9	26.9	26.9	26.3
77.5°	21.2	21.7	21.2	21.2	21.2
80°	16.6	16.0	16.0	16.0	16.6
82.5°	11.4	11.4	11.4	11.4	11.4
85°	6.8	6.8	6.8	6.8	6.8
87.5°	2.8	2.8	2.8	2.8	2.8
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)