

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581447

Luminaire Tested: **HCC4S07D010SL-HM40525835-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581447  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S07D010SL-HM40525835-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 946.6 lumens  
Efficiency: N/A  
Efficacy: 118.3 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581447  
CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581447

CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	98	97	96	95	94	92	92	92	92	92															
	1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92	92	92	92	92	92	92	92	92															
	2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	81	78	86	86	86	86	86	86	86	86															
	3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	73	73	73	73	73	73	73	73	73	73															
	4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	66	66	66	66	66	66	66	66	66	66															
	5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63	63	63	63	63	63	63	63	63															
	6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58	58	58	58	58	58	58	58	58															
	7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53	53	53	53	53	53	53	53	53															
	8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49	49	49	49	49	49	49	49	49															
	9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45	45	45	45	45	45	45	45	45															
	10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42	42	42	42	42	42	42	42	42															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	79583
5°	80184
10°	81186
15°	83220
20°	83850
25°	81440
30°	74675
35°	61436
40°	44779
45°	29061
50°	16388
55°	7785
60°	3059
65°	1897
70°	1262
75°	858
80°	426
85°	849



TEST NUMBER: P581447  
 CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.8	6.5
10°-20°	183.7	19.4
20°-30°	272.5	28.8
30°-40°	251.7	26.6
40°-50°	131.4	13.9
50°-60°	36.0	3.8
60°-70°	6.9	0.7
70°-80°	1.9	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.1	54.7
0°-40°	769.8	81.3
0°-60°	937.3	99.0
0°-90°	946.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	946.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	645	
5°	648	62
15°	652	184
25°	598	273
35°	408	252
45°	167	131
55°	36	36
65°	6	7
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P581447  
CATALOG NUMBER: HCC4S07D010SL-HM40525835-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	645.2
2.5°	643.4
5°	647.6
7.5°	649.3
10°	648.2
12.5°	649.3
15°	651.7
17.5°	649.3
20°	638.8
22.5°	621.5
25°	598.4
27.5°	567.0
30°	524.3
32.5°	470.3
35°	408.0
37.5°	342.8
40°	278.1
42.5°	218.8
45°	166.6
47.5°	122.2
50°	85.4
52.5°	56.9
55°	36.2
57.5°	21.4
60°	12.4
62.5°	8.9
65°	6.5
67.5°	4.8
70°	3.5
72.5°	2.4
75°	1.8
77.5°	1.1
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)