

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592570

Luminaire Tested: **HCC4S07D010SL-HM40525850-41WDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592570  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S07D010SL-HM40525850-41WDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 972.7 lumens  
Efficiency: N/A  
Efficacy: 121.6 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592570  
CATALOG NUMBER: HCC4S07D010SL-HM40525850-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P592570

CATALOG NUMBER: HCC4S07D010SL-HM40525850-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92						92													
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84						84													
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76						76													
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69						69													
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63						63													
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58						58													
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53						53													
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49						49													
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45						45													
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42						42													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	81790
5°	82400
10°	83428
15°	85519
20°	86160
25°	83686
30°	76726
35°	63122
40°	46035
45°	29881
50°	16829
55°	8000
60°	3133
65°	1955
70°	1298
75°	858
80°	426
85°	849



TEST NUMBER: P592570  
 CATALOG NUMBER: HCC4S07D010SL-HM40525850-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.5	6.5
10°-20°	188.8	19.4
20°-30°	280.1	28.8
30°-40°	258.7	26.6
40°-50°	135.1	13.9
50°-60°	37.0	3.8
60°-70°	7.1	0.7
70°-80°	2.0	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.4	54.7
0°-40°	791.1	81.3
0°-60°	963.2	99.0
0°-90°	972.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	972.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	663	
5°	666	64
15°	670	189
25°	615	280
35°	419	259
45°	171	135
55°	37	37
65°	7	7
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P592570  
CATALOG NUMBER: HCC4S07D010SL-HM40525850-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	663.1
2.5°	661.2
5°	665.5
7.5°	667.3
10°	666.1
12.5°	667.3
15°	669.7
17.5°	667.3
20°	656.4
22.5°	638.6
25°	614.9
27.5°	582.7
30°	538.7
32.5°	483.3
35°	419.2
37.5°	352.2
40°	285.9
42.5°	224.9
45°	171.3
47.5°	125.5
50°	87.7
52.5°	58.5
55°	37.2
57.5°	22.0
60°	12.7
62.5°	9.1
65°	6.7
67.5°	4.9
70°	3.6
72.5°	2.4
75°	1.8
77.5°	1.3
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)