

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581492

Luminaire Tested: **HCC4W07D010MB-HM40525927-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010MB-HM40525927-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 696.5 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581492
CATALOG NUMBER: HCC4W07D010MB-HM40525927-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581492

CATALOG NUMBER: HCC4W07D010MB-HM40525927-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41222	41222	41222
5°	42890	41615	41157
10°	44300	41971	41081
15°	45843	42102	41067
20°	46007	41098	40560
25°	44395	39033	39346
30°	41304	36362	37373
35°	37208	33263	34482
40°	32799	30255	31640
45°	28677	27247	28608
50°	25387	24524	25829
55°	22343	21655	22537
60°	19933	18502	19069
65°	17541	15002	14768
70°	15291	11072	10098
75°	12677	6672	5385
80°	9589	2557	1634
85°	4529	708	708



TEST NUMBER: P581492
 CATALOG NUMBER: HCC4W07D010MB-HM40525927-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.2	4.6
10°-20°	94.1	13.5
20°-30°	136.3	19.6
30°-40°	143.8	20.6
40°-50°	124.4	17.9
50°-60°	92.2	13.2
60°-70°	53.1	7.6
70°-80°	18.6	2.7
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	262.6	37.7
0°-40°	406.3	58.3
0°-60°	622.9	89.4
0°-90°	696.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	696.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	334	334	334	334	334	
5°	346	342	336	333	332	33
15°	359	347	330	322	322	101
25°	326	310	287	285	289	149
35°	247	236	221	226	229	154
45°	164	160	156	162	164	128
55°	104	102	101	104	105	94
65°	60	56	51	49	51	60
75°	27	22	14	11	11	29
85°	3	2	0	0	0	5
90°	0	0	0	0	0	



TEST NUMBER: P581492

CATALOG NUMBER: HCC4W07D010MB-HM40525927-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	334.2	334.2	334.2	334.2	334.2	334.2	334.2	334.2	334.2
2.5°	339.2	338.3	337.0	335.1	333.3	332.0	331.5	331.0	331.0
5°	346.4	344.6	342.0	338.3	336.1	334.7	333.3	332.4	332.4
7.5°	351.4	349.6	345.5	340.6	337.4	334.7	332.9	331.5	331.5
10°	353.7	351.4	346.4	340.1	335.1	331.5	328.8	328.0	328.0
12.5°	356.4	353.7	346.9	338.8	332.4	328.0	325.2	324.3	324.3
15°	359.0	356.0	347.3	337.9	329.7	324.3	322.1	321.6	321.6
17.5°	357.7	353.7	343.7	332.4	323.4	318.0	315.7	315.7	316.1
20°	350.5	346.4	335.1	322.5	313.1	309.0	307.1	308.1	309.0
22.5°	339.7	334.7	322.5	310.3	300.3	296.8	296.8	298.2	299.4
25°	326.2	321.6	309.9	296.3	286.8	284.2	285.0	287.2	289.1
27.5°	310.8	305.8	293.6	281.0	271.4	270.0	272.3	275.5	276.4
30°	290.0	285.9	275.5	263.3	255.3	254.8	257.9	260.1	262.4
32.5°	270.0	265.6	255.6	243.9	238.1	238.5	242.1	244.8	246.1
35°	247.1	243.0	235.8	226.2	220.9	221.8	225.9	228.5	229.0
37.5°	225.4	222.7	215.4	208.3	204.2	206.0	209.6	212.7	212.7
40°	203.7	201.4	196.1	190.2	187.9	190.2	193.8	196.5	196.5
42.5°	182.9	181.6	177.1	173.0	171.6	174.8	178.0	180.3	179.8
45°	164.4	163.1	159.9	156.7	156.2	159.4	162.2	163.5	164.0
47.5°	147.7	146.8	144.1	141.8	141.8	145.0	147.3	148.6	149.1
50°	132.3	131.4	129.2	127.3	127.8	131.0	132.8	134.2	134.6
52.5°	117.0	116.5	114.7	112.4	113.8	116.1	118.4	119.3	119.7
55°	103.9	103.9	101.6	99.8	100.7	103.0	104.4	104.8	104.8
57.5°	92.2	91.7	89.0	87.2	87.6	89.9	90.8	91.3	91.3
60°	80.8	80.3	77.7	75.0	75.0	76.4	76.8	77.3	77.3
62.5°	70.0	69.5	66.3	64.2	63.3	62.8	62.8	63.7	65.5
65°	60.1	59.6	56.4	52.8	51.4	50.2	48.8	49.7	50.6
67.5°	51.1	50.2	47.0	43.8	40.6	38.4	36.2	37.4	39.3
70°	42.4	41.5	37.9	34.4	30.7	27.1	25.3	27.1	28.0
72.5°	34.4	33.5	29.8	26.2	21.7	18.1	17.6	18.1	18.5
75°	26.6	26.2	22.5	18.5	14.0	11.3	11.3	11.3	11.3
77.5°	19.9	19.0	15.4	11.7	8.1	6.4	5.9	5.9	5.9
80°	13.5	12.6	9.4	6.8	3.6	2.7	2.7	2.3	2.3
82.5°	7.6	7.3	5.0	2.7	1.4	0.9	0.9	0.9	0.9
85°	3.2	2.7	1.8	0.9	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)