

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581460

Luminaire Tested: **HCC4W07D010SL-HM40525835-41WWWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581460  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010SL-HM40525835-41WWWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 895.6 lumens  
Efficiency: N/A  
Efficacy: 111.9 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581460  
CATALOG NUMBER: HCC4W07D010SL-HM40525835-41WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P581460

CATALOG NUMBER: HCC4W07D010SL-HM40525835-41WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75					75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58					58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51					51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46					46			
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41					41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37					37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34					34			
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	56961	56961	56961
5°	59903	56881	54752
10°	61998	56211	52266
15°	63899	55191	50032
20°	63964	52912	47162
25°	61570	49458	44218
30°	57170	45520	41275
35°	51241	40972	38216
40°	44972	36551	35311
45°	39301	32376	32567
50°	34694	28323	29340
55°	30580	25117	26386
60°	27333	22227	23115
65°	24224	19555	19555
70°	21169	16661	16661
75°	18062	14106	15822
80°	14277	12644	14277
85°	9199	10897	13303



TEST NUMBER: P581460  
 CATALOG NUMBER: HCC4W07D010SL-HM40525835-41WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.8	4.9
10°-20°	123.2	13.8
20°-30°	172.6	19.3
30°-40°	177.8	19.9
40°-50°	151.4	16.9
50°-60°	112.2	12.5
60°-70°	70.4	7.9
70°-80°	35.0	3.9
80°-90°	9.2	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.6	37.9
0°-40°	517.4	57.8
0°-60°	781.0	87.2
0°-90°	895.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	895.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	462	462	462	462	462	
5°	484	476	459	446	442	47
15°	500	478	432	401	392	141
25°	452	421	363	332	325	207
35°	340	315	272	254	254	212
45°	225	210	186	182	187	175
55°	142	131	117	119	123	129
65°	83	75	67	66	67	83
75°	38	34	30	32	33	40
85°	6	6	8	9	9	8
90°	0	0	0	0	0	



TEST NUMBER: P581460

CATALOG NUMBER: HCC4W07D010SL-HM40525835-41WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	461.8	461.8	461.8	461.8	461.8	461.8	461.8	461.8	461.8
2.5°	471.9	470.1	467.7	463.6	459.4	455.9	452.4	450.5	450.0
5°	483.8	480.2	475.5	467.7	459.4	452.4	446.4	443.5	442.2
7.5°	492.1	488.5	480.8	469.0	457.0	446.4	436.9	432.8	431.5
10°	495.0	490.8	480.2	464.2	448.8	435.7	425.0	419.7	417.3
12.5°	497.4	492.1	478.4	459.4	440.5	424.5	413.2	406.0	404.3
15°	500.4	494.5	477.8	454.7	432.2	413.2	400.8	394.2	391.8
17.5°	497.4	490.8	471.4	445.2	419.7	399.0	385.3	379.4	377.0
20°	487.3	480.2	458.3	430.4	403.1	381.8	368.1	362.2	359.3
22.5°	471.9	464.2	441.7	412.1	384.2	363.4	350.4	344.5	342.7
25°	452.4	444.6	420.9	390.7	363.4	343.2	332.0	326.6	324.9
27.5°	429.3	421.5	398.4	368.7	342.7	323.6	314.8	309.4	308.3
30°	401.4	393.6	371.1	343.8	319.6	301.8	294.6	290.5	289.8
32.5°	370.5	364.0	343.2	318.3	295.2	280.4	275.1	272.1	271.5
35°	340.3	333.2	314.8	292.2	272.1	259.1	254.3	253.8	253.8
37.5°	309.4	302.4	287.6	266.7	249.6	237.7	235.9	236.6	236.6
40°	279.3	272.7	259.7	242.5	227.0	218.2	217.6	218.7	219.3
42.5°	250.8	245.5	233.6	218.7	205.8	198.6	199.1	201.5	203.4
45°	225.3	220.5	209.8	196.9	185.6	180.3	182.0	184.9	186.7
47.5°	202.1	198.0	187.9	176.0	166.6	163.1	165.4	169.0	171.4
50°	180.8	177.3	167.7	155.3	147.6	145.2	148.2	151.8	152.9
52.5°	161.8	158.3	148.2	137.6	131.6	130.4	133.4	136.3	138.2
55°	142.2	139.3	131.0	121.5	116.8	116.2	119.1	121.5	122.7
57.5°	126.3	123.4	115.6	107.3	103.1	102.5	105.5	107.3	107.9
60°	110.8	107.9	100.8	93.1	90.1	90.1	91.8	93.1	93.7
62.5°	96.6	93.7	87.2	80.6	78.3	78.3	78.3	78.9	80.6
65°	83.0	80.6	74.7	68.7	67.0	65.8	65.8	65.8	67.0
67.5°	70.6	68.2	63.4	58.2	56.3	54.5	53.9	55.1	55.1
70°	58.7	56.9	52.1	48.0	46.2	44.5	43.8	46.2	46.2
72.5°	48.0	46.2	43.2	39.1	37.3	36.8	37.9	39.1	39.7
75°	37.9	36.2	33.8	31.4	29.6	30.3	32.0	32.7	33.2
77.5°	28.4	27.9	25.5	23.7	23.7	24.4	25.5	26.6	27.3
80°	20.1	19.6	18.3	17.2	17.8	19.0	19.6	20.7	20.1
82.5°	12.4	12.4	11.8	11.8	12.4	13.7	14.2	14.8	15.4
85°	6.5	6.5	6.5	7.2	7.7	8.3	8.9	9.4	9.4
87.5°	1.8	2.4	2.4	3.0	3.5	3.5	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)