

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581491

Luminaire Tested: **HCC4W07D010MW-HM40525927-41WDW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581491  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010MW-HM40525927-41WDW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 673.0 lumens  
Efficiency: N/A  
Efficacy: 84.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581491  
CATALOG NUMBER: HCC4W07D010MW-HM40525927-41WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581491

CATALOG NUMBER: HCC4W07D010MW-HM40525927-41WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	53803	53803	53803
5°	53675	53724	53724
10°	53055	53105	53055
15°	52420	52420	52420
20°	50260	50378	50444
25°	47021	47090	47185
30°	42130	42258	42258
35°	34196	34482	34542
40°	25811	25972	26036
45°	19764	19694	19694
50°	16292	16196	16196
55°	13978	13871	13871
60°	12458	12359	12359
65°	11733	11733	11733
70°	10927	10927	10927
75°	9913	10103	9913
80°	9305	8950	9305
85°	7784	7784	7784



TEST NUMBER: P581491  
 CATALOG NUMBER: HCC4W07D010MW-HM40525927-41WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.1	6.1
10°-20°	115.0	17.1
20°-30°	158.0	23.5
30°-40°	142.1	21.1
40°-50°	89.8	13.3
50°-60°	58.6	8.7
60°-70°	39.7	5.9
70°-80°	22.4	3.3
80°-90°	6.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.2	46.7
0°-40°	456.3	67.8
0°-60°	604.6	89.8
0°-90°	673.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	673.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	436	436	436	436	436	
5°	434	434	434	434	434	41
15°	410	410	410	410	410	115
25°	346	346	346	347	347	158
35°	227	228	229	230	229	141
45°	113	113	113	113	113	90
55°	65	65	64	65	64	59
65°	40	40	40	40	40	40
75°	21	21	21	21	21	22
85°	6	6	6	6	6	6
90°	0	0	0	0	0	



TEST NUMBER: P581491

CATALOG NUMBER: HCC4W07D010MW-HM40525927-41WDW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	436.2	436.2	436.2	436.2	436.2
2.5°	433.9	433.9	433.9	433.9	433.9
5°	433.5	433.5	433.9	433.9	433.9
7.5°	430.4	430.7	430.7	430.7	430.7
10°	423.6	423.6	424.0	424.0	423.6
12.5°	417.2	417.2	417.2	417.6	417.2
15°	410.5	410.5	410.5	410.5	410.5
17.5°	398.8	399.2	399.2	399.2	399.2
20°	382.9	383.8	383.8	384.3	384.3
22.5°	364.8	365.3	365.8	366.2	365.8
25°	345.5	346.0	346.0	346.7	346.7
27.5°	322.9	323.3	324.2	324.2	324.2
30°	295.8	296.2	296.7	296.7	296.7
32.5°	263.7	263.7	264.6	265.0	264.6
35°	227.1	228.1	229.0	229.9	229.4
37.5°	192.3	193.2	193.7	193.7	194.1
40°	160.3	161.3	161.3	162.2	161.7
42.5°	135.0	134.5	134.5	135.4	135.0
45°	113.3	112.9	112.9	112.9	112.9
47.5°	97.5	97.1	97.1	97.1	97.1
50°	84.9	84.4	84.4	84.4	84.4
52.5°	74.5	74.1	74.1	74.1	73.6
55°	65.0	65.0	64.5	65.0	64.5
57.5°	56.4	56.4	56.4	56.4	56.4
60°	50.5	50.1	50.1	50.1	50.1
62.5°	45.2	45.2	45.2	45.2	45.2
65°	40.2	40.2	40.2	40.2	40.2
67.5°	35.3	34.8	35.3	35.3	34.8
70°	30.3	29.8	30.3	30.3	30.3
72.5°	25.3	25.3	25.3	25.7	25.3
75°	20.8	21.2	21.2	21.2	20.8
77.5°	16.7	17.2	16.7	16.7	16.7
80°	13.1	12.6	12.6	12.6	13.1
82.5°	9.0	9.0	9.0	9.0	9.0
85°	5.5	5.5	5.5	5.5	5.5
87.5°	2.3	2.3	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)