

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581514

Luminaire Tested: **HCC4S07D010MW-HM40525930-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010MW-HM40525930-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 759.4 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581514
CATALOG NUMBER: HCC4S07D010MW-HM40525930-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581514

CATALOG NUMBER: HCC4S07D010MW-HM40525930-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87					87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75					75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66					66			
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58					58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51					51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46					46			
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41					41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37					37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34					34			
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	48302	48302	48302
5°	50777	48227	46431
10°	52567	47645	44313
15°	54169	46788	42421
20°	54237	44852	39982
25°	52193	41931	37481
30°	48468	38598	35009
35°	43442	34738	32389
40°	38113	30996	29933
45°	33317	27439	27613
50°	29417	24025	24888
55°	25935	21290	22365
60°	23189	18847	19587
65°	20518	16578	16578
70°	17924	14173	14173
75°	15346	11962	13392
80°	12146	10726	12146
85°	7925	9199	11463



TEST NUMBER: P581514
 CATALOG NUMBER: HCC4S07D010MW-HM40525930-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.1	4.9
10°-20°	104.5	13.8
20°-30°	146.4	19.3
30°-40°	150.8	19.9
40°-50°	128.4	16.9
50°-60°	95.1	12.5
60°-70°	59.7	7.9
70°-80°	29.7	3.9
80°-90°	7.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	287.9	37.9
0°-40°	438.7	57.8
0°-60°	662.2	87.2
0°-90°	759.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	392	392	392	392	392	
5°	410	403	390	378	375	39
15°	424	405	366	340	332	119
25°	384	357	308	281	275	175
35°	288	267	231	216	215	180
45°	191	178	157	154	158	148
55°	121	111	99	101	104	109
65°	70	63	57	56	57	70
75°	32	29	25	27	28	34
85°	6	6	6	8	8	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581514

CATALOG NUMBER: HCC4S07D010MW-HM40525930-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6	391.6
2.5°	400.1	398.5	396.6	393.1	389.5	386.5	383.5	382.0	381.5
5°	410.1	407.2	403.1	396.6	389.5	383.5	378.5	376.0	375.0
7.5°	417.2	414.1	407.6	397.6	387.5	378.5	370.4	366.9	365.9
10°	419.7	416.2	407.2	393.5	380.4	369.4	360.4	355.9	353.8
12.5°	421.7	417.2	405.6	389.5	373.5	359.8	350.3	344.2	342.8
15°	424.2	419.2	405.1	385.6	366.4	350.3	339.8	334.2	332.2
17.5°	421.7	416.2	399.6	377.5	355.9	338.2	326.7	321.7	319.7
20°	413.2	407.2	388.5	365.0	341.7	323.6	312.2	307.1	304.6
22.5°	400.1	393.5	374.4	349.4	325.7	308.1	297.0	292.0	290.5
25°	383.5	377.0	356.9	331.3	308.1	291.0	281.4	277.0	275.4
27.5°	363.9	357.3	337.8	312.6	290.5	274.5	266.9	262.4	261.4
30°	340.3	333.8	314.7	291.6	271.0	255.8	249.8	246.3	245.8
32.5°	314.1	308.6	291.0	269.9	250.4	237.7	233.2	230.7	230.2
35°	288.5	282.5	266.9	247.7	230.7	219.6	215.7	215.1	215.1
37.5°	262.4	256.4	243.8	226.2	211.6	201.5	200.1	200.5	200.5
40°	236.7	231.2	220.2	205.5	192.5	184.9	184.5	185.5	185.9
42.5°	212.6	208.1	198.0	185.5	174.5	168.4	168.9	170.9	172.4
45°	191.0	187.0	178.0	166.8	157.3	152.8	154.3	156.8	158.3
47.5°	171.4	167.9	159.3	149.3	141.2	138.3	140.2	143.3	145.2
50°	153.3	150.3	142.2	131.7	125.2	123.1	125.6	128.7	129.7
52.5°	137.2	134.2	125.6	116.6	111.6	110.6	113.1	115.6	117.1
55°	120.6	118.1	111.1	103.0	99.0	98.6	101.1	103.0	104.0
57.5°	107.1	104.6	98.0	90.9	87.5	86.9	89.4	90.9	91.5
60°	94.0	91.5	85.5	78.9	76.4	76.4	78.0	78.9	79.4
62.5°	81.9	79.4	73.9	68.4	66.3	66.3	66.3	66.8	68.4
65°	70.3	68.4	63.4	58.3	56.8	55.8	55.8	55.8	56.8
67.5°	59.9	57.8	53.8	49.3	47.8	46.2	45.7	46.8	46.8
70°	49.7	48.3	44.3	40.7	39.3	37.7	37.2	39.3	39.3
72.5°	40.7	39.3	36.6	33.2	31.6	31.2	32.2	33.2	33.7
75°	32.2	30.6	28.7	26.6	25.1	25.6	27.2	27.7	28.1
77.5°	24.1	23.7	21.6	20.1	20.1	20.6	21.6	22.6	23.1
80°	17.1	16.6	15.6	14.6	15.1	16.0	16.6	17.6	17.1
82.5°	10.6	10.6	10.0	10.0	10.6	11.6	12.1	12.5	13.1
85°	5.6	5.6	5.6	6.0	6.5	7.1	7.5	8.1	8.1
87.5°	1.5	2.0	2.0	2.5	3.1	3.1	3.5	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)