

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581510

Luminaire Tested: **HCC4W07D010BZ-HM40525930-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581510
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010BZ-HM40525930-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 774.9 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581510
CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581510

CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45872	45872	45872
5°	47719	46283	45787
10°	49285	46705	45691
15°	51028	46852	45690
20°	51192	45705	45115
25°	49376	43429	43769
30°	45947	40435	41589
35°	41379	36997	38367
40°	36502	33669	35198
45°	31905	30335	31817
50°	28266	27287	28745
55°	24859	24107	25053
60°	22178	20574	21191
65°	19496	16694	16432
70°	17022	12298	11252
75°	14154	7435	5957
80°	10655	2841	1776
85°	4953	708	708



TEST NUMBER: P581510
 CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	4.6
10°-20°	104.7	13.5
20°-30°	151.6	19.6
30°-40°	159.9	20.6
40°-50°	138.4	17.9
50°-60°	102.5	13.2
60°-70°	59.1	7.6
70°-80°	20.6	2.7
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.1	37.7
0°-40°	452.1	58.3
0°-60°	693.0	89.4
0°-90°	774.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	774.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	372	372	372	372	372	
5°	385	380	374	371	370	37
15°	400	386	367	358	358	112
25°	363	345	319	317	322	166
35°	275	262	246	251	255	172
45°	183	178	174	180	182	142
55°	116	113	112	116	116	104
65°	67	63	57	54	56	67
75°	30	25	16	12	12	32
85°	4	2	0	0	0	5
90°	0	0	0	0	0	



TEST NUMBER: P581510

CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	371.9	371.9	371.9	371.9	371.9	371.9	371.9	371.9	371.9
2.5°	377.4	376.3	374.9	372.9	370.9	369.4	368.8	368.4	368.4
5°	385.4	383.4	380.4	376.3	373.8	372.4	370.9	369.8	369.8
7.5°	391.0	389.0	384.4	379.0	375.4	372.4	370.3	368.8	368.8
10°	393.5	391.0	385.4	378.4	372.9	368.8	365.9	364.8	364.8
12.5°	396.5	393.5	385.9	376.9	369.8	364.8	361.8	360.9	360.9
15°	399.6	396.0	386.5	375.9	366.9	360.9	358.2	357.8	357.8
17.5°	398.0	393.5	382.4	369.8	359.8	353.8	351.3	351.3	351.8
20°	390.0	385.4	372.9	358.8	348.2	343.7	341.7	342.8	343.7
22.5°	377.9	372.4	358.8	345.3	334.2	330.1	330.1	331.6	333.2
25°	362.8	357.8	344.7	329.7	319.1	316.1	317.0	319.6	321.6
27.5°	345.7	340.3	326.6	312.6	302.0	300.5	303.0	306.6	307.5
30°	322.6	318.1	306.6	292.9	283.9	283.5	286.9	289.5	292.0
32.5°	300.5	295.4	284.4	271.4	264.8	265.4	269.4	272.3	273.9
35°	274.8	270.4	262.3	251.7	245.7	246.7	251.3	254.2	254.8
37.5°	250.7	247.7	239.7	231.7	227.1	229.2	233.2	236.7	236.7
40°	226.7	224.1	218.0	211.6	209.1	211.6	215.5	218.6	218.6
42.5°	203.5	202.0	197.0	192.4	191.0	194.5	198.0	200.5	199.9
45°	182.9	181.4	177.9	174.3	173.9	177.4	180.4	182.0	182.4
47.5°	164.3	163.3	160.3	157.8	157.8	161.3	163.9	165.4	165.8
50°	147.3	146.2	143.7	141.7	142.2	145.8	147.7	149.2	149.8
52.5°	130.2	129.6	127.7	125.2	126.7	129.2	131.7	132.7	133.1
55°	115.6	115.6	113.1	111.1	112.1	114.6	116.1	116.5	116.5
57.5°	102.5	102.0	99.0	97.0	97.5	100.0	101.1	101.5	101.5
60°	89.9	89.4	86.5	83.4	83.4	84.9	85.5	85.9	85.9
62.5°	77.8	77.4	73.9	71.4	70.3	69.9	69.9	70.9	72.8
65°	66.8	66.3	62.8	58.8	57.2	55.8	54.3	55.3	56.3
67.5°	56.8	55.8	52.2	48.7	45.2	42.7	40.2	41.8	43.7
70°	47.2	46.2	42.2	38.2	34.1	30.2	28.1	30.2	31.2
72.5°	38.2	37.2	33.1	29.1	24.1	20.1	19.6	20.1	20.6
75°	29.7	29.1	25.1	20.6	15.6	12.5	12.5	12.5	12.5
77.5°	22.1	21.1	17.1	13.1	9.0	7.1	6.5	6.5	6.5
80°	15.0	14.1	10.6	7.5	4.0	3.0	3.0	2.5	2.5
82.5°	8.5	8.1	5.6	3.0	1.5	1.0	1.0	1.0	1.0
85°	3.5	3.0	2.0	1.0	0.5	0.5	0.5	0.5	0.5
87.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)