

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581517

Luminaire Tested: **HCC4W07D010BZ-HM40525935-41MDH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581517  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W07D010BZ-HM40525935-41MDH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 778.3 lumens  
Efficiency: N/A  
Efficacy: 97.3 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581517  
CATALOG NUMBER: HCC4W07D010BZ-HM40525935-41MDH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P581517

CATALOG NUMBER: HCC4W07D010BZ-HM40525935-41MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	82	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67	67	67	67
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62	62	62	62
7	81	71	65	61	80	71	65	61	69	64	60	68	63	60	67	63	60	58	58	58	58
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
9	73	63	57	53	72	63	57	53	62	56	52	61	56	52	60	55	52	51	51	51	51
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100736
5°	98632
10°	93222
15°	87064
20°	79623
25°	71111
30°	59706
35°	41996
40°	25908
45°	15507
50°	9153
55°	4559
60°	2368
65°	1547
70°	938
75°	763
80°	426
85°	849



TEST NUMBER: P581517  
 CATALOG NUMBER: HCC4W07D010BZ-HM40525935-41MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.4	9.6
10°-20°	190.6	24.5
20°-30°	237.7	30.5
30°-40°	175.1	22.5
40°-50°	72.0	9.3
50°-60°	21.1	2.7
60°-70°	5.4	0.7
70°-80°	1.7	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.6	64.6
0°-40°	677.7	87.1
0°-60°	770.8	99.0
0°-90°	778.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	817	
5°	797	74
15°	682	191
25°	522	238
35°	279	175
45°	89	72
55°	21	21
65°	5	5
75°	2	2
85°	1	0
90°	0	



TEST NUMBER: P581517

CATALOG NUMBER: HCC4W07D010BZ-HM40525935-41MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	816.7
2.5°	808.2
5°	796.6
7.5°	775.4
10°	744.3
12.5°	713.5
15°	681.8
17.5°	646.3
20°	606.6
22.5°	565.2
25°	522.5
27.5°	474.8
30°	419.2
32.5°	352.0
35°	278.9
37.5°	214.4
40°	160.9
42.5°	119.1
45°	88.9
47.5°	65.7
50°	47.7
52.5°	32.8
55°	21.2
57.5°	12.7
60°	9.6
62.5°	6.8
65°	5.3
67.5°	3.8
70°	2.6
72.5°	2.2
75°	1.6
77.5°	1.0
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)