

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592581

Luminaire Tested: **HCC4S07D010MW-HM40525850-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P592581  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S07D010MW-HM40525850-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 739.5 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P592581  
CATALOG NUMBER: HCC4S07D010MW-HM40525850-41WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P592581

CATALOG NUMBER: HCC4S07D010MW-HM40525850-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	52804	52804	52804
5°	55953	52622	49997
10°	58266	51778	47068
15°	60490	50542	44247
20°	61063	48107	40927
25°	59080	44517	37467
30°	55248	40321	34083
35°	49254	35852	30627
40°	43040	31189	27260
45°	37504	26445	23584
50°	32718	22432	20225
55°	28687	18602	16365
60°	25089	15023	12014
65°	21860	11207	6742
70°	19114	7249	2200
75°	15679	3813	620
80°	11649	1705	426
85°	6935	849	849



TEST NUMBER: P592581  
 CATALOG NUMBER: HCC4S07D010MW-HM40525850-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.4	5.5
10°-20°	113.1	15.3
20°-30°	156.3	21.1
30°-40°	157.2	21.3
40°-50°	126.9	17.2
50°-60°	85.8	11.6
60°-70°	43.7	5.9
70°-80°	14.0	1.9
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.8	41.9
0°-40°	467.0	63.2
0°-60°	679.7	91.9
0°-90°	739.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	739.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	428	428	428	428	428	
5°	452	443	425	410	404	44
15°	474	448	396	358	346	133
25°	434	396	327	287	275	199
35°	327	295	238	208	203	204
45°	215	192	152	135	135	167
55°	133	115	86	76	76	120
65°	75	61	38	25	23	75
75°	33	23	8	2	1	35
85°	5	2	1	1	1	7
90°	0	0	0	0	0	



TEST NUMBER: P592581

CATALOG NUMBER: HCC4S07D010MW-HM40525850-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1
2.5°	439.6	437.2	434.8	430.5	425.6	420.8	417.8	415.3	414.1
5°	451.9	448.8	443.4	434.1	425.0	416.5	409.8	405.6	403.8
7.5°	461.6	457.4	448.1	435.4	421.4	408.0	399.4	393.4	390.9
10°	465.2	460.3	448.1	431.2	413.4	397.0	384.9	378.7	375.8
12.5°	469.5	464.1	448.8	427.4	405.6	386.1	372.1	364.2	361.1
15°	473.7	466.5	448.1	422.0	395.8	373.3	358.0	350.2	346.5
17.5°	473.7	465.2	443.4	412.9	383.1	359.3	342.2	333.1	330.0
20°	465.2	455.5	431.8	398.3	366.5	341.1	324.6	315.5	311.8
22.5°	451.9	440.9	415.3	380.5	347.1	322.2	305.7	297.1	293.5
25°	434.1	423.2	396.5	360.5	327.1	302.0	286.8	278.9	275.3
27.5°	413.4	401.3	374.5	338.6	305.7	282.0	267.9	260.6	257.6
30°	387.9	376.3	350.2	314.9	283.1	261.3	248.4	241.7	239.3
32.5°	358.0	348.3	322.7	289.8	260.0	239.9	228.4	222.8	220.4
35°	327.1	317.8	295.3	264.9	238.1	219.2	208.3	204.6	203.4
37.5°	297.8	289.8	267.9	239.9	215.5	199.1	189.4	187.0	185.7
40°	267.3	261.9	241.7	216.2	193.7	179.0	171.2	169.3	169.3
42.5°	239.9	233.9	216.2	193.0	173.0	158.3	152.8	151.0	151.6
45°	215.0	208.8	192.4	171.2	151.6	139.4	135.2	135.2	135.2
47.5°	191.9	186.3	171.2	149.2	133.4	123.6	119.4	119.4	119.9
50°	170.5	166.8	149.8	130.9	116.9	107.8	104.7	104.1	105.4
52.5°	150.4	146.1	130.9	113.9	100.5	93.2	90.1	89.6	90.1
55°	133.4	128.5	115.1	98.7	86.5	79.2	75.6	74.9	76.1
57.5°	116.9	113.2	99.2	84.7	73.1	65.8	62.7	61.5	62.1
60°	101.7	98.1	85.2	71.2	60.9	53.6	49.3	48.1	48.7
62.5°	87.7	84.7	72.5	59.1	48.7	42.0	37.8	34.7	36.0
65°	74.9	71.8	60.9	47.5	38.4	31.1	24.9	22.5	23.1
67.5°	64.0	60.3	50.0	37.8	28.7	20.7	14.0	12.7	12.7
70°	53.0	49.3	40.2	29.2	20.1	10.9	6.1	6.1	6.1
72.5°	42.7	39.6	31.1	22.0	12.7	4.9	2.4	2.4	2.4
75°	32.9	30.5	23.1	15.2	8.0	2.4	1.8	1.3	1.3
77.5°	24.4	22.0	16.4	10.4	4.9	1.3	1.3	1.3	1.3
80°	16.4	14.6	10.9	6.1	2.4	0.6	0.6	0.6	0.6
82.5°	9.8	8.5	6.1	3.1	1.3	0.6	0.6	0.6	0.6
85°	4.9	3.6	2.4	1.3	0.6	0.6	0.6	0.6	0.6
87.5°	1.3	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)