

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581528

Luminaire Tested: **HCC4S07D010MW-HM40525935-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010MW-HM40525935-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 816.3 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581528
CATALOG NUMBER: HCC4S07D010MW-HM40525935-41RWWC

Luminous Intensity Polar Plot





TEST NUMBER: P581528

CATALOG NUMBER: HCC4S07D010MW-HM40525935-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88				
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76				76				
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67				
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58				58				
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52				
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46				
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41				41				
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37				37				
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34				34				
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31				31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	48314	48314	48314
5°	50270	48771	48227
10°	51915	49185	48133
15°	53735	49355	48129
20°	53922	48147	47530
25°	52003	45756	46110
30°	48397	42600	43796
35°	43592	38984	40400
40°	38451	35456	37066
45°	33614	31939	33509
50°	29762	28745	30261
55°	26193	25375	26408
60°	23386	21684	22326
65°	20547	17599	17307
70°	17924	12983	11829
75°	14869	7816	6291
80°	11294	2983	1847
85°	5378	849	849



TEST NUMBER: P581528
 CATALOG NUMBER: HCC4S07D010MW-HM40525935-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.8	4.6
10°-20°	110.3	13.5
20°-30°	159.7	19.6
30°-40°	168.5	20.6
40°-50°	145.8	17.9
50°-60°	108.0	13.2
60°-70°	62.3	7.6
70°-80°	21.7	2.7
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	307.7	37.7
0°-40°	476.2	58.3
0°-60°	730.0	89.4
0°-90°	816.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	392	392	392	392	392	
5°	406	401	394	391	390	39
15°	421	407	386	377	377	118
25°	382	363	336	334	339	175
35°	290	276	259	265	268	181
45°	193	187	183	190	192	150
55°	122	119	118	122	123	110
65°	70	66	60	57	59	70
75°	31	26	16	13	13	34
85°	4	2	1	1	1	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581528

CATALOG NUMBER: HCC4S07D010MW-HM40525935-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	391.7	391.7	391.7	391.7	391.7	391.7	391.7	391.7	391.7
2.5°	397.5	396.5	394.9	392.7	390.7	389.1	388.5	388.1	388.1
5°	406.0	403.9	400.7	396.5	393.9	392.3	390.7	389.5	389.5
7.5°	411.8	409.7	404.9	399.1	395.5	392.3	390.1	388.5	388.5
10°	414.5	411.8	406.0	398.6	392.7	388.5	385.3	384.3	384.3
12.5°	417.6	414.5	406.5	397.0	389.5	384.3	381.1	380.1	380.1
15°	420.8	417.1	407.1	395.9	386.5	380.1	377.4	376.9	376.9
17.5°	419.2	414.5	402.9	389.5	379.0	372.7	370.0	370.0	370.5
20°	410.8	406.0	392.7	377.9	366.8	362.1	359.9	361.0	362.1
22.5°	398.1	392.3	377.9	363.7	352.0	347.8	347.8	349.4	351.0
25°	382.1	376.9	363.1	347.2	336.2	333.0	334.0	336.6	338.8
27.5°	364.2	358.4	344.0	329.2	318.2	316.6	319.2	322.9	324.0
30°	339.8	335.0	322.9	308.6	299.1	298.5	302.3	304.9	307.5
32.5°	316.6	311.2	299.6	285.9	278.9	279.5	283.7	286.9	288.5
35°	289.5	284.7	276.3	265.2	258.9	259.9	264.7	267.9	268.3
37.5°	264.1	260.9	252.5	244.0	239.2	241.4	245.6	249.3	249.3
40°	238.8	236.1	229.8	222.8	220.2	222.8	227.0	230.2	230.2
42.5°	214.4	212.8	207.5	202.8	201.2	204.8	208.6	211.2	210.6
45°	192.7	191.1	187.4	183.7	183.1	186.9	190.0	191.6	192.1
47.5°	173.1	172.1	168.9	166.3	166.3	169.9	172.5	174.1	174.7
50°	155.1	154.1	151.4	149.3	149.8	153.5	155.7	157.2	157.7
52.5°	137.1	136.6	134.4	131.8	133.4	136.0	138.7	139.7	140.3
55°	121.8	121.8	119.1	117.0	118.0	120.7	122.2	122.8	122.8
57.5°	108.0	107.4	104.2	102.2	102.6	105.4	106.4	107.0	107.0
60°	94.8	94.2	91.0	87.9	87.9	89.4	90.0	90.5	90.5
62.5°	82.0	81.5	77.8	75.2	74.1	73.6	73.6	74.7	76.7
65°	70.4	69.9	66.1	61.9	60.3	58.7	57.1	58.3	59.3
67.5°	59.9	58.7	55.1	51.3	47.7	45.0	42.3	43.9	46.1
70°	49.7	48.7	44.5	40.3	36.0	31.8	29.6	31.8	32.8
72.5°	40.3	39.1	34.9	30.7	25.4	21.2	20.6	21.2	21.7
75°	31.2	30.7	26.5	21.7	16.4	13.2	13.2	13.2	13.2
77.5°	23.3	22.2	18.0	13.8	9.6	7.4	6.8	6.8	6.8
80°	15.9	14.8	11.2	8.0	4.2	3.2	3.2	2.6	2.6
82.5°	9.0	8.4	5.8	3.2	1.6	1.0	1.0	1.0	1.0
85°	3.8	3.2	2.2	1.0	0.6	0.6	0.6	0.6	0.6
87.5°	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)