

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581483

Luminaire Tested: **HCC4S07D010MW-HM40525927-41WDH**

Issue Date: 9/9/2021

### Test Information

Test Method: LM-41-14  
 Report Number: P581483  
 TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 9/9/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO COMMERCIAL  
 Catalog Number: HCC4S07D010MW-HM40525927-41WDH  
 Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM  
 Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER  
 Ballast/Driver: ELECTRONIC DRIVER

### Summary


Lumens per Lamp: N/A  
 Luminaire Lumens: 721.4 lumens  
 Efficiency: N/A  
 Efficacy: 90.2 lumens/watt  
 Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11  
 Luminous Opening: Circular (Dia: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 8  
 Input Voltage (V): NR  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



TEST NUMBER: P581483  
CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581483

CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	72	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	83	73	66	61	81	72	66	61	70	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	60	56	65	60	55	64	59	55	63	58	55	53	53	53	53
8	74	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	60649
5°	61116
10°	61873
15°	63414
20°	63885
25°	62060
30°	56914
35°	46814
40°	34135
45°	22154
50°	12492
55°	5914
60°	2319
65°	1459
70°	974
75°	667
80°	355
85°	708



TEST NUMBER: P581483  
 CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.1	6.5
10°-20°	140.0	19.4
20°-30°	207.7	28.8
30°-40°	191.8	26.6
40°-50°	100.2	13.9
50°-60°	27.4	3.8
60°-70°	5.3	0.7
70°-80°	1.5	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	394.8	54.7
0°-40°	586.7	81.3
0°-60°	714.3	99.0
0°-90°	721.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	721.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	492	
5°	494	47
15°	497	140
25°	456	208
35°	311	192
45°	127	100
55°	28	27
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581483  
CATALOG NUMBER: HCC4S07D010MW-HM40525927-41WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	491.7
2.5°	490.4
5°	493.6
7.5°	494.9
10°	494.0
12.5°	494.9
15°	496.6
17.5°	494.9
20°	486.7
22.5°	473.6
25°	456.0
27.5°	432.1
30°	399.6
32.5°	358.4
35°	310.9
37.5°	261.2
40°	212.0
42.5°	166.7
45°	127.0
47.5°	93.1
50°	65.1
52.5°	43.4
55°	27.5
57.5°	16.3
60°	9.4
62.5°	6.8
65°	5.0
67.5°	3.6
70°	2.7
72.5°	1.8
75°	1.4
77.5°	0.9
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)