

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581509

Luminaire Tested: **HCC4S07D010SL-HM40525930-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010SL-HM40525930-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 748.7 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581509
CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581509

CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69								
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62								
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56								
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51								
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46								
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42								
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39								
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	59872	59872	59872
5°	59717	59791	59791
10°	59017	59080	59017
15°	58319	58319	58319
20°	55931	56049	56114
25°	52302	52384	52506
30°	46873	47001	47001
35°	38051	38352	38442
40°	28709	28870	28951
45°	21997	21909	21909
50°	18134	18038	18038
55°	15569	15440	15440
60°	13864	13765	13765
65°	13046	13046	13046
70°	12154	12154	12154
75°	11009	11247	11009
80°	10371	10016	10371
85°	8491	8491	8491



TEST NUMBER: P581509
 CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	6.1
10°-20°	128.0	17.1
20°-30°	175.8	23.5
30°-40°	158.1	21.1
40°-50°	99.9	13.3
50°-60°	65.2	8.7
60°-70°	44.2	5.9
70°-80°	24.9	3.3
80°-90°	7.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.5	46.7
0°-40°	507.6	67.8
0°-60°	672.8	89.9
0°-90°	748.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	748.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	482	482	483	483	483	46
15°	457	457	457	457	457	128
25°	384	385	385	386	386	175
35°	253	254	255	256	255	157
45°	126	126	126	126	126	100
55°	72	72	72	72	72	65
65°	45	45	45	45	45	44
75°	23	24	24	24	23	25
85°	6	6	6	6	6	7
90°	0	0	0	0	0	



TEST NUMBER: P581509

CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	485.4	485.4	485.4	485.4	485.4
2.5°	482.9	482.9	482.9	482.9	482.9
5°	482.3	482.3	482.9	482.9	482.9
7.5°	478.8	479.3	479.3	479.3	479.3
10°	471.2	471.2	471.7	471.7	471.2
12.5°	464.2	464.2	464.2	464.8	464.2
15°	456.7	456.7	456.7	456.7	456.7
17.5°	443.6	444.2	444.2	444.2	444.2
20°	426.1	427.0	427.0	427.5	427.5
22.5°	405.9	406.4	406.9	407.4	406.9
25°	384.3	384.9	384.9	385.8	385.8
27.5°	359.3	359.7	360.7	360.7	360.7
30°	329.1	329.6	330.0	330.0	330.0
32.5°	293.4	293.4	294.4	294.9	294.4
35°	252.7	253.7	254.7	255.7	255.3
37.5°	214.1	215.0	215.5	215.5	216.0
40°	178.3	179.3	179.3	180.4	179.8
42.5°	150.2	149.8	149.8	150.7	150.2
45°	126.1	125.6	125.6	125.6	125.6
47.5°	108.6	108.0	108.0	108.0	108.0
50°	94.5	94.0	94.0	94.0	94.0
52.5°	82.8	82.4	82.4	82.4	81.9
55°	72.4	72.4	71.8	72.4	71.8
57.5°	62.8	62.8	62.8	62.8	62.8
60°	56.2	55.8	55.8	55.8	55.8
62.5°	50.2	50.2	50.2	50.2	50.2
65°	44.7	44.7	44.7	44.7	44.7
67.5°	39.1	38.7	39.1	39.1	38.7
70°	33.7	33.1	33.7	33.7	33.7
72.5°	28.1	28.1	28.1	28.7	28.1
75°	23.1	23.6	23.6	23.6	23.1
77.5°	18.5	19.1	18.5	18.5	18.5
80°	14.6	14.1	14.1	14.1	14.6
82.5°	10.0	10.0	10.0	10.0	10.0
85°	6.0	6.0	6.0	6.0	6.0
87.5°	2.5	2.5	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)