

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581527

Luminaire Tested: **HCC4W07D010SL-HM40525935-41WDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010SL-HM40525935-41WDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 788.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.07 / 1.04
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581527
CATALOG NUMBER: HCC4W07D010SL-HM40525935-41WDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581527

CATALOG NUMBER: HCC4W07D010SL-HM40525935-41WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89					89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78					78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69					69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62					62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56					56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51					51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46					46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42					42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39					39			
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36					36			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	63054	63054	63054
5°	62899	62973	62973
10°	62173	62248	62173
15°	61422	61422	61422
20°	58897	59055	59107
25°	55092	55174	55310
30°	49365	49522	49522
35°	40084	40400	40475
40°	30255	30416	30513
45°	23165	23078	23078
50°	19093	18997	18997
55°	16387	16279	16279
60°	14629	14481	14481
65°	13747	13747	13747
70°	12803	12803	12803
75°	11628	11867	11628
80°	10939	10513	10939
85°	9057	9057	9057



TEST NUMBER: P581527
 CATALOG NUMBER: HCC4W07D010SL-HM40525935-41WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	6.1
10°-20°	134.8	17.1
20°-30°	185.2	23.5
30°-40°	166.5	21.1
40°-50°	105.2	13.3
50°-60°	68.7	8.7
60°-70°	46.5	5.9
70°-80°	26.2	3.3
80°-90°	7.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.2	46.7
0°-40°	534.7	67.8
0°-60°	708.6	89.8
0°-90°	788.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	788.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	508	508	509	509	509	48
15°	481	481	481	481	481	135
25°	405	405	405	406	406	185
35°	266	267	268	269	269	166
45°	133	132	132	132	132	105
55°	76	76	76	76	76	69
65°	47	47	47	47	47	47
75°	24	25	25	25	24	26
85°	6	6	6	6	6	7
90°	0	0	0	0	0	



TEST NUMBER: P581527

CATALOG NUMBER: HCC4W07D010SL-HM40525935-41WDW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	511.2	511.2	511.2	511.2	511.2
2.5°	508.6	508.6	508.6	508.6	508.6
5°	508.0	508.0	508.6	508.6	508.6
7.5°	504.4	504.8	504.8	504.8	504.8
10°	496.4	496.4	497.0	497.0	496.4
12.5°	489.0	489.0	489.0	489.5	489.0
15°	481.0	481.0	481.0	481.0	481.0
17.5°	467.3	467.8	467.8	467.8	467.8
20°	448.7	449.9	449.9	450.3	450.3
22.5°	427.5	428.1	428.7	429.1	428.7
25°	404.8	405.4	405.4	406.4	406.4
27.5°	378.4	379.0	380.0	380.0	380.0
30°	346.6	347.2	347.7	347.7	347.7
32.5°	309.1	309.1	310.1	310.7	310.1
35°	266.2	267.2	268.3	269.4	268.8
37.5°	225.4	226.5	227.0	227.0	227.6
40°	187.9	188.9	188.9	189.9	189.5
42.5°	158.2	157.7	157.7	158.8	158.2
45°	132.8	132.3	132.3	132.3	132.3
47.5°	114.3	113.8	113.8	113.8	113.8
50°	99.5	99.0	99.0	99.0	99.0
52.5°	87.3	86.8	86.8	86.8	86.3
55°	76.2	76.2	75.7	76.2	75.7
57.5°	66.1	66.1	66.1	66.1	66.1
60°	59.3	58.7	58.7	58.7	58.7
62.5°	52.9	52.9	52.9	52.9	52.9
65°	47.1	47.1	47.1	47.1	47.1
67.5°	41.3	40.7	41.3	41.3	40.7
70°	35.5	34.9	35.5	35.5	35.5
72.5°	29.6	29.6	29.6	30.2	29.6
75°	24.4	24.9	24.9	24.9	24.4
77.5°	19.6	20.1	19.6	19.6	19.6
80°	15.4	14.8	14.8	14.8	15.4
82.5°	10.6	10.6	10.6	10.6	10.6
85°	6.4	6.4	6.4	6.4	6.4
87.5°	2.6	2.6	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)