

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581589

Luminaire Tested: **HCC6S10D010SL-HM60525835-61MDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581589  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S10D010SL-HM60525835-61MDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1123.6 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581589  
CATALOG NUMBER: HCC6S10D010SL-HM60525835-61MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P581589  
 CATALOG NUMBER: HCC6S10D010SL-HM60525835-61MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97	97	96	94	94	91	89	87	85															
	1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	91	89	87	85	83	81	80	79	79																
	2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	83	81	80	79	79	77	74	72	72																
	3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	77	73	69	67	67	63	62	62	62																
	4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	71	67	63	62	62	62	62	62	62	62															
	5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	63	59	57	57	57	57	57	57	57	57															
	6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	63	59	57	57	57	57	57	57	57	57															
	7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	63	58	55	53	53	53	53	53	53	53															
	8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	63	58	55	53	53	53	53	53	53	53															
	9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	59	55	51	50	50	50	50	50	50	50															
	10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	56	51	48	47	47	47	47	47	47	47															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	56273
5°	56224
10°	55644
15°	54524
20°	51647
25°	46642
30°	39620
35°	29252
40°	16917
45°	8978
50°	5074
55°	2647
60°	1732
65°	1232
70°	882
75°	678
80°	505
85°	503



TEST NUMBER: P581589  
 CATALOG NUMBER: HCC6S10D010SL-HM60525835-61MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.8	8.6
10°-20°	268.7	23.9
20°-30°	350.7	31.2
30°-40°	268.0	23.9
40°-50°	97.0	8.6
50°-60°	28.1	2.5
60°-70°	10.0	0.9
70°-80°	3.5	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.2	63.7
0°-40°	984.2	87.6
0°-60°	1109.4	98.7
0°-90°	1123.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1123.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1026	
5°	1022	97
15°	961	269
25°	771	351
35°	437	268
45°	116	97
55°	28	28
65°	10	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P581589  
CATALOG NUMBER: HCC6S10D010SL-HM60525835-61MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1026.5
2.5°	1021.7
5°	1021.7
7.5°	1014.6
10°	999.6
12.5°	982.1
15°	960.7
17.5°	928.9
20°	885.3
22.5°	831.3
25°	771.1
27.5°	702.9
30°	625.9
32.5°	539.4
35°	437.1
37.5°	330.0
40°	236.4
42.5°	163.5
45°	115.8
47.5°	83.3
50°	59.5
52.5°	42.0
55°	27.7
57.5°	19.8
60°	15.8
62.5°	12.7
65°	9.5
67.5°	7.9
70°	5.5
72.5°	4.0
75°	3.2
77.5°	2.4
80°	1.6
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)