

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581585

Luminaire Tested: **HCC6S10D010SL-HM60525830-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010SL-HM60525830-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1118.4 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581585
CATALOG NUMBER: HCC6S10D010SL-HM60525830-61WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P581585

CATALOG NUMBER: HCC6S10D010SL-HM60525830-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87				87				
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76				76				
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66				66				
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58				
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52				52				
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46				46				
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42				42				
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38				38				
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34				34				
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31				31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	31308	31308	31308
5°	31983	31295	30734
10°	32960	31011	29965
15°	34007	30596	29223
20°	34542	29449	28032
25°	33976	27697	26421
30°	32347	25681	24694
35°	29500	23182	22821
40°	25791	20825	20717
45°	22196	18327	18746
50°	19300	15965	16298
55°	16860	14021	14164
60°	14966	12148	11118
65°	13361	10222	8496
70°	11765	8383	7133
75°	10061	6608	6778
80°	8113	5683	6661
85°	5409	4906	5913



TEST NUMBER: P581585
 CATALOG NUMBER: HCC6S10D010SL-HM60525830-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	4.8
10°-20°	153.9	13.8
20°-30°	219.7	19.6
30°-40°	230.2	20.6
40°-50°	193.8	17.3
50°-60°	137.9	12.3
60°-70°	80.7	7.2
70°-80°	38.2	3.4
80°-90°	9.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.7	38.2
0°-40°	657.9	58.8
0°-60°	989.6	88.5
0°-90°	1118.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1118.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	571	571	571	571	571	
5°	581	576	569	561	558	56
15°	599	577	539	517	515	169
25°	562	522	458	436	437	257
35°	441	404	346	335	341	274
45°	286	265	236	237	242	222
55°	176	162	147	147	148	159
65°	103	91	79	66	66	103
75°	48	40	31	30	32	51
85°	9	7	8	9	9	11
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581585

CATALOG NUMBER: HCC6S10D010SL-HM60525830-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1
2.5°	571.9	571.9	571.1	570.3	568.7	566.3	564.9	563.3	563.3
5°	581.2	579.7	576.5	572.7	568.7	564.1	560.9	558.5	558.5
7.5°	589.0	585.9	579.7	572.7	565.5	559.3	553.9	550.8	550.0
10°	592.1	588.2	578.9	567.9	557.1	548.5	542.2	538.3	538.3
12.5°	595.2	590.6	578.1	562.5	548.5	536.7	530.5	527.4	526.6
15°	599.2	592.9	577.3	557.8	539.1	525.8	517.2	514.9	514.9
17.5°	599.2	591.4	571.9	547.7	524.2	509.4	501.6	499.3	500.1
20°	592.1	583.5	560.1	530.5	504.8	489.1	481.3	479.7	480.5
22.5°	578.9	568.7	542.2	510.2	482.1	465.7	458.7	458.7	457.9
25°	561.7	550.8	522.0	488.3	457.9	441.6	436.0	436.8	436.8
27.5°	539.1	528.2	499.3	463.4	433.0	416.6	412.7	414.2	415.0
30°	511.0	499.3	468.9	433.8	405.7	389.3	386.9	389.3	390.1
32.5°	476.7	468.1	438.4	402.5	376.1	362.0	361.2	363.6	366.7
35°	440.8	431.4	404.1	371.3	346.4	334.7	334.7	338.6	341.0
37.5°	401.7	392.5	367.4	340.2	319.1	308.1	309.7	313.6	314.4
40°	360.4	353.4	332.4	308.9	291.0	282.4	284.7	288.7	289.5
42.5°	321.4	315.1	298.1	277.0	263.6	257.4	260.6	265.2	266.8
45°	286.3	279.3	265.2	247.3	236.4	233.3	237.2	240.3	241.8
47.5°	254.4	248.1	236.4	219.9	212.2	210.7	214.5	216.1	217.7
50°	226.3	219.9	208.3	193.5	187.2	187.2	190.4	191.9	191.1
52.5°	198.9	193.5	182.6	170.0	166.2	166.2	168.6	169.2	170.8
55°	176.4	170.8	161.5	149.8	146.7	145.1	146.7	146.7	148.2
57.5°	155.2	150.6	142.0	131.1	127.1	125.7	124.9	124.1	125.7
60°	136.5	132.7	123.3	113.9	110.8	106.9	103.8	100.6	101.4
62.5°	119.3	115.5	106.9	97.5	94.4	89.0	85.0	81.2	82.7
65°	103.0	99.0	91.2	83.4	78.8	72.6	66.3	64.0	65.5
67.5°	88.2	85.0	77.2	69.4	65.5	58.5	52.3	52.3	53.1
70°	73.4	70.2	64.0	56.9	52.3	46.1	43.7	44.5	44.5
72.5°	60.1	57.7	51.5	45.3	40.5	36.7	36.7	37.5	38.3
75°	47.5	46.1	39.7	34.3	31.2	28.9	30.5	31.2	32.0
77.5°	36.7	34.3	29.7	25.7	23.4	24.2	25.7	26.5	27.3
80°	25.7	25.0	21.1	18.7	18.0	18.7	20.3	21.1	21.1
82.5°	16.4	15.6	13.2	12.5	12.5	13.2	14.8	14.8	14.8
85°	8.6	7.8	7.0	7.0	7.8	8.6	9.4	9.4	9.4
87.5°	3.2	2.4	3.2	3.2	3.8	3.8	3.8	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)