

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581631

Luminaire Tested: **HCC6W10D010MW-HM60525927-61RWWH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W10D010MW-HM60525927-61RWWH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 916.2 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.19
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581631
CATALOG NUMBER: HCC6W10D010MW-HM60525927-61RWWH

Luminous Intensity Polar Plot





TEST NUMBER: P581631

CATALOG NUMBER: HCC6W10D010MW-HM60525927-61RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77								
3	95	86	79	74	93	84	78	73	82	76	72	79	74	70	77	73	69	67								
4	88	78	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59								
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53								
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47								
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	25628	25628	25628
5°	25897	25666	25490
10°	26263	25584	25311
15°	26884	25420	25176
20°	27133	24665	24735
25°	26542	23427	23868
30°	25137	21763	22497
35°	22761	19890	20626
40°	19823	17977	18642
45°	16816	15909	16482
50°	14899	13901	14268
55°	13123	11890	11823
60°	11753	10021	9210
65°	10494	8029	6590
70°	9232	5786	4119
75°	7795	3495	2330
80°	5998	1547	979
85°	3459	377	377



TEST NUMBER: P581631
 CATALOG NUMBER: HCC6W10D010MW-HM60525927-61RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	4.8
10°-20°	127.6	13.9
20°-30°	184.4	20.1
30°-40°	194.0	21.2
40°-50°	163.1	17.8
50°-60°	114.5	12.5
60°-70°	63.0	6.9
70°-80°	22.4	2.4
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	356.3	38.9
0°-40°	550.4	60.1
0°-60°	827.9	90.4
0°-90°	916.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	916.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	468	468	468	468	468	
5°	471	469	466	464	463	45
15°	474	466	448	442	444	134
25°	439	417	387	388	395	201
35°	340	320	297	303	308	211
45°	217	211	205	210	213	170
55°	137	130	124	124	124	124
65°	81	72	62	51	51	80
75°	37	29	16	11	11	39
85°	6	3	1	1	1	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581631

CATALOG NUMBER: HCC6W10D010MW-HM60525927-61RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	467.5	467.5	467.5	467.5	467.5	467.5	467.5	467.5	467.5
2.5°	467.5	467.5	466.9	466.9	465.7	465.7	465.1	465.1	465.1
5°	470.6	470.6	469.4	467.5	466.4	464.5	464.5	463.9	463.2
7.5°	472.5	471.8	470.0	467.5	464.5	461.4	460.2	460.8	460.2
10°	471.8	470.6	468.2	463.2	459.6	455.3	454.7	454.0	454.7
12.5°	473.1	471.3	466.4	460.2	454.0	449.2	448.6	448.6	449.2
15°	473.7	471.8	465.7	456.5	447.9	443.1	442.4	443.1	443.6
17.5°	471.8	469.4	460.2	447.9	438.2	433.2	433.2	434.5	435.7
20°	465.1	461.4	448.6	433.9	422.8	419.2	420.4	422.8	424.0
22.5°	452.8	448.6	433.9	417.3	405.7	402.7	405.7	408.8	410.0
25°	438.8	433.9	416.7	399.5	387.3	383.6	387.9	392.8	394.6
27.5°	419.7	414.2	398.4	378.7	366.4	364.6	369.5	375.0	376.3
30°	397.1	391.0	373.2	354.8	343.8	343.1	348.7	353.5	355.4
32.5°	369.5	364.1	348.7	330.3	320.5	320.5	326.0	330.3	332.1
35°	340.1	333.9	320.5	305.2	297.2	297.8	303.4	306.4	308.2
37.5°	305.2	303.4	293.0	280.1	274.5	275.8	280.1	282.5	284.4
40°	277.0	272.1	265.3	254.9	251.2	252.4	256.7	259.2	260.5
42.5°	246.3	243.3	237.7	230.4	228.0	229.8	233.4	235.3	234.7
45°	216.9	216.3	210.8	206.5	205.2	207.7	210.2	212.0	212.6
47.5°	195.5	193.0	188.1	185.1	183.8	186.3	188.7	189.9	189.9
50°	174.7	172.2	167.3	164.3	163.0	165.5	167.3	168.6	167.3
52.5°	153.8	151.3	147.0	143.4	142.7	144.0	144.7	145.2	146.5
55°	137.3	134.8	130.0	125.7	124.4	125.0	124.4	124.4	123.7
57.5°	121.4	118.9	114.0	109.1	107.2	106.6	104.8	104.1	103.6
60°	107.2	104.1	99.3	93.7	91.4	88.9	85.8	84.0	84.0
62.5°	93.7	90.7	85.1	80.3	76.6	72.3	67.4	65.0	65.0
65°	80.9	78.4	72.3	66.8	61.9	56.4	50.8	49.6	50.8
67.5°	68.6	66.2	60.1	54.6	48.4	41.7	36.8	36.8	38.0
70°	57.6	55.1	49.6	42.9	36.1	29.4	25.7	25.7	25.7
72.5°	47.2	44.7	38.6	32.5	25.7	19.0	17.2	17.8	17.2
75°	36.8	35.0	29.4	22.6	16.5	11.7	11.0	10.4	11.0
77.5°	27.6	25.7	20.8	14.7	9.2	6.8	6.1	6.1	6.1
80°	19.0	17.2	13.5	8.6	4.9	3.1	3.1	3.1	3.1
82.5°	11.7	9.8	7.4	4.3	1.8	1.8	1.8	1.8	1.8
85°	5.5	4.3	3.1	1.2	0.6	0.6	0.6	0.6	0.6
87.5°	1.2	1.2	0.6	0.6	0.0	0.6	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)