

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581665

Luminaire Tested: **HCC6S10D010SL-HM60525935-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S10D010SL-HM60525935-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 997.3 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581665
CATALOG NUMBER: HCC6S10D010SL-HM60525935-61PSMDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581665

CATALOG NUMBER: HCC6S10D010SL-HM60525935-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88	88	88	88	88	88	88	88																
	2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78	78	78	78	78	78	78	78	78	78	78																
	3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69	69	69	69	69	69	69	69	69	69	69																
	4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62	62	62	62	62	62	62	62	62	62	62																
	5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56	56	56	56	56	56	56	56	56	56	56																
	6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51	51	51	51	51	51	51	51	51	51	51																
	7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46	46	46	46	46	46	46	46	46	46	46																
	8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43	43	43	43	43	43	43	43	43	43	43																
	9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39	39	39	39	39	39	39	39	39	39	39																
	10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36	36	36	36	36	36	36	36	36	36	36																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35644
5°	35549
10°	35019
15°	34461
20°	33329
25°	31744
30°	28985
35°	23336
40°	15729
45°	11474
50°	9919
55°	8955
60°	8497
65°	8042
70°	7565
75°	7159
80°	6693
85°	6164



TEST NUMBER: P581665
 CATALOG NUMBER: HCC6S10D010SL-HM60525935-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.1	6.1
10°-20°	170.5	17.1
20°-30°	239.6	24.0
30°-40°	213.3	21.4
40°-50°	119.2	12.0
50°-60°	84.9	8.5
60°-70°	61.8	6.2
70°-80°	35.8	3.6
80°-90°	11.1	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.2	47.3
0°-40°	684.5	68.6
0°-60°	888.7	89.1
0°-90°	997.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	997.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	650	
5°	646	61
15°	607	171
25°	525	240
35°	349	213
45°	148	119
55°	94	85
65°	62	62
75°	34	36
85°	10	11
90°	0	



TEST NUMBER: P581665
CATALOG NUMBER: HCC6S10D010SL-HM60525935-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	650.2
2.5°	647.4
5°	646.0
7.5°	640.4
10°	629.1
12.5°	618.5
15°	607.2
17.5°	591.7
20°	571.3
22.5°	548.8
25°	524.8
27.5°	495.2
30°	457.9
32.5°	410.0
35°	348.7
37.5°	279.7
40°	219.8
42.5°	175.5
45°	148.0
47.5°	129.6
50°	116.3
52.5°	104.3
55°	93.7
57.5°	85.2
60°	77.5
62.5°	70.4
65°	62.0
67.5°	54.9
70°	47.2
72.5°	40.2
75°	33.8
77.5°	27.5
80°	21.2
82.5°	15.5
85°	9.8
87.5°	5.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)