

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581711

Luminaire Tested: **HCC6S15D010BZ-HM60525827-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S15D010BZ-HM60525827-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1420.8 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581711
CATALOG NUMBER: HCC6S15D010BZ-HM60525827-61WWWB

Luminous Intensity Polar Plot





TEST NUMBER: P581711

CATALOG NUMBER: HCC6S15D010BZ-HM60525827-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58								
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42								
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38								
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34								
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39772	39772	39772
5°	40628	39759	39049
10°	41877	39395	38064
15°	43195	38871	37123
20°	43888	37412	35616
25°	43164	35192	33570
30°	41095	32625	31366
35°	37477	29446	28984
40°	32769	26457	26314
45°	28204	23281	23816
50°	24511	20289	20707
55°	21399	17815	17997
60°	19012	15426	14122
65°	16980	12985	10805
70°	14938	10643	9056
75°	12814	8388	8599
80°	10323	7198	8461
85°	6856	6227	7485



TEST NUMBER: P581711
 CATALOG NUMBER: HCC6S15D010BZ-HM60525827-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.7	4.8
10°-20°	195.6	13.8
20°-30°	279.2	19.6
30°-40°	292.4	20.6
40°-50°	246.2	17.3
50°-60°	175.2	12.3
60°-70°	102.6	7.2
70°-80°	48.5	3.4
80°-90°	12.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.4	38.2
0°-40°	835.8	58.8
0°-60°	1257.2	88.5
0°-90°	1420.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1420.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	726	726	726	726	726	
5°	738	732	722	713	710	71
15°	761	733	685	657	654	215
25°	714	663	582	554	555	327
35°	560	513	440	425	433	348
45°	364	337	300	301	307	282
55°	224	205	186	186	188	202
65°	131	116	100	84	83	130
75°	60	50	40	39	41	65
85°	11	9	10	12	12	14
90°	0	0	0	0	0	



TEST NUMBER: P581711

CATALOG NUMBER: HCC6S15D010BZ-HM60525827-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5
2.5°	726.5	726.5	725.5	724.5	722.5	719.6	717.5	715.6	715.6
5°	738.3	736.4	732.4	727.4	722.5	716.5	712.6	709.6	709.6
7.5°	748.3	744.3	736.4	727.4	718.6	710.6	703.7	699.7	698.7
10°	752.3	747.3	735.4	721.5	707.7	696.8	688.8	683.8	683.8
12.5°	756.3	750.2	734.5	714.6	696.8	681.9	674.0	670.0	669.0
15°	761.1	753.2	733.4	708.7	684.9	668.1	657.1	654.1	654.1
17.5°	761.1	751.3	726.5	695.8	666.0	647.2	637.3	634.4	635.3
20°	752.3	741.4	711.6	674.0	641.3	621.4	611.5	609.5	610.5
22.5°	735.4	722.5	688.8	648.2	612.6	591.7	582.8	582.8	581.8
25°	713.6	699.7	663.1	620.4	581.8	560.9	554.0	555.0	555.0
27.5°	684.9	671.0	634.4	588.7	550.0	529.3	524.3	526.3	527.3
30°	649.2	634.4	595.6	551.0	515.4	494.5	491.6	494.5	495.5
32.5°	605.5	594.6	556.9	511.4	477.7	459.9	458.9	461.8	465.8
35°	560.0	548.1	513.4	471.8	440.0	425.2	425.2	430.2	433.1
37.5°	510.4	498.5	466.8	432.1	405.3	391.5	393.5	398.4	399.4
40°	457.9	449.0	422.2	392.5	369.7	358.8	361.7	366.7	367.7
42.5°	408.4	400.4	378.6	351.8	334.9	327.1	331.1	337.0	338.9
45°	363.8	354.8	337.0	314.2	300.3	296.3	301.3	305.3	307.2
47.5°	323.1	315.2	300.3	279.4	269.6	267.6	272.5	274.6	276.5
50°	287.4	279.4	264.6	245.8	237.9	237.9	241.9	243.8	242.8
52.5°	252.8	245.8	231.9	216.1	211.1	211.1	214.1	215.1	217.0
55°	223.9	217.0	205.2	190.3	186.4	184.3	186.4	186.4	188.3
57.5°	197.3	191.2	180.4	166.5	161.5	159.6	158.6	157.5	159.6
60°	173.4	168.4	156.6	144.7	140.7	135.7	131.8	127.8	128.8
62.5°	151.6	146.6	135.7	123.9	120.0	112.9	108.1	103.1	105.1
65°	130.9	125.9	116.0	106.0	100.1	92.2	84.2	81.3	83.3
67.5°	112.0	108.1	98.1	88.2	83.3	74.3	66.4	66.4	67.4
70°	93.2	89.2	81.3	72.3	66.4	58.5	55.5	56.5	56.5
72.5°	76.3	73.3	65.4	57.4	51.5	46.5	46.5	47.6	48.6
75°	60.5	58.5	50.5	43.6	39.6	36.7	38.7	39.6	40.6
77.5°	46.5	43.6	37.7	32.7	29.7	30.8	32.7	33.7	34.7
80°	32.7	31.7	26.8	23.8	22.8	23.8	25.8	26.8	26.8
82.5°	20.8	19.9	16.8	15.9	15.9	16.8	18.8	18.8	18.8
85°	10.9	9.9	9.0	9.0	9.9	10.9	11.9	11.9	11.9
87.5°	4.0	3.0	4.0	4.0	5.0	5.0	5.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)