

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581727

Luminaire Tested: **HCC6W15D010SL-HM60525830-61WWBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W15D010SL-HM60525830-61WWBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1351.0 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581727
CATALOG NUMBER: HCC6W15D010SL-HM60525830-61WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P581727

CATALOG NUMBER: HCC6W15D010SL-HM60525830-61WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69								
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	66	63	61								
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54								
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49								
7	72	60	52	47	70	59	52	47	58	51	46	56	51	46	55	50	46	44								
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40								
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37								
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41565	41565	41565
5°	42367	41487	40546
10°	43803	40953	39233
15°	45142	40239	38002
20°	45848	38568	36018
25°	45015	35923	33534
30°	42791	32733	30777
35°	38467	29259	27760
40°	33198	25641	24796
45°	28104	22072	21498
50°	24102	18643	18456
55°	20893	15694	15082
60°	18244	12740	10756
65°	16046	9819	5954
70°	13848	6491	2917
75°	11755	3177	1123
80°	9092	1357	695
85°	5346	629	629



TEST NUMBER: P581727
 CATALOG NUMBER: HCC6W15D010SL-HM60525830-61WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.5	5.3
10°-20°	202.3	15.0
20°-30°	284.9	21.1
30°-40°	291.1	21.5
40°-50°	234.7	17.4
50°-60°	157.4	11.7
60°-70°	79.7	5.9
70°-80°	25.5	1.9
80°-90°	3.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.8	41.4
0°-40°	849.8	62.9
0°-60°	1242.0	91.9
0°-90°	1351.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1351.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	758	758	758	758	758	
5°	770	764	754	742	737	74
15°	795	764	709	677	670	225
25°	744	686	594	558	554	341
35°	575	522	437	413	415	358
45°	362	334	285	275	277	282
55°	219	194	164	157	158	197
65°	124	102	76	50	46	123
75°	56	40	15	5	5	60
85°	8	4	1	1	1	11
90°	0	0	0	0	0	



TEST NUMBER: P581727

CATALOG NUMBER: HCC6W15D010SL-HM60525830-61WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	758.2	758.2	758.2	758.2	758.2	758.2	758.2	758.2	758.2
2.5°	761.4	760.2	759.2	757.0	753.9	750.7	748.5	746.4	745.4
5°	769.9	767.7	764.5	760.2	753.9	746.4	742.2	737.9	736.8
7.5°	781.6	777.4	768.8	759.2	748.5	737.9	730.4	726.2	723.0
10°	786.9	779.5	767.7	751.7	735.7	723.0	713.3	707.0	704.8
12.5°	791.2	782.7	765.6	744.2	723.0	705.9	695.2	689.9	687.8
15°	795.4	786.9	763.5	735.7	709.0	688.8	677.1	671.8	669.6
17.5°	795.4	783.7	756.0	720.8	688.8	664.3	652.6	647.3	646.2
20°	785.9	773.0	739.0	697.3	661.1	633.3	622.7	619.5	617.4
22.5°	767.7	752.8	714.4	667.5	628.0	601.4	589.6	587.5	585.4
25°	744.2	729.4	685.7	635.5	593.9	567.3	557.6	555.6	554.4
27.5°	714.4	698.5	652.6	601.4	556.6	531.1	522.4	522.4	521.4
30°	676.0	658.0	613.1	561.9	517.1	493.7	487.3	487.3	486.2
32.5°	629.1	611.0	570.5	521.4	478.7	454.2	448.9	451.0	450.0
35°	574.8	559.8	522.4	474.5	437.2	414.8	412.7	414.8	414.8
37.5°	520.4	506.4	474.5	432.9	397.7	377.5	377.5	380.7	379.7
40°	463.9	453.2	423.4	387.0	358.3	344.4	342.3	345.5	346.5
42.5°	410.5	402.0	376.4	346.5	321.0	307.1	310.3	312.5	313.5
45°	362.5	354.0	333.8	302.8	284.7	275.1	275.1	278.3	277.3
47.5°	319.8	313.5	293.3	263.3	247.4	243.1	245.3	247.4	247.4
50°	282.6	273.0	253.8	230.3	218.6	213.3	215.4	216.4	216.4
52.5°	247.4	241.0	221.8	200.4	189.8	186.6	186.6	187.6	187.6
55°	218.6	211.1	194.1	172.7	164.2	159.9	156.7	155.7	157.8
57.5°	190.9	184.4	168.4	148.2	138.6	134.4	127.9	125.9	127.9
60°	166.4	161.1	145.1	125.9	116.2	107.7	100.2	96.0	98.1
62.5°	145.1	138.6	122.6	106.6	96.0	86.4	74.7	68.2	71.4
65°	123.7	118.4	102.4	86.4	75.7	64.0	50.2	45.9	45.9
67.5°	104.5	99.2	84.2	70.4	57.5	43.7	30.9	29.9	30.9
70°	86.4	81.0	68.2	54.4	40.5	26.7	18.2	18.2	18.2
72.5°	71.4	65.0	53.3	39.5	25.5	13.8	9.6	10.7	10.7
75°	55.5	50.2	39.5	26.7	15.0	6.4	5.3	5.3	5.3
77.5°	41.5	37.3	27.7	17.0	7.5	2.2	2.2	2.2	2.2
80°	28.8	24.5	18.2	10.7	4.3	2.2	2.2	2.2	2.2
82.5°	17.0	15.0	10.7	5.3	2.2	1.0	1.0	1.0	1.0
85°	8.5	7.5	4.3	2.2	1.0	1.0	1.0	1.0	1.0
87.5°	2.2	2.2	1.0	1.0	0.0	1.0	1.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)